



MSR Gold™ MiniFastFit – substituição fácil da lâmpada, em segundos

MSR Gold™ MiniFastFit (DJ/Club)

Graças à base e ao suporte da lâmpada especialmente concebidos, a lâmpada MSR Gold™ MiniFastFit leva apenas segundos a substituir, ajudando a assegurar um entretenimento sem interrupções. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. O fácil manuseio e o design de equipamentos pequenos e compactos são possíveis devido ao tamanho compacto das lâmpadas, ao passo que a oscilação muito pequena proporciona uma sensação de luminosidade elevada e uma elevada intensidade de feixe.

Benefícios

- Lamp replacement in just seconds
- Easy handling, smaller and lighter fixtures
- Reduces early lamp or lamp holder failures. Excellent current transfer
- High perceived brightness
- High beam intensity

MSR Gold™ MiniFastFit (DJ/Club)

Características

- Philips MiniFastFit
- Compact design
- Innovative gold plated pins
- Color temperature >8000K
- Very short arc


Aplicação

- Eventos
- Espectáculos
- DJ/Clubes

Versions



Desenho dimensional



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Gold™ 300/2	23 mm	5,0 mm	65,8 mm	67,8 mm	66,8 mm	126 mm
MiniFastFit 1CT/4						

