



Product Description

MSR Hot Restrike

High-efficiency hot restrike metal halide lamps designed for optimum light collection

Benefits

- High luminous efficacy
- Compact arc (5 - 20 mm)
- Excellent colour rendering
- Dimmable with a stable colour temperature

Features

- Run-up time 2 minutes
- Frosted top of outer bulb to avoid excessively bright centre beam in open face luminaires
- Universal burning position

Application


- Indoor and outdoor filming
- Studios and theatres
- Professional photography
- Solar simulation

MSR Hot Restrike

Versions



Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 575	30 mm	7.0	69 mm	71 mm	70	145 mm	43 mm	42	41 mm
HR 1CT/4		mm			mm			mm	

