



MSR Platinum 35 – enhanced stage lighting

MSR Platinum (Touring/Stage)

Produktbeschreibung:

Vorteile

- Hohe Lichtausbeute
- Lange Lebensdauer

Merkmale

- Kurzer Lichtbogen
- Kompaktes System
- Philips FastFit-Technologie
- Philips Platinum-Technologie

Anwendung


- Events
- Shows/Theater
- Tourneen/Bühne

MSR Platinum (Touring/Stage)

Versions



Abmessungsskizzen



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Platinum 35 1CT	23,5 mm	3,0 mm	55 mm	57 mm	56 mm	116 mm

