



# MSR Platinum 35 – enhanced stage lighting

## MSR Platinum (Touring/Stage)

Today's stage designs call for lighting solutions which deliver high brightness and high-contrast beams to avoid shadow creation, as well as more compact luminaire and fixture designs to improve creative choice and design flexibility. Addressing this need, we have developed an incredibly powerful, brilliant and lightweight, compact system for the most amazing light experience – MSR Platinum 35. This lamp system provides a powerful and innovative tool to create intense lighting and delivers the same good light quality as other MSR lamps. The exceptionally short arc generates sparkling, bright light and this ultra-compact design makes the lamp suitable for smaller stage lighting fixtures.

### Benefits

- High beam intensity, high brightness
- Freedom to create smaller and lighter fixtures
- High perceived brightness
- Easy and fast lamp replacement
- A long and reliable lifetime

### Features

- Very short arc
- Compact system
- High Correlated color temperature
- Philips FastFit technology
- Philips Platinum technology

### Application


- Events
- Shows/Theater
- Touring/Stage

# MSR Platinum (Touring/Stage)

## Versions



## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Platinum 35 1CT	23.5 mm	3.0 mm	55 mm	57 mm	56 mm	116 mm

