



# MSR Platinum 35 ST – The best choice for studio/theater lighting

## MSR Platinum (Studio)

MSR Platinum 35 ST has been specially designed for the studio/theater world, where consistent high-quality light output, high brightness and excellent color rendering are important. This lightweight, compact system delivers intense, cool-white light for the most amazing light experience. It's a powerful and innovative tool, giving lighting designers far greater freedom and delivering the same good light quality as other MSR lamps. The exceptionally short arc generates sparkling, bright light, and the lamp's ultra-compact design makes it suitable for smaller lighting fixtures. The MSR Platinum 35 ST lamp has a balanced spectrum with extra red content for enhanced color rendering.

### Benefits

- High beam intensity, high brightness
- Freedom to create smaller and lighter fixtures
- High perceived brightness
- Easy and fast lamp replacement
- A long and reliable lifetime

### Features

- Very short arc
- Compact system
- High Correlated color temperature
- Philips FastFit technology
- Philips Platinum technology

# MSR Platinum (Studio)

## Application

- Events
- Shows/Theater
- Touring/Stage

## Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

## Versions



MSR Platinum 35 (ST)

## Dimensional drawing



| Product               | D (max) | O       | L (min)   | L (max)  | L        | C (max)   | F         |
|-----------------------|---------|---------|-----------|----------|----------|-----------|-----------|
| MSR Platinum 35<br>ST | 1 in    | 3/16 in | 2-3/16 in | 2-1/4 in | 2-1/4 in | 4-9/16 in | 1-7/16 in |

## MSR Platinum (Studio)

