



MSR Short Arc – for longer life

MSR Short Arc

The lamp's short arc and compact design helps enable a compact luminaire that provides high beam intensity, while the excellent color rendition characteristics help ensure optimal colors on stage. The highly innovative P3 technology, developed by Philips, allows MSR Short Arc lamps to be used at higher temperatures in any burning position. The result? Longer lifetime, fewer early failures and a highly consistent performance throughout the lamp's lifetime.

Benefits

- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time
- High beam intensity
- Compact design luminaries
- Excellent color characteristics, optimal colors on stage

Features

- Philips Pinch Protection
- Short arc
- Compact lamp design
- MSR filling

Application

- Entertainment


MSR Short Arc

Versions



MSR 1200 SA, MSR 2000 SA

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR 1200 SA 1CT/4	34 mm	7.0 mm	58 mm	60 mm	59 mm	135 mm

Colour Rendering Diagrams

