



MSR Gold™ MiniFastFit – lamp replacement in seconds

MSR Gold™ MiniFastFit (Touring/Stage)

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Benefits

- Lamp replacement in just seconds
- Easy handling, smaller and lighter fixtures
- Reduces early lamp or lamp holder failures. Excellent current transfer
- High perceived brightness
- High beam intensity

Features

- Philips MiniFastFit
- Compact design
- Innovative gold plated pins
- High color temperature
- Very short arc

Application

- Events
- Shows
- Touring/Stage

MSR Gold™ MiniFastFit (Touring/Stage)

Versions




MSR Gold™ 300/2 MiniFastFit




MSR Gold™ 400, 575/2, 700(1,2) MiniFastFit

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold™ 700/2 MiniFastFit 1CT/4	23.2 mm	3.8 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Gold™ 300/2 MiniFastFit 1CT/4	23 mm	5.0 mm	65.8 mm	67.8 mm	66.8 mm	126 mm

Controls and Dimming

Dimmable Yes

General Information

Cap-Base PGJX28
Life To 50% Failures (Nom) 750 h
Main Application Entertainment
Operating Position UNIVERSAL
System Description MiniFastFit

Light Technical

Color Code 2

Operating and Electrical

MSR Gold™ MiniFastFit (Touring/Stage)

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
928177105115	MSR Gold™ 300/2 MiniFastFit 1CT/4	3.8 A	300 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
928199905115	MSR Gold™ 700/2 MiniFastFit 1CT/4	10.2 A	700 W

Light Technical

Order Code	Full Product Name	Correlated Color			
		Temperature (Nom)	Rendering Index (Nom)	Luminous Flux (Min)	Luminous Flux (Nom)
928177105115	MSR Gold™ 300/2 MiniFastFit 1CT/4	9300 K	80	21000 lm	23000 lm

Order Code	Full Product Name	Correlated Color			
		Temperature (Nom)	Rendering Index (Nom)	Luminous Flux (Min)	Luminous Flux (Nom)
928199905115	MSR Gold™ 700/2 MiniFastFit 1CT/4	7200 K	75	44000 lm	47000 lm

