



TUV Amalgam XPT- Maximum efficiency, independent of temperature

TUV Amalgam XPT systems

Philips TUV Amalgam XPT system consists of an electronic driver that operates one TUV Amalgam XPT lamp, mounted in a sleeve. The electrical specifications are tailored to the lamp, ensuring an optimized performance of the Philips TUV Amalgam XPT system. Thanks to extensive testing before a lamp system is released, we can ensure maximum reliability and long lifetime.

Vantaggi

- Security of effective disinfection over the useful lifetime of the lamp
- Extreme reliability of driver; with annual failure rate of less than 1%
- Approximately 10% energy savings, because lamps can be dimmed to reach the same UV output compared to similar lamps on the market
- High system efficacy because it is not required to over-design the purification system to maintain effectiveness of disinfection
- Best environmental choice because of long reliable life, less waste and industry leading low amount of mercury
- High efficiency during dimming thanks to unique amalgam temperature control of the 800W lamps

TUV Amalgam XPT systems

Caratteristiche

- Short-wave UV radiation with a peak at 253.7 nm (UVC) for disinfection
- Special amalgam used for highest efficiency over wide temperature range
- Protective inside coating ensures constant UV output over the complete lifetime of the lamp
- Philips electronic driver available for a perfect interface
- Minimized amount of mercury
- Universal burning position possible for the T6 range, depending on lamp type and sleeve dimensions
- Tailor-made solutions possible
- Lamp can be made from special quartz (open/synthetic) to maximize 185 nm Ozone generation


Applicazione

- Deactivation of bacteria, viruses and other micro-organisms
- Municipal drinking water treatment equipment
- Process water treatment equipment
- Swimming pool units
- Equipment for the production of ultra-pure water, for example for the semiconductor, pharmaceuticals and cosmetics industry (ozone version)

Versions



Disegno tecnico



Product	D	O	C (max)
TUV 130W XPT SE UNP/20	19 mm	740 mm	842 mm

