



# Compact Source – for higher performance luminaires

## Broadway Compact Source Studio Théâtre monoculot

The very compact filament in the Compact Source series helps create a proportionately high beam intensity and the Compact Source range is therefore ideal for the latest generation of high-performance luminaires. Also, thanks to their low energy consumption, each dimmer can serve significantly more fixtures, thereby reducing overall dimmer costs. What's more, the Compact Source lamps incorporate the innovative P3 technology, developed by Philips, which enables the lamps to be used at higher temperatures in any burning position. This results in longer lamp lifetimes, reduced lamp replacement costs, and a more consistent lighting performance over the whole lifetime of the lamp.

### Avantages

- Permet une utilisation à des températures supérieures dans n'importe quelle position de fonctionnement. Durée de vie plus longue, moins de défaillances précoces, performances constantes sur le long terme.
- Intensité de faisceau élevée. Grâce à une consommation d'énergie réduite, un plus grand nombre d'appareillages de chaque variateur peut être proposé.

### Fonctions

- Protection de pincement P3 de Philips
- Filament très compact

### Application


- Éclairage pour studio, scène et divertissement

## Broadway Compact Source Studio Théâtre monoculot

### Versions



### Schéma dimensionnel



Product	D (max)	H	W	L	C (max)
6991P 600W G9.5 240V 1CT/10	19 mm	15.5 mm	8.5 mm	60.5 mm	101 mm

