



Halogen Low Voltage – long life, low costs

Halogen Low Voltage

The long lifetime of most of the Halogen Low Voltage lamps is further extended by the unique P3 technology developed by Philips. This allows the lamp to be used at higher temperatures, thereby extending the lamp's lifetime, reducing early failures, and resulting in fewer maintenance man hour costs. P3 also ensures consistency of high-quality light output, and allows the lamp to be used in any burning position, which enables more compact fixture designs. In addition, the compact filament produces a clean white light and high beam intensity for true natural colors on stage and without any hotspots.

Benefits

- Suitable for low-cost luminaires

Features


- Colour temperature: 3100 K
- Very compact filament enabling high efficiency
- Optimum between light and life
- Even light distribution over the entire beam
- Universal burning position

Application

- Discos
- Moving beam luminaires

Halogen Low Voltage

Dimensional drawing



Product	D (max)	C (max)
13163 ELC/5H 250W GX5.3 24V 1CT/24	50 mm	44.5 mm
13164 200W GX5.3 24V 1CT/24	50.7 mm	44.5 mm

General Information	
Cap-Base	GX5.3
Operating Position	S90
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	24 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Operating and Electrical

Order Code	Full Product Name	Power Consumption
923921120594	13164 200W GX5.3 24V 1CT/24	200 W

Order Code	Full Product Name	Power Consumption
924862720540	13163 ELC/5H 250W GX5.3 24V 1CT/24	250 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
923921120594	13164 200W GX5.3 24V 1CT/24	-

Order Code	Full Product Name	Bulb Shape
924862720540	13163 ELC/5H 250W GX5.3 24V 1CT/24	R50

