



Halogen Low Voltage – long life, low costs

Halogen Low Voltage

The long lifetime of most of the Halogen Low Voltage lamps is further extended by the unique P3 technology developed by Philips. This allows the lamp to be used at higher temperatures, thereby extending the lamp's lifetime, reducing early failures, and resulting in fewer maintenance man hour costs. P3 also ensures consistency of high-quality light output, and allows the lamp to be used in any burning position, which enables more compact fixture designs. In addition, the compact filament produces a clean white light and high beam intensity for true natural colors on stage and without any hotspots.

Benefits

- Suitable for low-cost luminaires

Features

- Colour temperature: 3100 K
- Very compact filament enabling high efficiency
- Optimum between light and life
- Even light distribution over the entire beam
- Universal burning position

Application


- Discos
- Moving beam luminaires

Halogen Low Voltage

Versions



Dimensional drawing



Product	D (max)	C (max)
6423XHP FO 150W GZ6.35 15V 1CT/10X5F	50 mm	42 mm

