



# Halogen FastFit - lamp replacement in seconds

## Halogen FastFit

Halogen FastFit lamps are replaced in seconds - thanks to the specially designed base. The compact filament ensures high beam intensity, while the shock-resistant design allows easy handling and reliable use in moving head systems. In addition, the highly innovative P3 technology allows use at higher temperatures, which further extends lifetime and consistency of light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. And because the FastFit design is also applied to Philips MSR/MSD Gold™ lamps, switching lamp technologies is also quick and easy.

### Benefits

- Lamp replacement in just seconds, exchangeable with HID lamp
- High beam intensity
- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time
- Easy handling, ideal for moving head systems

### Features

- Philips FastFit
- Compact Filament
- Philips P3 pinch protection technology
- Compact, shock resistant design

### Application


- Entertainment

# Halogen FastFit

## Versions



## Dimensional drawing



| Product                  | D (max) | H       | W       | L     | C (max) | E (max) |
|--------------------------|---------|---------|---------|-------|---------|---------|
| Hi-Brite 7016G 1200W 80V | 25 mm   | 10.5 mm | 11.7 mm | 82 mm | 140 mm  | 41 mm   |
| FastFit                  |         |         |         |       |         |         |

