



Product Description

Halogen reflector

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

Benefits

- Negligible depreciation in light output during lifetime
- High efficacy gives low energy consumption

Features

- Dichroic coating on glass reflector radiates about 75% of the generated heat backwards, keeping temperatures within safe limits
- Halogen burner is precisely aligned using an optical system, so no realignment is needed when the lamp is replaced

Application


- 8/16 mm film projection
- Slide projection
- Enlargers
- Minilabs/colour printers
- Overhead projection
- Medical equipment
- Solar simulation
- Measuring equipment
- Fibre optical applications

Halogen reflector

Versions



Dimensional drawing



Product	D (max)	C (max)
6423XHP FO 150W GZ6.35 15V 1CT/10X5F	50 mm	42 mm

