



HPL – approved for Source Four™

HPL

HPL lamps include a barrel-shaped filament that is approved by ETC for use in its Source Four™ fixtures. Bright, high quality light and high beam intensity is assured by the optimal filament design, while the unique P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which extends lifetime and consistency of high-quality light output, resulting in fewer early failures and fewer maintenance man hour costs.

优点

- Enables use at higher temperature in any burning position. Longer lifetime, fewer early failures, consistent performance over time.
- High beam intensity
- High beam intensity and high quality bright light

特点

- Philips Pinch Protection
- Optimal filament
- Designed for Source FourTM fixtures


应用

- Studio
- Theatre stages
- Entertainment lighting

Versions



二维绘图



Product	D (max)	H	W	D1	L	C (max)
7008 750W Heat Sink 115V 1CT/10	19 mm	10.5 mm	6.3 mm	6.3 mm	60.3 mm	104 mm
7007 575W Heat Sink 115V 1CT/10	19 mm	9 mm	6 mm	6 mm	60.3 mm	104 mm

控制調光	
可調光	Yes
運作和電氣	
電壓 (標稱)	115 V
基本資訊	
接口	HEATSINK
壽命 (故障率 50%) (標稱)	300 h
主要應用	Entertainment
操作位置	UNIVERSAL
系統說明	P3 技術
照明科技	
相關色溫 (標稱)	3250 K
顯色指數 (Nom)	100
機械和殼體	
燈泡表層	透明 (CL)
燈絲形狀	Bi-Plane

運作和電氣

Order Code	Full Product Name	速效 HBC 保險絲	功率 (額定)(標稱)
924554934428	7007 575W Heat Sink 115V 1CT/10	10 V	575 W
924555134428	7008 750W Heat Sink 115V 1CT/10	6.3 V	750 W

基本資訊

Order Code	Full Product Name	Philips 代碼
924554934428	7007 575W Heat Sink 115V 1CT/10	7007

Order Code	Full Product Name	Philips 代碼
924555134428	7008 750W Heat Sink 115V 1CT/10	7008

照明科技

Order Code	Full Product Name	光通量 (額定)(標稱)
924554934428	7007 575W Heat Sink 115V 1CT/10	16520 lm

Order Code	Full Product Name	光通量 (額定)(標稱)
924555134428	7008 750W Heat Sink 115V 1CT/10	21900 lm

