



# Halogen High Voltage DE – great color for film and video

## Halogen High Voltage DE

The high, constant light output and consistent color temperature of these double ended high voltage halogen lamps ensure attractive, accurately exposed pictures for both film and video. In addition, the wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.

### Benefits

- Studio/film: Good color rendering
- Video: Makes attractive, accurately exposed pictures possible

### Features

- Studio/film: Color temperature of 3200K
- Video: High constant light output and color temperature

### Application

- Studio/film: Studio, film, theater and disco lighting
- Video: Portable film and video lights


# Halogen High Voltage DE

## Versions



R7s

## Dimensional drawing



Product	D (max)	W	A	C (max)
PF801 R 1000W R7s 230V 1CT/10	9 mm	72 mm	121.7 mm	125.1 mm

