



Halogen High Voltage SE (Theater) – super extended lamp life

Halogen High Voltage SE (Theater)

Two distinctive features make this lamp ideal for use in theater luminaires where long life is essential. Firstly, the filament is especially designed for extended lifetime. Secondly the highly innovative P3 technology, developed by Philips, allows the pinch to better withstand extreme heat conditions which extends the average lamp lifetime, ensures consistent high-quality light output over time, and results in fewer early failures and fewer maintenance man hour costs.

优点

- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time.
- Ideal for theater lighting applications

特点

- Philips Pinch Protection
- Special filament design for use in luminaires where longer life is of great importance

应用



- Stage and theater lighting
- Effect lighting for discos and shows

Halogen High Voltage SE (Theater)

Versions



二维绘图



Product	D (max)	H	W	L	C (max)
6998P 650W GX9.5 230V 1CT/10	22 mm	12.5 mm	10 mm	55 mm	110 mm

Product	D (max)	H	W	L	C (max)
6800C 500W P28s 120V 1CT/10	20 mm	10 mm	8.5 mm	55.6 mm	130 mm

控制調光	
可調光	Yes
基本資訊	
主要應用	Entertainment
操作位置	UNIVERSAL
機械和殼體	
燈泡表層	透明 (CL)
燈絲形狀	Bi-Plane

運作和電氣

Halogen High Voltage SE (Theater)

Order Code	Full Product Name	電壓 (標稱)	速效 HBC 保險絲	功率 (額定)(標稱)
923865043228	6998P 650W GX9.5 230V 1CT/10	230 V	4 V	650 W

Order Code	Full Product Name	電壓 (標稱)	速效 HBC 保險絲	功率 (額定)(標稱)
924516636328	6800C 500W P28s 120V 1CT/10	120 V	6.3 V	500 W

基本資訊

Order Code	Full Product Name	Ansi 代碼	接口	LIF 代碼	壽命 (故障率 50%) (標稱)	Philips 代碼	系統說明
923865043228	6998P 650W GX9.5 230V 1CT/10	-	GX9.5	T/21 (T/12)	900 h	6998P	P3 技術
924516636328	6800C 500W P28s 120V 1CT/10	BTL	P28S	-	750 h	6800C	鈉

照明科技

Order Code	Full Product Name	相關色溫 (標稱)	光通量 (額定)(標稱)
923865043228	6998P 650W GX9.5 230V 1CT/10	3000 K	13000 lm

Order Code	Full Product Name	相關色溫 (標稱)	光通量 (額定)(標稱)
924516636328	6800C 500W P28s 120V 1CT/10	2950 K	11000 lm

