



Flexo print TL – high efficiency in reprographics and photopolymerization

Flexo Print

Flexo print TL lamps emit almost all of their light (99.9%) in the useful UVA and visible blue wavebands – between 350 and 400 nm – and have peak intensity at 370 nm (except for the /03 version). This makes them ideal for flexo printing equipment and photopolymerization processes. In addition, the 'R' lamps in the family have an internal 200-degree reflector to further optimize the lamp's overall efficiency.

优点

- Best match with photo sensitizers
- Highest output on irradiated area

特点

- Emit radiation in the range 380–480 nm with a maximum at 370 nm
- Internal reflector

应用

- Flexoprint reprographic equipment, Diazo copying machines


安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions




二维绘图



Product
TL 100W/10-R UV-A
TL 80W/10-R SLV/25
TL 60W/10-R SLV/25

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 140W/03	40.5 mm	1500 mm	1507.1 mm	1504.7 mm	1514.2 mm

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-K 40W/10-R	40.5 mm	589.8 mm	596.9 mm	594.5 mm	604 mm



基本信息	
底盖	G13
机械和壳体	
灯泡外形	T38

运营和电气

Order Code	Full Product Name	灯具电流 (标	功率(额定) 标	
		称)	电压 (标称)	称)
928004101029	Actinic BL TL-K 40W/10-R	0.86 A	50 V	40.5 W
928005901029	TL 80W/10-R SLV/25	0.83 A	110 V	80 W
928006901029	TL 100W/10-R UV-A	0.97 A	122 V	100 W

Order Code	Full Product Name	灯具电流 (标	功率(额定) 标	
		称)	电压 (标称)	称)
928008401003	TL 60W/10-R SLV/25	0.7 A	102 V	62 W
928012700303	TL 140W/03	1.46 A	118 V	140 W

基本信息

Order Code	Full Product Name	50% 故障条件下	有效寿命 (标	
		的使用寿命(标称)	称)	主要应用
928004101029	Actinic BL TL-K 40W/10-R	2000 h	2000 h	Insect traps
928005901029	TL 80W/10-R SLV/25	1000 h	1000 h	复印 (R)

Order Code	Full Product Name	50% 故障条件下	有效寿命 (标	
		的使用寿命(标称)	称)	主要应用
928006901029	TL 100W/10-R UV-A	2000 h	1000 h	Phototherapy
928008401003	TL 60W/10-R SLV/25	2000 h	1000 h	复印 (R)
928012700303	TL 140W/03	3000 h	-	复印 (R)

照明科技

Order Code	Full Product Name	颜色代码	颜色名称
928004101029	Actinic BL TL-K 40W/10-R	10-R	紫外线 A
928005901029	TL 80W/10-R SLV/25	10-R	紫外线 A
928006901029	TL 100W/10-R UV-A	10-R	紫外线 A

Order Code	Full Product Name	颜色代码	颜色名称
928008401003	TL 60W/10-R SLV/25	10-R	紫外线 A
928012700303	TL 140W/03	03	超光化学的

紫外线

Order Code	Full Product Name	紫外线 A 辐射	紫外线 A 辐射	UV-B/UV-A
		100 小时 (IEC)	0 小时 (IEC)	(IEC)
928004101029	Actinic BL TL-K 40W/10-R	7.4 W	8.0 W	0.1 %
928005901029	TL 80W/10-R SLV/25	20.5 W	-	0.1 %

Order Code	Full Product Name	紫外线 A 辐射	紫外线 A 辐射	UV-B/UV-A
		100 小时 (IEC)	0 小时 (IEC)	(IEC)
928006901029	TL 100W/10-R UV-A	26.0 W	28.0 W	0.1 %
928008401003	TL 60W/10-R SLV/25	15.8 W	-	0.1 %
928012700303	TL 140W/03	1.00 W	-	-

应用

Order Code	Full Product Name	汞 (Hg) 含量 (标称)
928004101029	Actinic BL TL-K 40W/10-R	-
928005901029	TL 80W/10-R SLV/25	13.0 mg
928006901029	TL 100W/10-R UV-A	13.0 mg

Order Code	Full Product Name	汞 (Hg) 含量 (标称)
928008401003	TL 60W/10-R SLV/25	13.0 mg
928012700303	TL 140W/03	-

