



TUV PL-L - Compact solution for professional applications

TUV PL-L

TUV PL-L lamps are compact UVC (germicidal) lamps used in professional water and air disinfection units. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-L lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Thanks to the single-ended lamp base, lamp replacement is easy.

Benefits

- Security of effective disinfection over the useful lifetime of the lamp
- High system efficacy because it is not required to over-design the purification system to maintain effectiveness of disinfection

Features

- Short-wave UV radiation with a peak at 253.7 nm (UVC) for disinfection purposes
- Protective inside coating ensures constant UV output over the complete lifetime of the lamp
- Special lamp glass filters out the 185 nm ozone-forming radiation
- High Output versions contain wind-chill correction for improved performance in moving air and reducing amount of required lamps
- High Output versions for optimum UVC output per lamp length, allowing for reduction of system size
- Warning sign on lamp indicates that the lamp radiates UVC


Application

- Deactivation of bacteria, viruses and other micro-organisms
- Residential drinking water units
- Fish pond and process water units
- In-duct air treatment units
- Stand alone air purifiers
- Air disinfection systems in for example hospitals, universities and laboratories

Versions



Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-L 95W/4P HO 1CT/25	18 mm	38 mm	505 mm	530 mm	535 mm
TUV PL-L 60W/4P HO 1CT/25	18 mm	38 mm	390 mm	415 mm	420 mm
TUV PL-L 55W/4P HF 1CT/25	18 mm	38 mm	505 mm	530 mm	535 mm
TUV PL-L 18W/4P 1CT/25	18 mm	39 mm	195 mm	220 mm	225 mm
TUV PL-L 36W/4P 1CT/25	18 mm	38 mm	385 mm	410 mm	415 mm
TUV PL-L 24W/4P UNP/50	18 mm	39 mm	290 mm	315 mm	320 mm
TUV PL-L 24W/4P 1CT/25	18 mm	39 mm	290 mm	315 mm	320 mm
TUV PL-L 35W/4P HO 1CT/25	18 mm	39 mm	195 mm	220 mm	225 mm

General Information

Cap-Base	2G11
Useful Life (Nom)	9000 h
Main Application	Disinfection

Light Technical

Colour Code	TUV
Colour Designation	-
Lumen Depreciation At Useful Lifetime	15 %

Mechanical and Housing

Bulb Shape	2xT16
------------	-------

Approval and Application

TUV PL-L

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
62492540	TUV PL-L 18W/4P 1CT/25	4.4 mg
21248500	TUV PL-L 24W/4P 1CT/25	4.4 mg
61294665	TUV PL-L 24W/4P UNP/50	4.4 mg
62878740	TUV PL-L 36W/4P 1CT/25	-

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
88827340	TUV PL-L 35W/4P HO 1CT/25	4.4 mg
63379840	TUV PL-L 55W/4P HF 1CT/25	4.4 mg
71034540	TUV PL-L 60W/4P HO 1CT/25	4.4 mg
88829740	TUV PL-L 95W/4P HO 1CT/25	4.4 mg

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power (Rated) (Nom)
62492540	TUV PL-L 18W/4P 1CT/25	0.37 A	60 V	18 W
21248500	TUV PL-L 24W/4P 1CT/25	0.345 A	87 V	24 W
61294665	TUV PL-L 24W/4P UNP/50	0.345 A	87 V	24 W
62878740	TUV PL-L 36W/4P 1CT/25	0.44 A	105 V	36 W
88827340	TUV PL-L 35W/4P HO 1CT/25	0.85 A	42 V	35 W

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power (Rated) (Nom)
63379840	TUV PL-L 55W/4P HF 1CT/25	0.54 A	103 V	55 W
71034540	TUV PL-L 60W/4P HO 1CT/25	0.800 A	84 V	60 W
88829740	TUV PL-L 95W/4P HO 1CT/25	0.8 A	115 V	90 W

General Information

Order Code	Full Product Name	System Description
62492540	TUV PL-L 18W/4P 1CT/25	na
21248500	TUV PL-L 24W/4P 1CT/25	na
61294665	TUV PL-L 24W/4P UNP/50	na
62878740	TUV PL-L 36W/4P 1CT/25	na

Order Code	Full Product Name	System Description
88827340	TUV PL-L 35W/4P HO 1CT/25	na
63379840	TUV PL-L 55W/4P HF 1CT/25	High Frequency
71034540	TUV PL-L 60W/4P HO 1CT/25	na
88829740	TUV PL-L 95W/4P HO 1CT/25	High Frequency

UV

Order Code	Full Product Name	UV-C Radiation
62492540	TUV PL-L 18W/4P 1CT/25	5.5 W
21248500	TUV PL-L 24W/4P 1CT/25	7.1 W
61294665	TUV PL-L 24W/4P UNP/50	7.1 W
62878740	TUV PL-L 36W/4P 1CT/25	12.0 W

Order Code	Full Product Name	UV-C Radiation
88827340	TUV PL-L 35W/4P HO 1CT/25	11.0 W
63379840	TUV PL-L 55W/4P HF 1CT/25	17.0 W
71034540	TUV PL-L 60W/4P HO 1CT/25	19.0 W
88829740	TUV PL-L 95W/4P HO 1CT/25	27.0 W

