PHILIPS Lighting



Iconic Iberian foursided luminaire

Villa LED

Villa LED retains the specific proportions and shape of the traditional four-sided luminaires originally used in 19th century Madrid. It allows a remarkable balance between performance and heritage preservation. Now widely used across the Iberian Peninsula, Villa LED is suitable for lighting historical environments and traditional towns and villages. Villa LED also allows municipalities to enjoy the benefits of the latest technologies developed by Philips Lighting, including the CityTouch connected lighting system. Villa LED is also equipped with dedicated light recipe that preserves a dark night sky.

Benefits

- · Iconic luminaire that fits both contemporary and historical environments
- \cdot Easy to maintain
- \cdot long life of the LED engine
- Complete lighting solution with a variety of brackets and columns
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

Features

- \cdot Historical shape
- \cdot Energy-efficient luminaire
- Variety of mounting options: luminaire can be combined with different columns, brackets and multiple-arm brackets

Villa LED

Application

- Main urban roads and streets
- $\boldsymbol{\cdot}$ Side and residential roads and streets
- \cdot City centers and historical areas
- \cdot Cycle and pedestrian paths
- Parkking areas
- Squares, parks and playgrounds

Specifications

Туре	BDP765 (post-top version)	Driver	Built-in (self ballasted LED-module)
	BSP765 (suspended version)		Philips Xitanium Driver
Light source	Integral LED-module	Mains voltage	220-240 V / 50-60 Hz
Power	Up to 79 W depending on configuration	Dimming	LumiStep (LS), DynaDimmer (DDF), LineSwitch (D11), Starsense
Luminous flux	500 - 6800 (warm white), 500 - 7700 (neutral white)		RF Wireless and CityTouch Ready, Photocell, MiniCell 35, 55, 75
	depending on configuration		lux)
Luminaire efficacy	Up to 122 lm/W	Optic	Distribution Medium (DM,DN), Pedestrian Crossing,
Correlated Color	3000 - 4000 K		Symmetrical, Wide and Extra Wide, Louver
Temperature			Tempered flat glass, clear or frosted
Color Rendering Index	80 - 70	Material	Housing: high-pressure aluminum
Lumen maintenance at	up to L95		Glass: thermally hardened, 5 mm thick
median useful life*		Color	Black N9 (MN332L)
100000 h			Other RAL or AKZO Futura colors available on request
Control gear failure rate	e 10%	Maintenance	Light module exchangeable by opening clip of the canopy
at median useful life		Installation	Post Top: 60 and 76 mm spigot, solid and open frog
100000 h			Suspended 3/4 or 1'G
Performance Ambient	+25 ºC		Recommended mounting height: 4 - 6 m
Temperature Tq			Weight: 10.5 kg max
Operating temperature	-25 to +35 °C		Max SCx: 0.26 m ²
range			

Versions



Villa LED BSP765 urban-lighting luminaire, suspended version

Villa LED



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2020, March 16 - data subject to change