



# Actinic BL TL(-K)/TL-D(-K) – optimized for Electronic Fly Killers

## Actinic BL TL(-K)/TL-D(-K)

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

### 优点

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- Design freedom

### 特点


- Emits long-wave UV-A radiation in the 350-400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280-315nm)
- 100% lead-free
- Low mercury content
- Wide power range

### 应用


- Insect traps, Electronic Fly Killers (EFKs)

# Actinic BL TL(-K)/TL-D(-K)


## Versions




## 二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL MINI 15W/09 /10X25CC	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm




Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL 8W/10 1FM/ 10X25CC	16 mm	288.3 mm	295.4 mm	293 mm	302.5 mm

# Actinic BL TL(-K)/TL-D(-K)

## 二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
ACTINIC BL TL-DK - 30W/10 1SL	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

### 照明科技

色彩名稱

Actinic

## 應用

Order Code	Full Product Name	汞 (Hg) 含量 (標稱)
928001001030	Actinic BL TL 8W/10 1FM/10X25CC	4.4 mg
928001200911	Actinic BL TL MINI 15W/09 /10X25CC	-

Order Code	Full Product Name	汞 (Hg) 含量 (標稱)
928019501029	ACTINIC BL TL-DK - 30W/10 1SL	8.0 mg
928024801029	Actinic BL TL-D 15W/10 1SL/25	5.0 mg

## 運作和電氣

Order Code	Full Product Name	燈具電流 (標稱)	電壓 (標稱)	功率 (額定)
928001001030	Actinic BL TL 8W/10 1FM/10X25CC	0.145 A	56 V	7.1 W
928001200911	Actinic BL TL MINI 15W/09 /10X25CC	0.35 A	46 V	13 W

Order Code	Full Product Name	燈具電流 (標稱)	電壓 (標稱)	功率 (額定)
928019501029	ACTINIC BL TL-DK - 30W/10 1SL	0.805 A	45 V	30 W
928024801029	Actinic BL TL-D 15W/10 1SL/25	0.34 A	51 V	15 W

## 基本資訊

Order Code	Full Product Name	接口	壽命 (故障率 50%) (標稱)	可用使用時間 (最大)	可用使用時間 (標稱)	主要應用
928001001030	Actinic BL TL 8W/10 1FM/10X25CC	G5	10000 h	-	5000 h	Reprography (R)
928001200911	Actinic BL TL MINI 15W/09 /10X25CC	G5	-	1000 h	-	-
928019501029	ACTINIC BL TL-DK - 30W/10 1SL	G13	2000 h	-	2000 h	Insect traps
928024801029	Actinic BL TL-D 15W/10 1SL/25	G13	8000 h	-	5000 h	Reprography (R)

## 照明科技

Order Code	Full Product Name	色碼
928001001030	Actinic BL TL 8W/10 1FM/10X25CC	10
928001200911	Actinic BL TL MINI 15W/09 /10X25CC	09

Order Code	Full Product Name	色碼
928019501029	ACTINIC BL TL-DK - 30W/10 1SL	10
928024801029	Actinic BL TL-D 15W/10 1SL/25	10

## 機械和殼體

Order Code	Full Product Name	燈泡形狀
928001001030	Actinic BL TL 8W/10 1FM/10X25CC	T16
928001200911	Actinic BL TL MINI 15W/09 /10X25CC	-

Order Code	Full Product Name	燈泡形狀
928019501029	ACTINIC BL TL-DK - 30W/10 1SL	T26
928024801029	Actinic BL TL-D 15W/10 1SL/25	T26

## Actinic BL TL(-K)/TL-D(-K)

### 紫外線

Order Code	Full Product Name	UV-A 輻射 100Hr (IEC)	UV-B/UV-A (IEC)
928001001030	Actinic BL TL 8W/10 1FM/10X25CC	1.60 W	0.2 %
928001200911	Actinic BL TL MINI 15W/09 / 10X25CC	2 W	-

Order Code	Full Product Name	UV-A 輻射 100Hr (IEC)	UV-B/UV-A (IEC)
928019501029	ACTINIC BL TL-DK - 30W/10 1SL	6.6 W	0.2 %
928024801029	Actinic BL TL-D 15W/10 1SL/25	3.5 W	0.2 %

