



Philips Eletrocutores para insetos BL

Eletrocutores para insetos BL

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Benefícios

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- Design freedom

Características

- Emits long-wave UV-A radiation in the 350–400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280–315nm)
- 100% lead-free
- Low mercury content
- Vasta gama de potências

Aplicação

- Insect traps, Electronic Fly Killers (EFKs)

Avisos e Segurança

- É extremamente improvável que a quebra de uma lâmpada tenha qualquer impacto na sua saúde. Se uma lâmpada quebrar, ventile a divisão durante 30 minutos e remova as partes da lâmpada, de preferência com luvas. Coloque-as num saco de plástico fechado e leve-o para o ecocentro mais próximo para reciclagem. Não utilize o aspirador.

Eletrócutores para insetos BL


Versions




XPPR XUBTL 10 G5

Actinic BL TL-D 15W/10 1SL/25


Desenho dimensional



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-DK 36W/10 1SL/25	28 mm	589,8 mm	596,9 mm	594,5 mm	604 mm




Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL MINI 15W/10 / 10X25CC	16 mm	288,3 mm	295,4 mm	293,0 mm	302,5 mm




Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 1SL/25	28 mm	437,4 mm	444,5 mm	442,1 mm	451,6 mm
Actinic BL TL-D 18W/10 1SL/25	28 mm	589,8 mm	596,9 mm	594,5 mm	604 mm

Eletrocutores para insetos BL

Desenho dimensional



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL 11W/10	16 mm	212,1 mm	219,2 mm	216,8 mm	226,3 mm
Actinic BL TL 6W/10 1FM/10X25CC	16 mm	212,1 mm	219,2 mm	216,8 mm	226,3 mm
Actinic BL TL 8W/10 1FM/10X25CC	16 mm	288,3 mm	295,4 mm	293 mm	302,5 mm



Product	D (max)	A (max)	B	C (max)
Actinic BL TL 40W/10 SLV/25	37,25 mm	1.198,4 mm	1.205,4 mm	1.212,4 mm

Caraterísticas técnicas da luz

Designação da cor	Actinic
Código da cor	10

Informações gerais

Order Code	Full Product Name	Casquilho
26026000	Actinic BL TL 40W/10 1SL/25	G13
95148927	ACTINIC BL 15W/10 FAM/10X25BOX	G5
26039027	Actinic BL TL 6W/10 1FM/10X25CC	G5
95145827	Actinic BL TL 11W/10	G5

Order Code	Full Product Name	Casquilho
26042027	Actinic BL TL 8W/10 1FM/10X25CC	G5
86083200	Actinic BL TL-DK 36W/10 1SL/25	G13
71093240	Actinic BL TL-D 15W/10 1SL/25	G13
26325440	Actinic BL TL-D 18W/10 1SL/25	G13

Funcionamento e caraterísticas elétricas

Order Code	Full Product Name	Corrente de lâmpada (Nom.)	Tensão (Nom.)	Consumo de Energia
26026000	Actinic BL TL 40W/10 1SL/25	0,43 A	101 V	39 W
95148927	ACTINIC BL 15W/10 FAM/10X25BOX	0,40 A	43 V	15 W
26039027	Actinic BL TL 6W/10 1FM/10X25CC	0,16 A	42 V	6 W
95145827	Actinic BL TL 11W/10	0,400 A	34 V	11,5 W
26042027	Actinic BL TL 8W/10 1FM/10X25CC	0,145 A	56 V	7,1 W

Order Code	Full Product Name	Corrente de lâmpada (Nom.)	Tensão (Nom.)	Consumo de Energia
86083200	Actinic BL TL-DK 36W/10 1SL/25	0,865 A	50 V	36 W
71093240	Actinic BL TL-D 15W/10 1SL/25	0,34 A	55 V	15 W
26325440	Actinic BL TL-D 18W/10 1SL/25	0,36 A	59 V	18 W

Eletrócutores para insetos BL

Características mecânicas e compartimento

Order Code	Full Product Name	Formato da lâmpada
26026000	Actinic BL TL 40W/10 1SL/25	T12
95148927	ACTINIC BL 15W/10 FAM/10X25BOX	T16
26039027	Actinic BL TL 6W/10 1FM/10X25CC	T16
95145827	Actinic BL TL 11W/10	T16

Order Code	Full Product Name	Formato da lâmpada
26042027	Actinic BL TL 8W/10 1FM/10X25CC	T16
86083200	Actinic BL TL-DK 36W/10 1SL/25	T26
71093240	Actinic BL TL-D 15W/10 1SL/25	T26
26325440	Actinic BL TL-D 18W/10 1SL/25	T26

Aprovação e aplicação

Order Code	Full Product Name	Conteúdo de mercúrio (Hg) (Nom.)
26026000	Actinic BL TL 40W/10 1SL/25	13,0 mg
95148927	ACTINIC BL 15W/10 FAM/10X25BOX	-
26039027	Actinic BL TL 6W/10 1FM/10X25CC	4,4 mg
95145827	Actinic BL TL 11W/10	4,4 mg

Order Code	Full Product Name	Conteúdo de mercúrio (Hg) (Nom.)
26042027	Actinic BL TL 8W/10 1FM/10X25CC	4,4 mg
86083200	Actinic BL TL-DK 36W/10 1SL/25	8,0 mg
71093240	Actinic BL TL-D 15W/10 1SL/25	5,0 mg
26325440	Actinic BL TL-D 18W/10 1SL/25	5,0 mg

