



Sophisticated yet simple energy-efficient lighting control solutions

Dynalite Multipurpose Controllers

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, driver control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

Benefits

- Controllers support distributed intelligence, i.e. each device has a CPU with presets and can act as a stand-alone control unit
- Some devices have out-of-the-box functionality with re-configuration capability
- Simplified network messages and commissioning process

Application

- Retail and Hospitality, Office and Industry
- Public spaces, Stadiums and multi-purpose Event Centers
- Residential

Dynalite Multipurpose Controllers


Versions



DMC4-CE Multipurpose Modular
Controller



DMR610 GL UL



DSM4 XX



DCM DYNET Communications
Module




DMR316 UL



DSM2 XX Supply module



DDMC802 8 x 2A Multipurpose
Modular Controller




DGBM200 2 Channel Signal
dimmer driver module

Dynalite Multipurpose Controllers

Versions

DGLM105 1 x 5 A Leading edge
dimmer module




DGLM402 4 x 2 A Leading edge
dimmer module




DGRM204 2 x 4 A Relay control
module




DGTM402 4 x 2 A Trailing edge
dimmer module




DGLM202 2 x 2 A Leading edge
dimmer module



DGTM104 1 x 4 A Trailing edge
dimmer module




DGTM202 2 x 2 A Trailing edge
dimmer module







Dynalite Multipurpose Controllers

Dimensional drawing



Dynalite Multipurpose Controllers


Dimensional drawing



Product details



DMC2 Multipurpose Modular
Controller - Front



DMC2 Multipurpose Modular
Controller - exploded view



DMC2 Multipurpose Modular
Controller - open



DMC4-CE Multipurpose Modular
Controller - exploded view

Dynalite Multipurpose Controllers

Product details



DMC4-CE Multipurpose Modular
Controller - front



DMC4 Complete BottomOpen
Front




DMC4 DSM4 DMR316 DMD316
DMR610 DMP603 BottomClose




DMC4 DSM4 DMR316 DMD316
DMR610 DMP603 BottomOpen



DMC4 DSM4 DMR316 DMD316
DMR610 DMP603



DMC4 DSM4 DMR316 DMD316
DMR610 DMP603 Front



DMC4 DSM4 DMR316 DMD316
DMR610 Front



DMC4 DSM4 DMR316 DMD316

Dynalite Multipurpose Controllers

Product details



DMC4 DSM4 DMR316



DMC4 DSM4 DMR316 Front



DMC4 DSM4 Front



DMC4 Empty BottomOpen



DMC4 UL BS



DMC4 UL Empty



DMC4 UL Empty Front



DMD316 FR UL Front

Dynalite Multipurpose Controllers

Product details


DMP603 GL UL Front



DMR316 FR UL Front



DMR610 GL UL Front



DSM4 XX Front



DCM-DYNET Communications module



DMP310_GL_UL Front



DMD316_UL Front




DMR316_UL Front




Dynalite Multipurpose Controllers

Product details

DSM2_XX Supply Module Front




DDMC802 front detail




DGBM200 2 Channel Signal dimmer driver module



DGLM105 1 x 5 A Leading edge dimmer module




DGLM402 4 x 2 A Leading edge dimmer module



DGRM204 2 x 4 A Relay control module




DGTM402 4 x 2 A Trailing edge dimmer module




Dynalite Multipurpose Controllers


Product details



DGLM202 2 x 2 A Leading edge
dimmer module



DGTM104 1 x 4 A Trailing edge
dimmer module



DGTM202 2 x 2 A Trailing edge
dimmer module

