



# Sophisticated yet simple energy-efficient lighting solutions

## Dynalite Relay Controllers

As one of the most popular forms of lighting control, relay and multi-use devices can have the greatest impact in terms of energy management and lighting control. Available in both DIN-rail and wall-box configurations, this Philips Dynalite solution enables a vast range of relay controllers with a variety of circuit numbers and sizes to work individually or as part of a system, thus fulfilling any project requirement. Each device can store over 170 presets, allowing the recall of complex switching logic from simple network messages. As the required preset scenarios are stored within each relay device, the commissioning process and network messages are simplified.

### Benefits

- Enables a range of relay controllers with a variety of circuit numbers and sizes to work individually or as part of a system.
- Simplifies commissioning process and network messages.

### Features

- Available in both DIN-rail and wall-box configurations
- Each device can store over 170 presets

### Application

- Depends on the lighting system in which the controls are used

# Dynalite Relay Controllers

## Versions



DDRC1220FR-GL 12 x 20A Relay Controller



DDRC810DT-GL 8 x 10A Relay Controller



DDRC420FR Relay Controller



DMRC210 Relay Controller





PDUVCC




DDRC-GRMS-E

## Dimensional drawing



# Dynalite Relay Controllers

## Dimensional drawing




## Product details

Front of the DDR810DT-GL 8 x 10A Relay Controller



DDRC420FR Relay Controller



# Dynalite Relay Controllers

## Product details

DMRC210 Relay Controller

