



# Sophisticated yet simple energy-efficient lighting control solutions

## Dynalite Relay Controllers

As one of the most popular forms of lighting control, relay controllers can have the greatest impact in terms of energy management and lighting control. Available in both DIN-rail and wall-box configurations, this Dynalite solution enables a vast range of relay controllers with a variety of circuit numbers and sizes to work individually or as part of a system, thus fulfilling any project requirement. Each device can store over 170 presets, allowing the recall of complex switching logic from simple network messages. As the required preset scenarios are stored within each relay device, the commissioning process and network messages are simplified.

### Benefits

- Enables a range of relay controllers with a variety of circuit numbers and sizes to work individually or as part of a system
- Simplifies commissioning process and network messages

### Application

- Retail and Hospitality, Office and Industry
- Public spaces, Stadiums and multi-purpose Event Centers
- Residential

# Dynalite Relay Controllers

## Versions



DDR810DT-GL



DMRC210 2 x 10A Relay Controller



DMRC210DA-RJ12



DDRC1220FR-GL-V3



DDRC420FR 4 x 20A Relay Controller



DRC-GRMS-UL



DDRC-GRMS

## Product details

Front of the DDR810DT-GL 8 x 10A Relay Controller



DMRC210\_new\_Front



Front of the DMRC210-RJ-DA 2 x 10A Ecoset Relay Controller




Front of the DDRC1220FR-GL 12 x 20A Relay Controller



# Dynalite Relay Controllers

## Product details

DDRC420FR\_new\_Front



DRC-GRMS-UL General Room Relay Controller



DDMC-GRMS Front

