



The most affordable LED specification office lighting

Coreline 2.0

Coreline 2.0 keeps the compact design of the last generation with performance improvement and more variants for different markets. Integrating with ActiLume controller, Coreline 2.0 offers additional energy saving through daylight harvesting and motion sensing.

Benefits

- 60% more energy efficient compared to conventional TL solution
- Additional energy saving up to 50% in combination with controls
- Design continuity towards last generation Coreline for both recessed and suspended types

Features

- System efficiency 100 lm/W
- CRI ≥ 80 , SDCM ≤ 4
- High reliability, 50k hours (L70@25deg)

Application

- Open plan office
- Cell office
- Hospital
- Meeting/Training room

Coreline 2.0

Versions



LED module 1500 lm - 90°



SM100C/RC100C LED25S/LED35S W60L60

