



Energy-efficient lighting for industrial and commercial applications

GreenPerform Hygeia

Customers operating highly hygienic facilities require easy-to-clean, dust-free luminaires that meet all lighting requirements and norms. The New Hygeia with a IP40 and compliance to 1,000 – 100,000 class cleanroom makes it a good choice. The new Hygeia CR308 has a streamlined shape that minimizes dust gathering and disturbed airflow. The cleanroom luminaire uses the latest Philips LED Line platform to provide most value for money. This means extremely low operational cost over the total lifetime of the luminaire, and so an excellent financial return on investment.

Benefits

- Professional design, streamlined shape minimizes dust gathering and disturbed airflow
- Reliable and sustainable lifetime
- Slim and light, 7kgs, easy to install

Features

- Suitable for 1,000 to 100,000 Class cleanroom
- IP40 with smooth surface and easy to clean
- 30% lighter compared to the older version

Application

- Semiconductor and electronics industry
- Pharmaceutical industry
- Healthcare
- Food and beverage industry
- Precision instruments
- Fine mechanics

Versions



CR418B LED40/LED80

Application Conditions

Ambient temperature range	-25 to +35 °C
Suitable for random switching	No

Approval and Application

Mech. impact protection code	IK03
Ingress protection code	IP40

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Voltage	220-240 V
---------------	-----------

General Information

Beam angle of light source	120 °
CE mark	-
Protection class IEC	Safety class I (I)
Optical cover/lens type	PCF
Driver included	Yes
ENEC mark	-
Flammability mark	NO
Gear	-
Glow-wire test	650/30
Light source replaceable	No
Number of gear units	1 unit
Optic type	WB
UL mark	No

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <5
Init. Corr. Colour Temperature	4000 K
Init. Colour Rendering Index	80
Luminous flux tolerance	+/-7.5%

Mechanical and Housing

Colour	White
--------	-------

General Information

Order Code	Full Product Name	Lamp family code
911401591601	CR418B LED80/NW	LED79S
911401591701	CR418B LED40/NW	LED38S
911401592001	CR418C LED40/NW	LED38S
911401592101	CR418C LED80/NW	LED79S

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401591601	CR418B LED80/NW	90 lm/W	7200 lm	80 W
911401591701	CR418B LED40/NW	95 lm/W	3800 lm	40 W

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401592001	CR418C LED40/NW	95 lm/W	3800 lm	40 W
911401592101	CR418C LED80/NW	90 lm/W	7200 lm	80 W

