



Energy-efficient lighting for industrial and commercial applications

GreenPerform Teardrop

Highly hygienic facilities require special easy to clean, dust free luminaires that meet all lighting requirements and norms. Teardrop LED CR385 is suitable for 10 to 1000 Class cleanroom facilities. With the latest LED engine on board, this LED cleanroom luminaire represents the ideal solution, delivering market leading energy performance – far beyond fluorescent solutions – over 50,000 hours of maintenance-free operation. In short, Teardrop LED represents an excellent deal for those looking for pleasant and efficient cleanroom lighting

Benefits

- Safety reinforced, LED light source contains no hazardous matters
- mercury
- Reliable and sustainable lifetime
- Slim and lithier, 2.4kgs, easy to install

Features

- Suitable for 10 to 1000 Class cleanroom
- 93lm/W that provides best value for money
- 2.4 kg only, can be installed by 1 person

Application

- Semiconductor and electronics industry
- Pharmaceutical industry
- Healthcare
- Food and beverage industry
- Precision instruments
- Fine mechanics
- Research and laboratories

