



# Energy-efficient lighting for industrial and commercial applications

## GreenPerform Trunking

With Philips GreenPerform Trunking, industry and supermarket owners have an innovative LED solution that intelligently combines high-performance lighting features with maximised energy savings. This solution is designed to boost productivity and enhance the shopping experience without compromising performance and energy-efficiency. Suitable for a wide range of applications, GreenPerform Trunking is safe, reliable and versatile, the perfect direct replacement for conventional fluorescent trunking.

### Benefits

- A system efficacy of 108lm/w, providing up to 50% energy saving when replacing 2 x 58w fluorescent trunking. Designed for 70% lumen maintenance over 50,000 hours ensuring reliable performance over the product lifetime.
- Specially designed plastic caps improve uniformity along the length leading to a more uniform lighting distribution.
- 3 different beam angles available (Double asymmetric / Wide-beam / Opal) enabling you to choose the most optimum solution for different applications.
- An integrated modular design with 3-phase 5-wire connection ensuring easy and flexible installation, and the possibility of controlling each phase separately.

### Features

- Philips Fortimo LED Line 1R for high efficiency and reliability
- Advanced optics enable precise and energy-saving beam shapes
- Requires much less packaging than fluorescent

## GreenPerform Trunking

### Application

- Supermarkets
- Warehouses
- Production facilities

