



Energy-efficient lighting for industrial and commercial applications

Greenperform Waterproof

GreenPerform LED Waterproof is a high quality luminaire with a high system efficacy that delivers significant energy savings of up to 50% as compared to conventional T8 battens. With a reliable and robust housing structure, this maximizes the endurance and contributes to its long lifetime. It is suitable to be used in both direct and indirect lighting applications. This is due to its flexible optics and choice of symmetric or asymmetric mounting accessories that allows for a variety of different lighting applications.

Benefits

- Good energy savings
- Easy to install for various applications
- Quality lighting with good color uniformity
- Reliable and sustainable lifetime

Features

- System efficacy of more than 90lm/w
- stand alone and continuous version
- IP65 and IK08 ratings
- Lifetime of 50,000 hours with 70% lumen maintained

Application

- Industry – Automotive assembly line, Food and beverage general areas
- Corridors / walkways
- Indoor car parks

Greenperform Waterproof

Versions

