



# Energy-efficient lighting for industrial and commercial applications

## GreenUp Wellglass

GreenUp LED Welglass luminaire is designed to replace traditional WelGlass up to 70W with only 35% of the load for similar illumination. It is a perfect LED solution for outdoor application and industry of harsh condition like power plant, metal, and non hazardous area in chemical and petrochemical industry. Compared to conventional HID WelGlass, it improves reliability, comfort, while reducing energy and maintenance cost dramatically. GreenUp Welglass comes with 2 different mounting, pipe and bracket, and comes with 2 beam, lambertian and batwing.

### Benefits

- Safe and reliable qualities
- High energy saving
- Comfortable light

### Features

- Waterproof, dustproof, impact proof and corrosion proof features, meeting requirements of outdoor application
- System efficacy 100lm/W, 1:1 replacement of HID up to 68% energy saving
- CRI>80, comfortable light with low glare ratings
- 50,000 hrs life with 70% lumen maintained
- Two mounting options: pipe mounting and bracket for wall/ceiling mounting

### Application

- Harsh Industry Application

### Accessories



Ordercode 911401578911



Ordercode 911401579111

