



# Energy-efficient lighting for industrial and commercial applications

## SmartBright Highbay

SmartBright Essential Highbay is a high efficient and reliable LED luminaire, designed for industrial application without humid and dust protection requirements. It enables point to point replacement of HID conventional luminaires, and delivers significant energy savings of up to 64% as compared to HID lamp system. With the innovation of micro prism structure optical plate, it provides an excellent glare control and smooth uniform lighting surface, which effectively improve the comfort of your environment.

### Benefits

- High energy efficient
- Elegant design
- High quality light effect

### Features

- System efficacy of 90lm/W
- Micro prism optical plate: Low glare, good uniformity
- Solid SPCC housing with anti-fire PC cover
- 25,000hrs lifetime @Ta35C
- Suitable for pole and hook mounting

### Application

- Industry
- High ceiling indoor

# SmartBright Highbay

## Versions



BY218P LED180 PSU

