



Reliable savings, lasting brightness

SmartBright LED Batten

SmartBright LED Batten G2 is an affordable replacement for T5 and T8 batten in indirect lighting solutions, such as pelmet or cove lighting. The product comes in a variety of lengths, and an excellent lifetime of 30,000 hours. The product also comes with a plug in the packaging, so is easy for installation.

Benefits

- Slim and narrow end cap designed for cove and shelf lighting
- 5 lengths, 3 colours, flexible, mix and match
- Power cable included for easier purchase

Features

- Patented glass diffuser
- Better heat conduction, no embrittlement, no yellowing
- Longer life time
- 30,000 hours
- Higher energy-efficiency
- 79lm/w
- Lower TCO vs. TL5 batten triggered to replace conventional batten more easily

Application

- Shop Window Cove Shelf Convenience Store Freezer

SmartBright LED Batten

Versions



BN012C LED20

Application Conditions

Ambient temperature range	-20 to +35 °C
Maximum dim level	Not applicable

Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Voltage	220-240 V
---------------	-----------

General Information

CE mark	CE mark
Driver included	Yes
ENEC mark	-
Flammability mark	NO
Light source replaceable	No
Optic type	No
UL mark	-

Initial Performance (IEC Compliant)

Init. Colour Rendering Index	80
Luminous flux tolerance	+/-10%
Initial input power	21 W

Mechanical and Housing

Colour	White
--------	-------

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature
01840199	BN012C LED20/NW L1200	4000 K
01840299	BN012C LED20/CW L1200	6500 K
01841099	BN012C LED20/CW L1200 X25	6500 K

