



# The most cost-effective full window design delivering uniform light

## SmartBright Panel

SmartBright Panel is the most affordable LED panel delivering comfortable light with excellent uniformity

### Benefits

- 60% more energy efficient compared to conventional TL solution
- Comfortable light
- Multiple mountings: recessed, suspended and plaster ceiling options all available

### Features

- System efficiency >90lm/W
- CRI >80, SDCM 5
- 25,000 hrs lifetime (L70@25deg)

### Application

- Meeting room
- Office
- Public area

# SmartBright Panel

## Versions



### RC099V LED26S/LED36S

Application Conditions	
Average ambient temperature	25 °C
Approval and Application	
Mech. impact protection code	IK02
Ingress protection code	IP20
Controls and Dimming	
Dimmable	No
Operating and Electrical	
Input Voltage	220-240 V
General Information	
CE mark	CE mark
Protection class IEC	Safety class I (I)
Optical cover/lens type	TW
Driver included	Yes
ENEC mark	-
Glow-wire test	650/30
Light source replaceable	No
Number of gear units	1 unit
Number of light sources	12
Optic type	60-120
UL mark	No
Initial Performance (IEC Compliant)	
Init. Colour Rendering Index	80
Luminous flux tolerance	+/-10%
Mechanical and Housing	
Colour	White

### Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial input power
911401833999	RC099V LED26S/840 W60L60 GM	4000 K	-
911401834099	RC099V LED26S/865 W60L60 GM	6500 K	-
911401834799	RC099V LED26S/840 W60L60 PCV GM	4000 K	-
911401834899	RC099V LED26S/865 W60L60 PCV GM	6500 K	-
911401835199	RC099V LED36S/840 W60L60 GM	4000 K	34 W
911401836099	RC099V LED36S/865 W60L60 PCV GM	6500 K	34 W

