



# The most cost-effective designed LED troffer to replace conventional luminaire

## SmartBright Troffer

SmartBright 2.0 troffer is the most affordable LED troffer delivering comfortable light with high quality. It offers two lumen options with three dimension types, 600x600, 300x1200 and 600x1200mm

### Benefits

- 50% more energy efficient compared to conventional TL solution
- Delivery high quality light with cost effective luminaire design
- Multiple mounting to cater various applications

### Features

- System efficiency >80lm/W
- CRI >80, SDCM 4
- 25,000 hrs (L70@25deg)

### Application

- Open plan office
- Public indoor area
- Meeting/Training room

# SmartBright Troffer

## Versions



RC098V LED22 W30L120 CPC

