



The most cost-effective designed LED troffer to replace conventional luminaire

SmartBright Troffer

SmartBright 2.0 troffer is the most affordable LED troffer delivering comfortable light with high quality. It offers two lumen options with three dimension types, 600x600, 300x1200 and 600x1200mm

Benefits

- 50% more energy efficient compared to conventional TL solution
- Delivery high quality light with cost effective luminaire design
- Multiple mounting to cater various applications

Features

- System efficiency >80lm/W
- CRI >80, SDCM 4
- 25,000 hrs (L70@25deg)

Application

- Open plan office
- Public indoor area
- Meeting/Training room

SmartBright Troffer

Versions



RC098V LED22 W60L60 PCV

