



The most comfortable LED office lighting

SmartPanel 2.0

SmartPanel 2.0 keeps the design continuity of SmartPanel 1.1 with performance improvement and more cost effective structure. It offers two lumen options with higher system efficacy, 80lm/W @ 4000K. Reliability is improved by the extending of lifetime from 30K hours to 50K hours L70 Ta 25°C

Benefits

- 50% more energy efficient compared to conventional T5 solution
- Slim design preferred by lighting designer and specifier
- Deliver uniform and soft light with sufficient lumen output

Features

- System efficiency 80lm/W
- CRI ≥ 80 , SDCM ≤ 5
- High reliability, 50k hours (L70@25deg)

Application

- Open plan office
- Cell office
- Hospital
- Meeting/Training room

SmartPanel 2.0

Versions



RC160V LED25S/LED34S W60L60

