



# The most comfortable LED office lighting

## SmartPanel 2.0

SmartPanel 2.0 keeps the design continuity of SmartPanel 1.1 with performance improvement and more cost effective structure. It offers two lumen options with higher system efficacy, 80lm/W @ 4000K. Reliability is improved by the extending of lifetime from 30K hours to 50K hours L70 Ta 25°C

### Benefits

- 50% more energy efficient compared to conventional T5 solution
- Slim design preferred by lighting designer and specifier
- Deliver uniform and soft light with sufficient lumen output

### Features

- System efficiency 80lm/W
- CRI >80, SDCM <=5
- High reliability, 50k hours (L70@25deg)

### Application

- Open plan office
- Cell office
- Hospital
- Meeting/Training room

## SmartPanel 2.0

### Versions



RC160V LED25S/LED34S W60L60

