



Best Area Lighting Luminaire within Your Budget

Tango G2 LED

Tango G2 LED is a general purpose LED flood lighting luminaire for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

Benefits

- Energy saving: more than 50% of energy saving when compared to conventional floodlight
- Free from lamp replacement
- Low maintenance cost: IP65 housing ensures low maintenance with no need for internal cleaning, resulting in a lower total cost of ownership

Features



- Optical beam choice of symmetric and asymmetric fulfils majority needs of lighting application
- Painted non-corrosive die-cast aluminum housing and steel bracket
- Universal "U" shape mounting bracket

Application

- Area lighting
- Industry area
- Façade

Tango G2 LED

Versions



BVP283 220-240V

BVP282 220-240 V

Approval and Application	
Mech. impact protection code	IK07
Controls and Dimming	
Dimmable	No
General Information	
CE mark	CE mark
Driver included	Yes
Mechanical and Housing	
Colour	Aluminium and Grey

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401604403	BVP283 LED340/CW 335W 220-240V AWBE	-
911401604503	BVP283 LED320/CW 315W 220-240V AWBE	-
911401604603	BVP283 LED280/CW 280W 220-240V AWBE	-
911401604703	BVP283 LED245/CW 245W 220-240V AWBE	-
911401604803	BVP283 LED311/WW 335W 220-240V AWBE	-
911401604903	BVP283 LED210/CW 210W 220-240V AWBE	-
911401605003	BVP283 LED293/WW 315W 220-240V AWBE	-
911401605103	BVP283 LED256/WW 280W 220-240V AWBE	-
911401605203	BVP283 LED224/WW 245W 220-240V AWBE	-
911401605303	BVP283 LED192/WW 210W 220-240V AWBE	-
911401605403	BVP283 LED340/NW 335W 220-240V AWBE	-
911401605503	BVP283 LED320/NW 315W 220-240V AWBE	-
911401605603	BVP283 LED280/NW 280W 220-240V AWBE	-
911401605703	BVP283 LED245/NW 245W 220-240V AWBE	-
911401605803	BVP283 LED210/NW 210W 220-240V AWBE	-
911401667002	BVP283 LED311/WW 335W 220-240V NB	-
911401667102	BVP283 LED293/WW 315W 220-240V NB	-
911401667202	BVP283 LED256/WW 280W 220-240V NB	-
911401667302	BVP283 LED224/WW 245W 220-240V NB	-
911401667402	BVP283 LED192/WW 210W 220-240V NB	-

Order Code	Full Product Name	Maximum dim level
911401667502	BVP283 LED340/CW 335W 220-240V NB	-
911401667602	BVP283 LED320/CW 315W 220-240V NB	-
911401667702	BVP283 LED280/CW 280W 220-240V NB	-
911401667802	BVP283 LED245/CW 245W 220-240V NB	-
911401667902	BVP283 LED210/CW 210W 220-240V NB	-
911401668002	BVP283 LED340/NW 335W 220-240V NB	-
911401668102	BVP283 LED320/NW 315W 220-240V NB	-
911401668202	BVP283 LED280/NW 280W 220-240V NB	-
911401668302	BVP283 LED245/NW 245W 220-240V NB	-
911401668402	BVP283 LED210/NW 210W 220-240V NB	-
911401668502	BVP283 LED311/WW 335W 220-240V SWB	-
911401668602	BVP283 LED307/WW 315W 220-240V SWB	-
911401668702	BVP283 LED224/WW 245W 220-240V SWB	-
911401668802	BVP283 LED256/WW 280W 220-240V SWB	-
911401668902	BVP283 LED192/WW 210W 220-240V SWB	-
911401669002	BVP283 LED340/CW 335W 220-240V SWB	-
911401669102	BVP283 LED320/CW 315W 220-240V SWB	-
911401669202	BVP283 LED280/CW 280W 220-240V SWB	-
911401669302	BVP283 LED245/CW 245W 220-240V SWB	-
911401669402	BVP283 LED210/CW 210W 220-240V SWB	-

Tango G2 LED

Order Code	Full Product Name	Maximum dim level
911401669502	BVP283 LED340/NW 335W 220-240V SWB	-
911401669602	BVP283 LED320/NW 315W 220-240V SWB	Not applicable
911401669702	BVP283 LED280/NW 280W 220-240V SWB	Not applicable
911401669802	BVP283 LED245/NW 245W 220-240V SWB	Not applicable
911401669902	BVP283 LED210/NW 210W 220-240V SWB	-
911401670002	BVP283 LED311/WW 335W 220-240V AWB	-
911401670102	BVP283 LED293/WW 315W 220-240V AWB	-
911401670202	BVP283 LED256/WW 280W 220-240V AWB	-
911401670302	BVP283 LED224/WW 245W 220-240V AWB	-
911401670402	BVP283 LED192/WW 210W 220-240V AWB	-
911401670502	BVP283 LED340/CW 335W 220-240V AWB	-
911401670602	BVP283 LED320/CW 315W 220-240V AWB	-
911401670702	BVP283 LED280/CW 280W 220-240V AWB	-
911401670802	BVP283 LED245/CW 245W 220-240V AWB	-
911401670902	BVP283 LED210/CW 210W 220-240V AWB	-
911401671002	BVP283 LED340/NW 335W 220-240V AWB	-
911401671102	BVP283 LED320/NW 315W 220-240V AWB	Not applicable
911401671202	BVP283 LED280/NW 280W 220-240V AWB	Not applicable
911401671302	BVP283 LED245/NW 245W 220-240V AWB	Not applicable
911401671402	BVP283 LED210/NW 210W 220-240V AWB	-
911401689102	BVP283 LED327/WW 350W 220-240V NB	-
911401689202	BVP283 LED355/NW 350W 220-240V AWB	Not applicable
911401689302	BVP283 LED355/CW 350W 220-240V AWB	-
911401689402	BVP283 LED327/WW 350W 220-240V AWB	-
911401689502	BVP283 LED355/NW 350W 220-240V SWB	Not applicable
911401689602	BVP283 LED355/CW 350W 220-240V SWB	-
911401689702	BVP283 LED327/WW 350W 220-240V SWB	-
911401689802	BVP283 LED355/NW 350W 220-240V NB	-
911401689902	BVP283 LED355/CW 350W 220-240V NB	-
911401697402	BVP283 LED355/NW 350W 220-240V AWBE	-
911401697502	BVP283 LED327/WW 350W 220-240V AWBE	-
911401697602	BVP283 LED355/CW 350W 220-240V AWBE	-
911401660504	BVP281 LED101/CW 80W 220-240V SWB	-
911401660704	BVP281 LED101/CW 80W 220-240V AMB	-
911401660804	BVP281 LED50/CW 40W 220-240V SWB	-
911401660904	BVP281 LED101/WW 80W 220-240V SMB	-
911401661004	BVP281 LED50/NW 40W 220-240V SWB	-

Order Code	Full Product Name	Maximum dim level
911401661104	BVP281 LED101/WW 80W 220-240V AMB	-
911401661204	BVP281 LED50/NW 40W 220-240V SMB	-
911401661304	BVP281 LED50/NW 40W 220-240V AMB	-
911401661404	BVP281 LED50/CW 40W 220-240V SMB	-
911401661604	BVP281 LED50/CW 40W 220-240V AMB	-
911401661704	BVP281 LED50/WW 40W 220-240V SMB	-
911401661804	BVP281 LED101/CW 80W 220-240V SMB	-
911401661904	BVP281 LED101/NW 80W 220-240V AMB	-
911401662004	BVP281 LED151/CW 120W 220-240V AMB	-
911401662104	BVP281 LED151/WW 120W 220-240V AMB	-
911401662204	BVP281 LED151/NW 120W 220-240V AMB	-
911401662304	BVP281 LED101/NW 80W 220-240V SWB	-
911401662404	BVP281 LED151/CW 120W 220-240V SMB	-
911401662504	BVP281 LED151/WW 120W 220-240V SMB	-
911401662604	BVP281 LED151/CW 120W 220-240V SWB	-
911401662704	BVP281 LED101/NW 80W 220-240V SMB	-
911401662804	BVP281 LED151/NW 120W 220-240V SWB	-
911401662904	BVP281 LED151/NW 120W 220-240V SMB	-
911401663004	BVP282 LED202/WW 160W 220-240V AMB	-
911401663104	BVP282 LED202/WW 160W 220-240V SWB	-
911401663204	BVP282 LED202/NW 160W 220-240V SWB	-
911401663304	BVP282 LED202/NW 160W 220-240V AMB	-
911401663404	BVP282 LED202/CW 160W 220-240V SMB	-
911401663504	BVP282 LED202/CW 160W 220-240V AMB	-
911401663604	BVP282 LED202/NW 160W 220-240V SMB	-
911401663704	BVP282 LED202/CW 160W 220-240V SWB	-
911401663804	BVP282 LED252/WW 200W 220-240V SMB	-
911401663904	BVP282 LED252/CW 200W 220-240V SWB	-
911401664004	BVP282 LED252/WW 200W 220-240V SWB	-
911401664104	BVP282 LED252/NW 200W 220-240V AMB	-
911401664204	BVP282 LED252/WW 200W 220-240V AMB	-
911401664304	BVP282 LED252/CW 200W 220-240V SMB	-
911401664404	BVP282 LED252/CW 200W 220-240V AMB	-
911401664504	BVP282 LED252/NW 200W 220-240V SWB	-
911401664604	BVP282 LED252/NW 200W 220-240V SMB	-
911401664704	BVP282 LED202/WW 160W 220-240V SMB	-

Approval and Application

Order Code	Full Product Name	Surge Protection (Common/Differential)
911401604403	BVP283 LED340/CW 335W 220-240V AWBE	-
911401604503	BVP283 LED320/CW 315W 220-240V AWBE	-
911401604603	BVP283 LED280/CW 280W 220-240V AWBE	-
911401604703	BVP283 LED245/CW 245W 220-240V AWBE	-
911401604803	BVP283 LED311/WW 335W 220-240V AWBE	-

Order Code	Full Product Name	Surge Protection (Common/Differential)
911401604903	BVP283 LED210/CW 210W 220-240V AWBE	-
911401605003	BVP283 LED293/WW 315W 220-240V AWBE	-
911401605103	BVP283 LED256/WW 280W 220-240V AWBE	-
911401605203	BVP283 LED224/WW 245W 220-240V AWBE	-
911401605303	BVP283 LED192/WW 210W 220-240V AWBE	-

Tango G2 LED

Order Code	Full Product Name	Surge Protection (Common/Differential)
911401605403	BVP283 LED340/NW 335W 220-240V AWBE	Surge protection level until 10 kV
911401605503	BVP283 LED320/NW 315W 220-240V AWBE	Surge protection level until 10 kV
911401605603	BVP283 LED280/NW 280W 220-240V AWBE	Surge protection level until 10 kV
911401605703	BVP283 LED245/NW 245W 220-240V AWBE	Surge protection level until 10 kV
911401605803	BVP283 LED210/NW 210W 220-240V AWBE	Surge protection level until 10 kV
911401667002	BVP283 LED311/WW 335W 220-240V NB	-
911401667102	BVP283 LED293/WW 315W 220-240V NB	-
911401667202	BVP283 LED256/WW 280W 220-240V NB	-
911401667302	BVP283 LED224/WW 245W 220-240V NB	-
911401667402	BVP283 LED192/WW 210W 220-240V NB	-
911401667502	BVP283 LED340/CW 335W 220-240V NB	-
911401667602	BVP283 LED320/CW 315W 220-240V NB	-
911401667702	BVP283 LED280/CW 280W 220-240V NB	-
911401667802	BVP283 LED245/CW 245W 220-240V NB	-
911401667902	BVP283 LED210/CW 210W 220-240V NB	-
911401668002	BVP283 LED340/NW 335W 220-240V NB	-
911401668102	BVP283 LED320/NW 315W 220-240V NB	-
911401668202	BVP283 LED280/NW 280W 220-240V NB	-
911401668302	BVP283 LED245/NW 245W 220-240V NB	-
911401668402	BVP283 LED210/NW 210W 220-240V NB	Surge protection level until 10 kV
911401668502	BVP283 LED311/WW 335W 220-240V SWB	-
911401668602	BVP283 LED307/WW 315W 220-240V SWB	-
911401668702	BVP283 LED224/WW 245W 220-240V SWB	-
911401668802	BVP283 LED256/WW 280W 220-240V SWB	-
911401668902	BVP283 LED192/WW 210W 220-240V SWB	-
911401669002	BVP283 LED340/CW 335W 220-240V SWB	-
911401669102	BVP283 LED320/CW 315W 220-240V SWB	-
911401669202	BVP283 LED280/CW 280W 220-240V SWB	-
911401669302	BVP283 LED245/CW 245W 220-240V SWB	-

Order Code	Full Product Name	Surge Protection (Common/Differential)
911401669402	BVP283 LED210/CW 210W 220-240V SWB	-
911401669502	BVP283 LED340/NW 335W 220-240V SWB	-
911401669602	BVP283 LED320/NW 315W 220-240V SWB	Surge protection level until 10 kV
911401669702	BVP283 LED280/NW 280W 220-240V SWB	Surge protection level until 10 kV
911401669802	BVP283 LED245/NW 245W 220-240V SWB	Surge protection level until 10 kV
911401669902	BVP283 LED210/NW 210W 220-240V SWB	Surge protection level until 10 kV
911401670002	BVP283 LED311/WW 335W 220-240V AWB	-
911401670102	BVP283 LED293/WW 315W 220-240V AWB	-
911401670202	BVP283 LED256/WW 280W 220-240V AWB	-
911401670302	BVP283 LED224/WW 245W 220-240V AWB	-
911401670402	BVP283 LED192/WW 210W 220-240V AWB	-
911401670502	BVP283 LED340/CW 335W 220-240V AWB	-
911401670602	BVP283 LED320/CW 315W 220-240V AWB	-
911401670702	BVP283 LED280/CW 280W 220-240V AWB	-
911401670802	BVP283 LED245/CW 245W 220-240V AWB	-
911401670902	BVP283 LED210/CW 210W 220-240V AWB	Surge protection level until 10 kV
911401671002	BVP283 LED340/NW 335W 220-240V AWB	-
911401671102	BVP283 LED320/NW 315W 220-240V AWB	Surge protection level until 10 kV
911401671202	BVP283 LED280/NW 280W 220-240V AWB	Surge protection level until 10 kV
911401671302	BVP283 LED245/NW 245W 220-240V AWB	Surge protection level until 10 kV
911401671402	BVP283 LED210/NW 210W 220-240V AWB	Surge protection level until 10 kV
911401689102	BVP283 LED327/WW 350W 220-240V NB	-
911401689202	BVP283 LED355/NW 350W 220-240V AWB	Surge protection level until 10 kV
911401689302	BVP283 LED355/CW 350W 220-240V AWB	-
911401689402	BVP283 LED327/WW 350W 220-240V AWB	-

Tango G2 LED

Order Code	Full Product Name	Surge Protection (Common/Differential)
911401689502	BVP283 LED355/NW 350W 220-240V SWB	Surge protection level until 10 kV
911401689602	BVP283 LED355/CW 350W 220-240V SWB	-
911401689702	BVP283 LED327/WW 350W 220-240V SWB	-
911401689802	BVP283 LED355/NW 350W 220-240V NB	-
911401689902	BVP283 LED355/CW 350W 220-240V NB	Surge protection level until 10 kV
911401697402	BVP283 LED355/NW 350W 220-240V AWBE	-
911401697502	BVP283 LED327/WW 350W 220-240V AWBE	-
911401697602	BVP283 LED355/CW 350W 220-240V AWBE	-
911401660504	BVP281 LED101/CW 80W 220-240V SWB	Surge protection level until 10 kV
911401660704	BVP281 LED101/CW 80W 220-240V AMB	Surge protection level until 10 kV
911401660804	BVP281 LED50/CW 40W 220-240V SWB	Surge protection level until 10 kV
911401660904	BVP281 LED101/WW 80W 220-240V SMB	Surge protection level until 10 kV
911401661004	BVP281 LED50/NW 40W 220-240V SWB	Surge protection level until 10 kV
911401661104	BVP281 LED101/WW 80W 220-240V AMB	Surge protection level until 10 kV
911401661204	BVP281 LED50/NW 40W 220-240V SMB	Surge protection level until 10 kV
911401661304	BVP281 LED50/NW 40W 220-240V AMB	Surge protection level until 10 kV
911401661404	BVP281 LED50/CW 40W 220-240V SMB	Surge protection level until 10 kV
911401661604	BVP281 LED50/CW 40W 220-240V AMB	Surge protection level until 10 kV
911401661704	BVP281 LED50/WW 40W 220-240V SMB	Surge protection level until 10 kV
911401661804	BVP281 LED101/CW 80W 220-240V SMB	Surge protection level until 10 kV
911401661904	BVP281 LED101/NW 80W 220-240V AMB	Surge protection level until 10 kV
911401662004	BVP281 LED151/CW 120W 220-240V AMB	Surge protection level until 10 kV
911401662104	BVP281 LED151/WW 120W 220-240V AMB	Surge protection level until 10 kV
911401662204	BVP281 LED151/NW 120W 220-240V AMB	Surge protection level until 10 kV
911401662304	BVP281 LED101/NW 80W 220-240V SWB	Surge protection level until 10 kV

Order Code	Full Product Name	Surge Protection (Common/Differential)
911401662404	BVP281 LED151/CW 120W 220-240V SMB	Surge protection level until 10 kV
911401662504	BVP281 LED151/WW 120W 220-240V SMB	Surge protection level until 10 kV
911401662604	BVP281 LED151/CW 120W 220-240V SWB	Surge protection level until 10 kV
911401662704	BVP281 LED101/NW 80W 220-240V SMB	Surge protection level until 10 kV
911401662804	BVP281 LED151/NW 120W 220-240V SWB	Surge protection level until 10 kV
911401662904	BVP281 LED151/NW 120W 220-240V SMB	Surge protection level until 10 kV
911401663004	BVP282 LED202/WW 160W 220-240V AMB	Surge protection level until 10 kV
911401663104	BVP282 LED202/WW 160W 220-240V SWB	Surge protection level until 10 kV
911401663204	BVP282 LED202/NW 160W 220-240V SWB	Surge protection level until 10 kV
911401663304	BVP282 LED202/NW 160W 220-240V AMB	Surge protection level until 10 kV
911401663404	BVP282 LED202/CW 160W 220-240V SMB	Surge protection level until 10 kV
911401663504	BVP282 LED202/CW 160W 220-240V AMB	Surge protection level until 10 kV
911401663604	BVP282 LED202/NW 160W 220-240V SMB	Surge protection level until 10 kV
911401663704	BVP282 LED202/CW 160W 220-240V SWB	Surge protection level until 10 kV
911401663804	BVP282 LED252/WW 200W 220-240V SMB	Surge protection level until 10 kV
911401663904	BVP282 LED252/CW 200W 220-240V SWB	Surge protection level until 10 kV
911401664004	BVP282 LED252/WW 200W 220-240V SWB	Surge protection level until 10 kV
911401664104	BVP282 LED252/NW 200W 220-240V AMB	Surge protection level until 10 kV
911401664204	BVP282 LED252/WW 200W 220-240V AMB	Surge protection level until 10 kV
911401664304	BVP282 LED252/CW 200W 220-240V SMB	Surge protection level until 10 kV
911401664404	BVP282 LED252/CW 200W 220-240V AMB	Surge protection level until 10 kV
911401664504	BVP282 LED252/NW 200W 220-240V SWB	Surge protection level until 10 kV
911401664604	BVP282 LED252/NW 200W 220-240V SMB	Surge protection level until 10 kV
911401664704	BVP282 LED202/WW 160W 220-240V SMB	Surge protection level until 10 kV

General Information (1/2)

Tango G2 LED

Order Code	Full Product Name	Luminaire light		Optical	Flammability	Glow-wire	Lamp family	Light source
		beam spread	Light source colour	cover/lens				
911401604403	BVP283 LED340/CW 335W 220-240V AWBE	-	740 neutral white	G	-	-	-	-
911401604503	BVP283 LED320/CW 315W 220-240V AWBE	-	740 neutral white	G	-	-	-	-
911401604603	BVP283 LED280/CW 280W 220-240V AWBE	-	740 neutral white	G	-	-	-	-
911401604703	BVP283 LED245/CW 245W 220-240V AWBE	-	740 neutral white	G	-	-	-	-
911401604803	BVP283 LED311/WW 335W 220-240V AWBE	-	740 neutral white	G	-	-	-	-
911401604903	BVP283 LED210/CW 210W 220-240V AWBE	-	730 warm white	G	-	-	-	-
911401605003	BVP283 LED293/WW 315W 220-240V AWBE	-	740 neutral white	G	-	-	-	-
911401605103	BVP283 LED256/WW 280W 220-240V AWBE	-	740 neutral white	G	-	-	-	-
911401605203	BVP283 LED224/WW 245W 220-240V AWBE	-	740 neutral white	G	-	-	-	-
911401605303	BVP283 LED192/WW 210W 220-240V AWBE	-	730 warm white	G	-	-	-	-
911401605403	BVP283 LED340/NW 335W 220-240V AWBE	16° x 80°	740 neutral white	G	-	-	-	Yes
911401605503	BVP283 LED320/NW 315W 220-240V AWBE	16° x 80°	740 neutral white	G	-	-	-	Yes
911401605603	BVP283 LED280/NW 280W 220-240V AWBE	16° x 80°	740 neutral white	G	-	-	-	Yes
911401605703	BVP283 LED245/NW 245W 220-240V AWBE	16° x 80°	740 neutral white	G	-	-	-	Yes
911401605803	BVP283 LED210/NW 210W 220-240V AWBE	16° x 80°	740 neutral white	G	-	-	-	Yes
911401667002	BVP283 LED311/WW 335W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401667102	BVP283 LED293/WW 315W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401667202	BVP283 LED256/WW 280W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401667302	BVP283 LED224/WW 245W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401667402	BVP283 LED192/WW 210W 220-240V NB	-	730 warm white	G	-	-	-	-
911401667502	BVP283 LED340/CW 335W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401667602	BVP283 LED320/CW 315W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401667702	BVP283 LED280/CW 280W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401667802	BVP283 LED245/CW 245W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401667902	BVP283 LED210/CW 210W 220-240V NB	-	730 warm white	G	-	-	-	-
911401668002	BVP283 LED340/NW 335W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401668102	BVP283 LED320/NW 315W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401668202	BVP283 LED280/NW 280W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401668302	BVP283 LED245/NW 245W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401668402	BVP283 LED210/NW 210W 220-240V NB	20° x 20°	740 neutral white	G	-	-	-	Yes
911401668502	BVP283 LED311/WW 335W 220-240V SWB	-	740 neutral white	G	-	-	-	-
911401668602	BVP283 LED307/WW 315W 220-240V SWB	-	740 neutral white	G	-	-	-	-

Tango G2 LED

Order Code	Full Product Name	Luminaire light		Optical	Flammability	Glow-wire	Lamp family	Light source
		beam spread	Light source colour	cover/lens				
911401668702	BVP283 LED224/WW 245W 220-240V SWB	-	740 neutral white	G	-	-	-	-
911401668802	BVP283 LED256/WW 280W 220-240V SWB	-	740 neutral white	G	-	-	-	-
911401668902	BVP283 LED192/WW 210W 220-240V SWB	-	730 warm white	G	-	-	-	-
911401669002	BVP283 LED340/CW 335W 220-240V SWB	-	740 neutral white	G	-	-	-	-
911401669102	BVP283 LED320/CW 315W 220-240V SWB	-	740 neutral white	G	-	-	-	-
911401669202	BVP283 LED280/CW 280W 220-240V SWB	-	740 neutral white	G	-	-	-	-
911401669302	BVP283 LED245/CW 245W 220-240V SWB	-	740 neutral white	G	-	-	-	-
911401669402	BVP283 LED210/CW 210W 220-240V SWB	-	730 warm white	G	-	-	-	-
911401669502	BVP283 LED340/NW 335W 220-240V SWB	-	740 neutral white	G	-	-	-	-
911401669602	BVP283 LED320/NW 315W 220-240V SWB	30° x 80°	740 neutral white	G	-	-	-	Yes
911401669702	BVP283 LED280/NW 280W 220-240V SWB	30° x 80°	740 neutral white	G	-	-	-	Yes
911401669802	BVP283 LED245/NW 245W 220-240V SWB	30° x 80°	740 neutral white	G	-	-	-	Yes
911401669902	BVP283 LED210/NW 210W 220-240V SWB	30° x 80°	740 neutral white	G	-	-	-	Yes
911401670002	BVP283 LED311/WW 335W 220-240V AWB	-	740 neutral white	G	-	-	-	-
911401670102	BVP283 LED293/WW 315W 220-240V AWB	-	740 neutral white	G	-	-	-	-
911401670202	BVP283 LED256/WW 280W 220-240V AWB	-	740 neutral white	G	-	-	-	-
911401670302	BVP283 LED224/WW 245W 220-240V AWB	-	740 neutral white	G	-	-	-	-
911401670402	BVP283 LED192/WW 210W 220-240V AWB	-	730 warm white	G	-	-	-	-
911401670502	BVP283 LED340/CW 335W 220-240V AWB	-	740 neutral white	G	-	-	-	-
911401670602	BVP283 LED320/CW 315W 220-240V AWB	-	740 neutral white	G	-	-	-	-
911401670702	BVP283 LED280/CW 280W 220-240V AWB	-	740 neutral white	G	-	-	-	-
911401670802	BVP283 LED245/CW 245W 220-240V AWB	-	740 neutral white	G	-	-	-	-
911401670902	BVP283 LED210/CW 210W 220-240V AWB	40° x 95°	730 warm white	G	-	-	-	Yes
911401671002	BVP283 LED340/NW 335W 220-240V AWB	-	740 neutral white	G	-	-	-	-
911401671102	BVP283 LED320/NW 315W 220-240V AWB	40° x 95°	740 neutral white	G	-	-	-	Yes

Tango G2 LED

Order Code	Full Product Name	Luminaire light		Optical	Flammability	Glow-wire	Lamp family	Light source
		beam spread	Light source colour	cover/lens				
				type	mark	test	code	replaceable
911401671202	BVP283 LED280/NW 280W 220-240V AWB	40° x 95°	740 neutral white	G	-	-	-	Yes
911401671302	BVP283 LED245/NW 245W 220-240V AWB	40° x 95°	740 neutral white	G	-	-	-	Yes
911401671402	BVP283 LED210/NW 210W 220-240V AWB	40° x 95°	740 neutral white	G	-	-	-	Yes
911401689102	BVP283 LED327/WW 350W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401689202	BVP283 LED355/NW 350W 220-240V AWB	40° x 95°	740 neutral white	G	-	-	-	Yes
911401689302	BVP283 LED355/CW 350W 220-240V AWB	-	740 neutral white	G	-	-	-	-
911401689402	BVP283 LED327/WW 350W 220-240V AWB	-	740 neutral white	G	-	-	-	-
911401689502	BVP283 LED355/NW 350W 220-240V SWB	30° x 80°	740 neutral white	G	-	-	-	Yes
911401689602	BVP283 LED355/CW 350W 220-240V SWB	-	740 neutral white	G	-	-	-	-
911401689702	BVP283 LED327/WW 350W 220-240V SWB	-	740 neutral white	G	-	-	-	-
911401689802	BVP283 LED355/NW 350W 220-240V NB	-	740 neutral white	G	-	-	-	-
911401689902	BVP283 LED355/CW 350W 220-240V NB	-	740 neutral white	G	NO	NO	LED35S	No
911401697402	BVP283 LED355/NW 350W 220-240V AWBE	-	740 neutral white	G	-	-	-	-
911401697502	BVP283 LED327/WW 350W 220-240V AWBE	-	740 neutral white	G	-	-	-	-
911401697602	BVP283 LED355/CW 350W 220-240V AWBE	-	740 neutral white	G	-	-	-	-
911401660504	BVP281 LED101/CW 80W 220-240V SWB	100°	Cool white	PC-MLO	NO	-	-	Yes
911401660704	BVP281 LED101/CW 80W 220-240V AMB	100° x 30°	Cool white	PC-MLO	NO	-	-	Yes
911401660804	BVP281 LED50/CW 40W 220-240V SWB	100°	Cool white	PC-MLO	NO	-	-	Yes
911401660904	BVP281 LED101/WW 80W 220-240V SMB	54°	Warm white	PC-MLO	NO	-	-	Yes
911401661004	BVP281 LED50/NW 40W 220-240V SWB	100°	Neutral white	PC-MLO	NO	-	-	Yes
911401661104	BVP281 LED101/WW 80W 220-240V AMB	100° x 30°	Warm white	PC-MLO	NO	-	-	Yes
911401661204	BVP281 LED50/NW 40W 220-240V SMB	54°	Neutral white	PC-MLO	NO	-	-	Yes
911401661304	BVP281 LED50/NW 40W 220-240V AMB	100° x 30°	Neutral white	PC-MLO	NO	-	-	Yes
911401661404	BVP281 LED50/CW 40W 220-240V SMB	54°	Cool white	PC-MLO	NO	-	-	Yes
911401661604	BVP281 LED50/CW 40W 220-240V AMB	100° x 30°	Cool white	PC-MLO	NO	-	-	Yes
911401661704	BVP281 LED50/WW 40W 220-240V SMB	54°	Warm white	PC-MLO	NO	-	-	Yes
911401661804	BVP281 LED101/CW 80W 220-240V SMB	54°	Cool white	PC-MLO	NO	-	-	Yes
911401661904	BVP281 LED101/NW 80W 220-240V AMB	100° x 30°	Neutral white	PC-MLO	NO	-	-	Yes
911401662004	BVP281 LED151/CW 120W 220-240V AMB	100° x 30°	Cool white	PC-MLO	NO	-	-	Yes
911401662104	BVP281 LED151/WW 120W 220-240V AMB	100° x 30°	Warm white	PC-MLO	NO	-	-	Yes
911401662204	BVP281 LED151/NW 120W 220-240V AMB	100° x 30°	Neutral white	PC-MLO	NO	-	-	Yes
911401662304	BVP281 LED101/NW 80W 220-240V SWB	100°	Neutral white	PC-MLO	NO	-	-	Yes
911401662404	BVP281 LED151/CW 120W 220-240V SMB	54°	Cool white	PC-MLO	NO	-	-	Yes
911401662504	BVP281 LED151/WW 120W 220-240V SMB	54°	Warm white	PC-MLO	NO	-	-	Yes
911401662604	BVP281 LED151/CW 120W 220-240V SWB	100°	Cool white	PC-MLO	NO	-	-	Yes
911401662704	BVP281 LED101/NW 80W 220-240V SMB	54°	Neutral white	PC-MLO	NO	-	-	Yes
911401662804	BVP281 LED151/NW 120W 220-240V SWB	100°	Neutral white	PC-MLO	NO	-	-	Yes
911401662904	BVP281 LED151/NW 120W 220-240V SMB	54°	Neutral white	PC-MLO	NO	-	-	Yes

Tango G2 LED

Order Code	Full Product Name	Luminaire light		Optical	Flammability	Glow-wire	Lamp family	Light source
		beam spread	Light source colour	cover/lens type				
911401663004	BVP282 LED202/WW 160W 220-240V AMB	100° x 30°	Warm white	PC-MLO	NO	-	-	Yes
911401663104	BVP282 LED202/WW 160W 220-240V SWB	100°	Warm white	PC-MLO	NO	-	-	Yes
911401663204	BVP282 LED202/NW 160W 220-240V SWB	100°	Neutral white	PC-MLO	NO	-	-	Yes
911401663304	BVP282 LED202/NW 160W 220-240V AMB	100° x 30°	Neutral white	PC-MLO	NO	-	-	Yes
911401663404	BVP282 LED202/CW 160W 220-240V SMB	54°	Cool white	PC-MLO	NO	-	-	Yes
911401663504	BVP282 LED202/CW 160W 220-240V AMB	100° x 30°	Cool white	PC-MLO	NO	-	-	Yes
911401663604	BVP282 LED202/NW 160W 220-240V SMB	54°	Neutral white	PC-MLO	NO	-	-	Yes
911401663704	BVP282 LED202/CW 160W 220-240V SWB	100°	Cool white	PC-MLO	NO	-	-	Yes
911401663804	BVP282 LED252/WW 200W 220-240V SMB	54°	Warm white	PC-MLO	NO	-	-	Yes
911401663904	BVP282 LED252/CW 200W 220-240V SWB	100°	Cool white	PC-MLO	NO	-	-	Yes
911401664004	BVP282 LED252/WW 200W 220-240V SWB	100°	Warm white	PC-MLO	NO	-	-	Yes
911401664104	BVP282 LED252/NW 200W 220-240V AMB	100° x 30°	Neutral white	PC-MLO	NO	-	-	Yes
911401664204	BVP282 LED252/WW 200W 220-240V AMB	100° x 30°	Warm white	PC-MLO	NO	-	-	Yes
911401664304	BVP282 LED252/CW 200W 220-240V SMB	54°	Cool white	PC-MLO	NO	-	-	Yes
911401664404	BVP282 LED252/CW 200W 220-240V AMB	100° x 30°	Cool white	PC-MLO	NO	-	-	Yes
911401664504	BVP282 LED252/NW 200W 220-240V SWB	100°	Neutral white	PC-MLO	NO	-	-	Yes
911401664604	BVP282 LED252/NW 200W 220-240V SMB	54°	Neutral white	PC-MLO	NO	-	-	Yes
911401664704	BVP282 LED202/WW 160W 220-240V SMB	54°	Warm white	PC-MLO	NO	-	-	Yes

General Information (2/2)

Order Code	Full Product Name	Number of		Order Code	Full Product Name	Number of	
		gear units	Optic type			gear units	Optic type
911401604403	BVP283 LED340/CW 335W 220-240V AWBE	-	-	911401604803	BVP283 LED311/WW 335W 220-240V AWBE	-	-
911401604503	BVP283 LED320/CW 315W 220-240V AWBE	-	-	911401604903	BVP283 LED210/CW 210W 220-240V AWBE	-	-
911401604603	BVP283 LED280/CW 280W 220-240V AWBE	-	-	911401605003	BVP283 LED293/WW 315W 220-240V AWBE	-	-
911401604703	BVP283 LED245/CW 245W 220-240V AWBE	-	-	911401605103	BVP283 LED256/WW 280W 220-240V AWBE	-	-

Tango G2 LED

Order Code	Full Product Name	Number of gear units	Optic type
911401605203	BVP283 LED224/WW 245W 220-240V AWBE	-	-
911401605303	BVP283 LED192/WW 210W 220-240V AWBE	-	-
911401605403	BVP283 LED340/NW 335W 220-240V AWBE	-	Asymmetrical wide beam
911401605503	BVP283 LED320/NW 315W 220-240V AWBE	-	Asymmetrical wide beam
911401605603	BVP283 LED280/NW 280W 220-240V AWBE	-	Asymmetrical wide beam
911401605703	BVP283 LED245/NW 245W 220-240V AWBE	-	Asymmetrical wide beam
911401605803	BVP283 LED210/NW 210W 220-240V AWBE	-	Asymmetrical wide beam
911401667002	BVP283 LED311/WW 335W 220-240V NB	-	-
911401667102	BVP283 LED293/WW 315W 220-240V NB	-	-
911401667202	BVP283 LED256/WW 280W 220-240V NB	-	-
911401667302	BVP283 LED224/WW 245W 220-240V NB	-	-
911401667402	BVP283 LED192/WW 210W 220-240V NB	-	-
911401667502	BVP283 LED340/CW 335W 220-240V NB	-	-
911401667602	BVP283 LED320/CW 315W 220-240V NB	-	-
911401667702	BVP283 LED280/CW 280W 220-240V NB	-	-
911401667802	BVP283 LED245/CW 245W 220-240V NB	-	-
911401667902	BVP283 LED210/CW 210W 220-240V NB	-	-
911401668002	BVP283 LED340/NW 335W 220-240V NB	-	-
911401668102	BVP283 LED320/NW 315W 220-240V NB	-	-
911401668202	BVP283 LED280/NW 280W 220-240V NB	-	-
911401668302	BVP283 LED245/NW 245W 220-240V NB	-	-
911401668402	BVP283 LED210/NW 210W 220-240V NB	-	Narrow beam
911401668502	BVP283 LED311/WW 335W 220-240V SWB	-	-
911401668602	BVP283 LED307/WW 315W 220-240V SWB	-	-
911401668702	BVP283 LED224/WW 245W 220-240V SWB	-	-

Order Code	Full Product Name	Number of gear units	Optic type
911401668802	BVP283 LED256/WW 280W 220-240V SWB	-	-
911401668902	BVP283 LED192/WW 210W 220-240V SWB	-	-
911401669002	BVP283 LED340/CW 335W 220-240V SWB	-	-
911401669102	BVP283 LED320/CW 315W 220-240V SWB	-	-
911401669202	BVP283 LED280/CW 280W 220-240V SWB	-	-
911401669302	BVP283 LED245/CW 245W 220-240V SWB	-	-
911401669402	BVP283 LED210/CW 210W 220-240V SWB	-	-
911401669502	BVP283 LED340/NW 335W 220-240V SWB	-	-
911401669602	BVP283 LED320/NW 315W 220-240V SWB	-	Symmetrical wide beam
911401669702	BVP283 LED280/NW 280W 220-240V SWB	-	Symmetrical wide beam
911401669802	BVP283 LED245/NW 245W 220-240V SWB	-	Symmetrical wide beam
911401669902	BVP283 LED210/NW 210W 220-240V SWB	-	Symmetrical wide beam
911401670002	BVP283 LED311/WW 335W 220-240V AWB	-	-
911401670102	BVP283 LED293/WW 315W 220-240V AWB	-	-
911401670202	BVP283 LED256/WW 280W 220-240V AWB	-	-
911401670302	BVP283 LED224/WW 245W 220-240V AWB	-	-
911401670402	BVP283 LED192/WW 210W 220-240V AWB	-	-
911401670502	BVP283 LED340/CW 335W 220-240V AWB	-	-
911401670602	BVP283 LED320/CW 315W 220-240V AWB	-	-
911401670702	BVP283 LED280/CW 280W 220-240V AWB	-	-
911401670802	BVP283 LED245/CW 245W 220-240V AWB	-	-
911401670902	BVP283 LED210/CW 210W 220-240V AWB	-	Asymmetrical wide beam
911401671002	BVP283 LED340/NW 335W 220-240V AWB	-	-
911401671102	BVP283 LED320/NW 315W 220-240V AWB	-	Asymmetrical wide beam
911401671202	BVP283 LED280/NW 280W 220-240V AWB	-	Asymmetrical wide beam

Tango G2 LED

Order Code	Full Product Name	Number of gear units	Optic type
911401671302	BVP283 LED245/NW 245W 220-240V AWB	-	Asymmetrical wide beam
911401671402	BVP283 LED210/NW 210W 220-240V AWB	-	Asymmetrical wide beam
911401689102	BVP283 LED327/WW 350W 220-240V NB	-	-
911401689202	BVP283 LED355/NW 350W 220-240V AWB	-	Asymmetrical wide beam
911401689302	BVP283 LED355/CW 350W 220-240V AWB	-	-
911401689402	BVP283 LED327/WW 350W 220-240V AWB	-	-
911401689502	BVP283 LED355/NW 350W 220-240V SWB	-	Symmetrical wide beam
911401689602	BVP283 LED355/CW 350W 220-240V SWB	-	-
911401689702	BVP283 LED327/WW 350W 220-240V SWB	-	-
911401689802	BVP283 LED355/NW 350W 220-240V NB	-	-
911401689902	BVP283 LED355/CW 350W 220-240V NB	1 unit	Narrow beam high reflectance
911401697402	BVP283 LED355/NW 350W 220-240V AWBE	-	-
911401697502	BVP283 LED327/WW 350W 220-240V AWBE	-	-
911401697602	BVP283 LED355/CW 350W 220-240V AWBE	-	-
911401660504	BVP281 LED101/CW 80W 220-240V SWB	-	Symmetrical wide beam
911401660704	BVP281 LED101/CW 80W 220-240V AMB	-	Asymmetrical medium beam
911401660804	BVP281 LED50/CW 40W 220-240V SWB	-	Symmetrical wide beam
911401660904	BVP281 LED101/WW 80W 220-240V SMB	-	Symmetrical medium beam
911401661004	BVP281 LED50/NW 40W 220-240V SWB	-	Symmetrical wide beam
911401661104	BVP281 LED101/WW 80W 220-240V AMB	-	Asymmetrical medium beam
911401661204	BVP281 LED50/NW 40W 220-240V SMB	-	Symmetrical medium beam
911401661304	BVP281 LED50/NW 40W 220-240V AMB	-	Asymmetrical medium beam
911401661404	BVP281 LED50/CW 40W 220-240V SMB	-	Symmetrical medium beam
911401661604	BVP281 LED50/CW 40W 220-240V AMB	-	Asymmetrical medium beam
911401661704	BVP281 LED50/WW 40W 220-240V SMB	-	Symmetrical medium beam

Order Code	Full Product Name	Number of gear units	Optic type
911401661804	BVP281 LED101/CW 80W 220-240V SMB	-	Symmetrical medium beam
911401661904	BVP281 LED101/NW 80W 220-240V AMB	-	Asymmetrical medium beam
911401662004	BVP281 LED151/CW 120W 220-240V AMB	-	Asymmetrical medium beam
911401662104	BVP281 LED151/WW 120W 220-240V AMB	-	Asymmetrical medium beam
911401662204	BVP281 LED151/NW 120W 220-240V AMB	-	Asymmetrical medium beam
911401662304	BVP281 LED101/NW 80W 220-240V SWB	-	Symmetrical wide beam
911401662404	BVP281 LED151/CW 120W 220-240V SMB	-	Symmetrical medium beam
911401662504	BVP281 LED151/WW 120W 220-240V SMB	-	Symmetrical medium beam
911401662604	BVP281 LED151/CW 120W 220-240V SWB	-	Symmetrical wide beam
911401662704	BVP281 LED101/NW 80W 220-240V SMB	-	Symmetrical medium beam
911401662804	BVP281 LED151/NW 120W 220-240V SWB	-	Symmetrical wide beam
911401662904	BVP281 LED151/NW 120W 220-240V SMB	-	Symmetrical medium beam
911401663004	BVP282 LED202/WW 160W 220-240V AMB	-	Asymmetrical medium beam
911401663104	BVP282 LED202/WW 160W 220-240V SWB	-	Symmetrical wide beam
911401663204	BVP282 LED202/NW 160W 220-240V SWB	-	Symmetrical wide beam
911401663304	BVP282 LED202/NW 160W 220-240V AMB	-	Asymmetrical medium beam
911401663404	BVP282 LED202/CW 160W 220-240V SMB	-	Symmetrical medium beam
911401663504	BVP282 LED202/CW 160W 220-240V AMB	-	Asymmetrical medium beam
911401663604	BVP282 LED202/NW 160W 220-240V SMB	-	Symmetrical medium beam
911401663704	BVP282 LED202/CW 160W 220-240V SWB	-	Symmetrical wide beam
911401663804	BVP282 LED252/WW 200W 220-240V SMB	-	Symmetrical medium beam
911401663904	BVP282 LED252/CW 200W 220-240V SWB	-	Symmetrical wide beam
911401664004	BVP282 LED252/WW 200W 220-240V SWB	-	Symmetrical wide beam
911401664104	BVP282 LED252/NW 200W 220-240V AMB	-	Asymmetrical medium beam
911401664204	BVP282 LED252/WW 200W 220-240V AMB	-	Asymmetrical medium beam

Tango G2 LED

Order Code	Full Product Name	Number of gear units	Optic type
911401664304	BVP282 LED252/CW 200W 220-240V SMB	-	Symmetrical medium beam
911401664404	BVP282 LED252/CW 200W 220-240V AMB	-	Asymmetrical medium beam
911401664504	BVP282 LED252/NW 200W 220-240V SWB	-	Symmetrical wide beam

Order Code	Full Product Name	Number of gear units	Optic type
911401664604	BVP282 LED252/NW 200W 220-240V SMB	-	Symmetrical medium beam
911401664704	BVP282 LED202/WW 160W 220-240V SMB	-	Symmetrical medium beam

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
911401604403	BVP283 LED340/CW 335W 220-240V AWBE	5700 K	>70	34000 lm
911401604503	BVP283 LED320/CW 315W 220-240V AWBE	5700 K	>70	32000 lm
911401604603	BVP283 LED280/CW 280W 220-240V AWBE	5700 K	>70	28000 lm
911401604703	BVP283 LED245/CW 245W 220-240V AWBE	5700 K	>70	24500 lm
911401604803	BVP283 LED311/WW 335W 220-240V AWBE	3000 K	>70	31100 lm
911401604903	BVP283 LED210/CW 210W 220-240V AWBE	5700 K	>70	21000 lm
911401605003	BVP283 LED293/WW 315W 220-240V AWBE	3000 K	>70	29300 lm
911401605103	BVP283 LED256/WW 280W 220-240V AWBE	3000 K	>70	25600 lm
911401605203	BVP283 LED224/WW 245W 220-240V AWBE	3000 K	>70	22400 lm
911401605303	BVP283 LED192/WW 210W 220-240V AWBE	3000 K	>70	19200 lm
911401605403	BVP283 LED340/NW 335W 220-240V AWBE	4000 K	>70	34000 lm
911401605503	BVP283 LED320/NW 315W 220-240V AWBE	4000 K	>70	32000 lm
911401605603	BVP283 LED280/NW 280W 220-240V AWBE	4000 K	>70	28000 lm
911401605703	BVP283 LED245/NW 245W 220-240V AWBE	4000 K	>70	24500 lm
911401605803	BVP283 LED210/NW 210W 220-240V AWBE	4000 K	>70	21000 lm
911401667002	BVP283 LED311/WW 335W 220-240V NB	3000 K	>70	31100 lm
911401667102	BVP283 LED293/WW 315W 220-240V NB	3000 K	>70	29300 lm
911401667202	BVP283 LED256/WW 280W 220-240V NB	3000 K	>70	25600 lm
911401667302	BVP283 LED224/WW 245W 220-240V NB	3000 K	>70	22400 lm

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
911401667402	BVP283 LED192/WW 210W 220-240V NB	3000 K	>70	19200 lm
911401667502	BVP283 LED340/CW 335W 220-240V NB	5700 K	>70	34000 lm
911401667602	BVP283 LED320/CW 315W 220-240V NB	5700 K	>70	32000 lm
911401667702	BVP283 LED280/CW 280W 220-240V NB	5700 K	>70	28000 lm
911401667802	BVP283 LED245/CW 245W 220-240V NB	5700 K	>70	24500 lm
911401667902	BVP283 LED210/CW 210W 220-240V NB	5700 K	>70	21000 lm
911401668002	BVP283 LED340/NW 335W 220-240V NB	4000 K	>70	34000 lm
911401668102	BVP283 LED320/NW 315W 220-240V NB	4000 K	>70	32000 lm
911401668202	BVP283 LED280/NW 280W 220-240V NB	4000 K	>70	28000 lm
911401668302	BVP283 LED245/NW 245W 220-240V NB	4000 K	>70	24500 lm
911401668402	BVP283 LED210/NW 210W 220-240V NB	4000 K	>70	21000 lm
911401668502	BVP283 LED311/WW 335W 220-240V SWB	3000 K	>70	31100 lm
911401668602	BVP283 LED307/WW 315W 220-240V SWB	3000 K	>70	29300 lm
911401668702	BVP283 LED224/WW 245W 220-240V SWB	3000 K	>70	22400 lm
911401668802	BVP283 LED256/WW 280W 220-240V SWB	3000 K	>70	25600 lm
911401668902	BVP283 LED192/WW 210W 220-240V SWB	3000 K	>70	19200 lm
911401669002	BVP283 LED340/CW 335W 220-240V SWB	5700 K	>70	34000 lm
911401669102	BVP283 LED320/CW 315W 220-240V SWB	5700 K	>70	32000 lm
911401669202	BVP283 LED280/CW 280W 220-240V SWB	5700 K	>70	28000 lm

Tango G2 LED

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
911401669302	BVP283 LED245/CW 245W 220-240V SWB	5700 K	>70	24500 lm
911401669402	BVP283 LED210/CW 210W 220-240V SWB	5700 K	>70	21000 lm
911401669502	BVP283 LED340/NW 335W 220-240V SWB	4000 K	>70	34000 lm
911401669602	BVP283 LED320/NW 315W 220-240V SWB	4000 K	>70	32000 lm
911401669702	BVP283 LED280/NW 280W 220-240V SWB	4000 K	>70	28000 lm
911401669802	BVP283 LED245/NW 245W 220-240V SWB	4000 K	>70	24500 lm
911401669902	BVP283 LED210/NW 210W 220-240V SWB	4000 K	>70	21000 lm
911401670002	BVP283 LED311/WW 335W 220-240V AWB	3000 K	>70	31100 lm
911401670102	BVP283 LED293/WW 315W 220-240V AWB	3000 K	>70	29300 lm
911401670202	BVP283 LED256/WW 280W 220-240V AWB	3000 K	>70	25600 lm
911401670302	BVP283 LED224/WW 245W 220-240V AWB	3000 K	>70	22400 lm
911401670402	BVP283 LED192/WW 210W 220-240V AWB	3000 K	>70	19200 lm
911401670502	BVP283 LED340/CW 335W 220-240V AWB	5700 K	>70	34000 lm
911401670602	BVP283 LED320/CW 315W 220-240V AWB	5700 K	>70	32000 lm
911401670702	BVP283 LED280/CW 280W 220-240V AWB	5700 K	>70	28000 lm
911401670802	BVP283 LED245/CW 245W 220-240V AWB	5700 K	>70	24500 lm
911401670902	BVP283 LED210/CW 210W 220-240V AWB	5700 K	>70	21000 lm
911401671002	BVP283 LED340/NW 335W 220-240V AWB	4000 K	>70	34000 lm
911401671102	BVP283 LED320/NW 315W 220-240V AWB	4000 K	>70	32000 lm
911401671202	BVP283 LED280/NW 280W 220-240V AWB	4000 K	>70	28000 lm
911401671302	BVP283 LED245/NW 245W 220-240V AWB	4000 K	>70	24500 lm
911401671402	BVP283 LED210/NW 210W 220-240V AWB	4000 K	>70	21000 lm
911401689102	BVP283 LED327/WW 350W 220-240V NB	3000 K	>70	32700 lm
911401689202	BVP283 LED355/NW 350W 220-240V AWB	4000 K	>70	35500 lm
911401689302	BVP283 LED355/CW 350W 220-240V AWB	5700 K	>70	35500 lm

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
911401689402	BVP283 LED327/WW 350W 220-240V AWB	3000 K	>70	32700 lm
911401689502	BVP283 LED355/NW 350W 220-240V SWB	4000 K	>70	35500 lm
911401689602	BVP283 LED355/CW 350W 220-240V SWB	5700 K	>70	35500 lm
911401689702	BVP283 LED327/WW 350W 220-240V SWB	3000 K	>70	32700 lm
911401689802	BVP283 LED355/NW 350W 220-240V NB	4000 K	>70	35500 lm
911401689902	BVP283 LED355/CW 350W 220-240V NB	5700 K	>70	35500 lm
911401697402	BVP283 LED355/NW 350W 220-240V AWBE	4000 K	>70	35500 lm
911401697502	BVP283 LED327/WW 350W 220-240V AWBE	3000 K	>70	32700 lm
911401697602	BVP283 LED355/CW 350W 220-240V AWBE	5700 K	>70	35500 lm
911401660504	BVP281 LED101/CW 80W 220-240V SWB	5700 K	70	10100 lm
911401660704	BVP281 LED101/CW 80W 220-240V AMB	5700 K	70	10100 lm
911401660804	BVP281 LED50/CW 40W 220-240V SWB	5700 K	70	5000 lm
911401660904	BVP281 LED101/WW 80W 220-240V SMB	3000 K	70	10100 lm
911401661004	BVP281 LED50/NW 40W 220-240V SWB	4000 K	70	5000 lm
911401661104	BVP281 LED101/WW 80W 220-240V AMB	3000 K	70	10100 lm
911401661204	BVP281 LED50/NW 40W 220-240V SMB	4000 K	70	5000 lm
911401661304	BVP281 LED50/NW 40W 220-240V AMB	4000 K	70	5000 lm
911401661404	BVP281 LED50/CW 40W 220-240V SMB	5700 K	70	5000 lm
911401661604	BVP281 LED50/CW 40W 220-240V AMB	5700 K	70	5000 lm
911401661704	BVP281 LED50/WW 40W 220-240V SMB	3000 K	70	5000 lm
911401661804	BVP281 LED101/CW 80W 220-240V SMB	5700 K	70	10100 lm
911401661904	BVP281 LED101/NW 80W 220-240V AMB	4000 K	70	10100 lm
911401662004	BVP281 LED151/CW 120W 220-240V AMB	5700 K	70	15100 lm
911401662104	BVP281 LED151/WW 120W 220-240V AMB	3000 K	70	15100 lm
911401662204	BVP281 LED151/NW 120W 220-240V AMB	4000 K	70	15100 lm

Tango G2 LED

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour	
			Rendering Index	Initial luminous flux
911401662304	BVP281 LED101/NW 80W 220-240V SWB	4000 K	70	10100 lm
911401662404	BVP281 LED151/CW 120W 220-240V SMB	5700 K	70	15100 lm
911401662504	BVP281 LED151/WW 120W 220-240V SMB	3000 K	70	15100 lm
911401662604	BVP281 LED151/CW 120W 220-240V SWB	5700 K	70	15100 lm
911401662704	BVP281 LED101/NW 80W 220-240V SMB	4000 K	70	10100 lm
911401662804	BVP281 LED151/NW 120W 220-240V SWB	4000 K	70	15100 lm
911401662904	BVP281 LED151/NW 120W 220-240V SMB	4000 K	70	15100 lm
911401663004	BVP282 LED202/WW 160W 220-240V AMB	3000 K	70	20200 lm
911401663104	BVP282 LED202/WW 160W 220-240V SWB	3000 K	70	20200 lm
911401663204	BVP282 LED202/NW 160W 220-240V SWB	4000 K	70	20200 lm
911401663304	BVP282 LED202/NW 160W 220-240V AMB	4000 K	70	20200 lm
911401663404	BVP282 LED202/CW 160W 220-240V SMB	5700 K	70	20200 lm
911401663504	BVP282 LED202/CW 160W 220-240V AMB	5700 K	70	20200 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour	
			Rendering Index	Initial luminous flux
911401663604	BVP282 LED202/NW 160W 220-240V SMB	4000 K	70	20200 lm
911401663704	BVP282 LED202/CW 160W 220-240V SWB	5700 K	70	20200 lm
911401663804	BVP282 LED252/WW 200W 220-240V SMB	3000 K	70	25200 lm
911401663904	BVP282 LED252/CW 200W 220-240V SWB	5700 K	70	25200 lm
911401664004	BVP282 LED252/WW 200W 220-240V SWB	3000 K	70	25200 lm
911401664104	BVP282 LED252/NW 200W 220-240V AMB	4000 K	70	25200 lm
911401664204	BVP282 LED252/WW 200W 220-240V AMB	3000 K	70	25200 lm
911401664304	BVP282 LED252/CW 200W 220-240V SMB	5700 K	70	25200 lm
911401664404	BVP282 LED252/CW 200W 220-240V AMB	5700 K	70	25200 lm
911401664504	BVP282 LED252/NW 200W 220-240V SWB	4000 K	70	25200 lm
911401664604	BVP282 LED252/NW 200W 220-240V SMB	4000 K	70	25200 lm
911401664704	BVP282 LED202/WW 160W 220-240V SMB	3000 K	70	20200 lm

Light Technical

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward
				light output ratio
911401604403	BVP283 LED340/CW 335W 220-240V AWBE	-	-	-
911401604503	BVP283 LED320/CW 315W 220-240V AWBE	-	-	-
911401604603	BVP283 LED280/CW 280W 220-240V AWBE	-	-	-
911401604703	BVP283 LED245/CW 245W 220-240V AWBE	-	-	-
911401604803	BVP283 LED311/WW 335W 220-240V AWBE	-	-	-
911401604903	BVP283 LED210/CW 210W 220-240V AWBE	-	-	-
911401605003	BVP283 LED293/WW 315W 220-240V AWBE	-	-	-
911401605103	BVP283 LED256/WW 280W 220-240V AWBE	-	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward
				light output ratio
911401605203	BVP283 LED224/WW 245W 220-240V AWBE	-	-	-
911401605303	BVP283 LED192/WW 210W 220-240V AWBE	-	-	-
911401605403	BVP283 LED340/NW 335W 220-240V AWBE	-	-	-
911401605503	BVP283 LED320/NW 315W 220-240V AWBE	-	-	-
911401605603	BVP283 LED280/NW 280W 220-240V AWBE	-	-	-
911401605703	BVP283 LED245/NW 245W 220-240V AWBE	-	-	-
911401605803	BVP283 LED210/NW 210W 220-240V AWBE	-	-	-
911401667002	BVP283 LED311/WW 335W 220-240V NB	-	-	-

Tango G2 LED

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
911401667102	BVP283 LED293/WW 315W 220-240V NB	-	-	-
911401667202	BVP283 LED256/WW 280W 220-240V NB	-	-	-
911401667302	BVP283 LED224/WW 245W 220-240V NB	-	-	-
911401667402	BVP283 LED192/WW 210W 220-240V NB	-	-	-
911401667502	BVP283 LED340/CW 335W 220-240V NB	-	-	-
911401667602	BVP283 LED320/CW 315W 220-240V NB	-	-	-
911401667702	BVP283 LED280/CW 280W 220-240V NB	-	-	-
911401667802	BVP283 LED245/CW 245W 220-240V NB	-	-	-
911401667902	BVP283 LED210/CW 210W 220-240V NB	-	-	-
911401668002	BVP283 LED340/NW 335W 220-240V NB	-	-	-
911401668102	BVP283 LED320/NW 315W 220-240V NB	-	-	-
911401668202	BVP283 LED280/NW 280W 220-240V NB	-	-	-
911401668302	BVP283 LED245/NW 245W 220-240V NB	-	-	-
911401668402	BVP283 LED210/NW 210W 220-240V NB	-	-	-
911401668502	BVP283 LED311/WW 335W 220-240V SWB	-	-	-
911401668602	BVP283 LED307/WW 315W 220-240V SWB	-	-	-
911401668702	BVP283 LED224/WW 245W 220-240V SWB	-	-	-
911401668802	BVP283 LED256/WW 280W 220-240V SWB	-	-	-
911401668902	BVP283 LED192/WW 210W 220-240V SWB	-	-	-
911401669002	BVP283 LED340/CW 335W 220-240V SWB	-	-	-
911401669102	BVP283 LED320/CW 315W 220-240V SWB	-	-	-
911401669202	BVP283 LED280/CW 280W 220-240V SWB	-	-	-
911401669302	BVP283 LED245/CW 245W 220-240V SWB	-	-	-
911401669402	BVP283 LED210/CW 210W 220-240V SWB	-	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
911401669502	BVP283 LED340/NW 335W 220-240V SWB	-	-	-
911401669602	BVP283 LED320/NW 315W 220-240V SWB	-	-	-
911401669702	BVP283 LED280/NW 280W 220-240V SWB	-	-	-
911401669802	BVP283 LED245/NW 245W 220-240V SWB	-	-	-
911401669902	BVP283 LED210/NW 210W 220-240V SWB	-	-	-
911401670002	BVP283 LED311/WW 335W 220-240V AWB	-	-	-
911401670102	BVP283 LED293/WW 315W 220-240V AWB	-	-	-
911401670202	BVP283 LED256/WW 280W 220-240V AWB	-	-	-
911401670302	BVP283 LED224/WW 245W 220-240V AWB	-	-	-
911401670402	BVP283 LED192/WW 210W 220-240V AWB	-	-	-
911401670502	BVP283 LED340/CW 335W 220-240V AWB	-	-	-
911401670602	BVP283 LED320/CW 315W 220-240V AWB	-	-	-
911401670702	BVP283 LED280/CW 280W 220-240V AWB	-	-	-
911401670802	BVP283 LED245/CW 245W 220-240V AWB	-	-	-
911401670902	BVP283 LED210/CW 210W 220-240V AWB	-	-	-
911401671002	BVP283 LED340/NW 335W 220-240V AWB	-	-	-
911401671102	BVP283 LED320/NW 315W 220-240V AWB	-	-	-
911401671202	BVP283 LED280/NW 280W 220-240V AWB	-	-	-
911401671302	BVP283 LED245/NW 245W 220-240V AWB	-	-	-
911401671402	BVP283 LED210/NW 210W 220-240V AWB	-	-	-
911401689102	BVP283 LED327/WW 350W 220-240V NB	-	-	-
911401689202	BVP283 LED355/NW 350W 220-240V AWB	-	-	-
911401689302	BVP283 LED355/CW 350W 220-240V AWB	-	-	-
911401689402	BVP283 LED327/WW 350W 220-240V AWB	-	-	-

Tango G2 LED

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
911401689502	BVP283 LED355/NW 350W 220-240V SWB	-	-	-
911401689602	BVP283 LED355/CW 350W 220-240V SWB	-	-	-
911401689702	BVP283 LED327/WW 350W 220-240V SWB	-	-	-
911401689802	BVP283 LED355/NW 350W 220-240V NB	-	-	-
911401689902	BVP283 LED355/CW 350W 220-240V NB	-	-	1
911401697402	BVP283 LED355/NW 350W 220-240V AWBE	-	-	-
911401697502	BVP283 LED327/WW 350W 220-240V AWBE	-	-	-
911401697602	BVP283 LED355/CW 350W 220-240V AWBE	-	-	-
911401660504	BVP281 LED101/CW 80W 220-240V SWB	-	-	-
911401660704	BVP281 LED101/CW 80W 220-240V AMB	-	-	-
911401660804	BVP281 LED50/CW 40W 220-240V SWB	-	-	-
911401660904	BVP281 LED101/WW 80W 220-240V SMB	-	-	-
911401661004	BVP281 LED50/NW 40W 220-240V SWB	-	-	-
911401661104	BVP281 LED101/WW 80W 220-240V AMB	-	-	-
911401661204	BVP281 LED50/NW 40W 220-240V SMB	-	-	-
911401661304	BVP281 LED50/NW 40W 220-240V AMB	-	-	-
911401661404	BVP281 LED50/CW 40W 220-240V SMB	-	-	-
911401661604	BVP281 LED50/CW 40W 220-240V AMB	-	-	-
911401661704	BVP281 LED50/WW 40W 220-240V SMB	-	-	-
911401661804	BVP281 LED101/CW 80W 220-240V SMB	-	-	-
911401661904	BVP281 LED101/NW 80W 220-240V AMB	-	-	-
911401662004	BVP281 LED151/CW 120W 220-240V AMB	-	-	-
911401662104	BVP281 LED151/WW 120W 220-240V AMB	-	-	-
911401662204	BVP281 LED151/NW 120W 220-240V AMB	-	-	-
911401662304	BVP281 LED101/NW 80W 220-240V SWB	-	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
911401662404	BVP281 LED151/CW 120W 220-240V SMB	-	-	-
911401662504	BVP281 LED151/WW 120W 220-240V SMB	-	-	-
911401662604	BVP281 LED151/CW 120W 220-240V SWB	-	-	-
911401662704	BVP281 LED101/NW 80W 220-240V SMB	-	-	-
911401662804	BVP281 LED151/NW 120W 220-240V SWB	-	-	-
911401662904	BVP281 LED151/NW 120W 220-240V SMB	-	-	-
911401663004	BVP282 LED202/WW 160W 220-240V AMB	-	-	-
911401663104	BVP282 LED202/WW 160W 220-240V SWB	-	-	-
911401663204	BVP282 LED202/NW 160W 220-240V SWB	-	-	-
911401663304	BVP282 LED202/NW 160W 220-240V AMB	-	-	-
911401663404	BVP282 LED202/CW 160W 220-240V SMB	-	-	-
911401663504	BVP282 LED202/CW 160W 220-240V AMB	-	-	-
911401663604	BVP282 LED202/NW 160W 220-240V SMB	-	-	-
911401663704	BVP282 LED202/CW 160W 220-240V SWB	-	-	-
911401663804	BVP282 LED252/WW 200W 220-240V SMB	-	-	-
911401663904	BVP282 LED252/CW 200W 220-240V SWB	-	-	-
911401664004	BVP282 LED252/WW 200W 220-240V SWB	-	-	-
911401664104	BVP282 LED252/NW 200W 220-240V AMB	-	-	-
911401664204	BVP282 LED252/WW 200W 220-240V AMB	-	-	-
911401664304	BVP282 LED252/CW 200W 220-240V SMB	-	-	-
911401664404	BVP282 LED252/CW 200W 220-240V AMB	-	-	-
911401664504	BVP282 LED252/NW 200W 220-240V SWB	-	-	-
911401664604	BVP282 LED252/NW 200W 220-240V SMB	-	-	-
911401664704	BVP282 LED202/WW 160W 220-240V SMB	-	-	-

Tango G2 LED

