



Best Area Lighting Luminaire within Your Budget

Tango G2 LED

Tango G2 LED is a general purpose LED flood lighting luminaire for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

Benefits

- Energy saving: more than 50% of energy saving when compared to conventional floodlight
- Free from lamp replacement
- Low maintenance cost: IP65 housing ensures low maintenance with no need for internal cleaning, resulting in a lower total cost of ownership

Features


- Optical beam choice of symmetric and asymmetric fulfils majority needs of lighting application
- Painted non-corrosive die-cast aluminum housing and steel bracket
- Universal "U" shape mounting bracket

Application

- Area lighting
- Industry area
- Façade

Tango G2 LED

Versions



BVP283 220-240V

Approval and Application

Mech. impact protection code IK07

Controls and Dimming

Dimmable No

General Information

CE mark CE mark

Light source colour 740 neutral white

Optical cover/lens type G

Driver included Yes

Initial Performance (IEC Compliant)

Init. Corr. Colour Temperature 3000 K

Init. Colour Rendering Index >70

Mechanical and Housing

Colour Aluminium and Grey

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial luminous flux
911401667302	BVP283 LED224/WW 245W 220-240V NB	22400 lm
911401668502	BVP283 LED311/WW 335W 220-240V SWB	31100 lm

