



Best Area Lighting Luminaire within Your Budget

Tango G2 LED

Tango G2 LED is a general purpose LED flood lighting luminaire for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

Benefits

- Energy saving: more than 50% of energy saving when compared to conventional floodlight
- Free from lamp replacement
- Low maintenance cost: IP65 housing ensures low maintenance with no need for internal cleaning, resulting in a lower total cost of ownership

Features


- Optical beam choice of symmetric and asymmetric fulfils majority needs of lighting application
- Painted non-corrosive die-cast aluminum housing and steel bracket
- Universal "U" shape mounting bracket

Application

- Area lighting
- Industry area
- Façade

Tango G2 LED

Versions



BVP283 220-240V

Approval and Application

Mech. impact protection code IK08

General Information

CE mark CE mark

Optical cover/lens type PC-MLO

Driver included Yes

Initial Performance (IEC Compliant)

Init. Colour Rendering Index >70

Mechanical and Housing

Colour Aluminium and Grey

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401692505	BVP283 LED262/CW 200W 220-240V AWB	No
911401692605	BVP283 LED262/CW 200W 220-240V AWBE	No
911401692705	BVP283 LED262/CW 200W 220-240V NB	No
911401692805	BVP283 LED262/CW 200W 220-240V SWB	No
911401692905	BVP283 LED262/NW 200W 220-240V AWB	No
911401693005	BVP283 LED262/NW 200W 220-240V AWBE	No
911401693105	BVP283 LED262/NW 200W 220-240V NB	No
911401693205	BVP283 LED262/NW 200W 220-240V SWB	No
911401693505	BVP283 LED281/WW 235W 220-240V AWB	No
911401693605	BVP283 LED281/WW 235W 220-240V AWBE	No
911401693705	BVP283 LED306/CW 235W 220-240V AWB	No
911401693805	BVP283 LED306/CW 235W 220-240V AWBE	No
911401693905	BVP283 LED306/NW 235W 220-240V AWB	No
911401694005	BVP283 LED306/NW 235W 220-240V AWBE	No
911401694105	BVP283 LED319/WW 270W 220-240V AWBE	No
911401694205	BVP283 LED319/WW 270W 220-240V NB	No
911401694305	BVP283 LED347/CW 270W 220-240V AWBE	No
911401694405	BVP283 LED347/CW 270W 220-240V NB	No
911401694505	BVP283 LED347/NW 270W 220-240V AWBE	No

Order Code	Full Product Name	Dimmable
911401694605	BVP283 LED347/NW 270W 220-240V NB	No
911401694905	BVP283 LED390/CW 305W 220-240V AWBE	No
911401695005	BVP283 LED390/CW 305W 220-240V NB	No
911401695105	BVP283 LED390/CW 305W 220-240V SWB	No
911401695205	BVP283 LED390/NW 305W 220-240V AWBE	No
911401695305	BVP283 LED390/NW 305W 220-240V NB	No
911401695405	BVP283 LED390/NW 305W 220-240V SWB	No
911401695505	BVP283 LED375/WW 320W 220-240V AWB	No
911401695605	BVP283 LED375/WW 320W 220-240V AWBE	No
911401695705	BVP283 LED375/WW 320W 220-240V NB	No
911401695805	BVP283 LED375/WW 320W 220-240V SWB	No
911401695905	BVP283 LED408/CW 320W 220-240V AWB	No
911401696005	BVP283 LED408/CW 320W 220-240V AWBE	No
911401696105	BVP283 LED408/CW 320W 220-240V NB	No
911401696205	BVP283 LED408/CW 320W 220-240V SWB	No
911401696305	BVP283 LED408/NW 320W 220-240V AWB	No
911401696405	BVP283 LED408/NW 320W 220-240V AWBE	No
911401696505	BVP283 LED408/NW 320W 220-240V NB	No
911401696605	BVP283 LED408/NW 320W 220-240V SWB	No

Tango G2 LED

Order Code	Full Product Name	Dimmable
911401697005	BVP283 LED395/WW 335W 220-240V AWBE	No
911401697105	BVP283 LED395/WW 335W 220-240V NB	No
911401697205	BVP283 LED395/WW 335W 220-240V SWB	No
911401697305	BVP283 LED430/CW 335W 220-240V AWB	No
911401697405	BVP283 LED430/CW 335W 220-240V AWBE	No
911401697505	BVP283 LED430/CW 335W 220-240V NB	No

Order Code	Full Product Name	Dimmable
911401697605	BVP283 LED430/CW 335W 220-240V SWB	No
911401697705	BVP283 LED430/NW 335W 220-240V AWB	No
911401697805	BVP283 LED430/NW 335W 220-240V AWBE	No
911401697905	BVP283 LED430/NW 335W 220-240V NB	No
911401698005	BVP283 LED430/NW 335W 220-240V SWB	No
911401698105	BVP283 LED430/NW 335W AWB P7 GM	Yes

General Information

Order Code	Full Product Name	Light source colour
911401692505	BVP283 LED262/CW 200W 220-240V AWB	757 cool white
911401692605	BVP283 LED262/CW 200W 220-240V AWBE	757 cool white
911401692705	BVP283 LED262/CW 200W 220-240V NB	757 cool white
911401692805	BVP283 LED262/CW 200W 220-240V SWB	757 cool white
911401692905	BVP283 LED262/NW 200W 220-240V AWB	740 neutral white
911401693005	BVP283 LED262/NW 200W 220-240V AWBE	740 neutral white
911401693105	BVP283 LED262/NW 200W 220-240V NB	740 neutral white
911401693205	BVP283 LED262/NW 200W 220-240V SWB	740 neutral white
911401693505	BVP283 LED281/WW 235W 220-240V AWB	730 warm white
911401693605	BVP283 LED281/WW 235W 220-240V AWBE	730 warm white
911401693705	BVP283 LED306/CW 235W 220-240V AWB	757 cool white
911401693805	BVP283 LED306/CW 235W 220-240V AWBE	757 cool white
911401693905	BVP283 LED306/NW 235W 220-240V AWB	740 neutral white
911401694005	BVP283 LED306/NW 235W 220-240V AWBE	740 neutral white
911401694105	BVP283 LED319/WW 270W 220-240V AWBE	730 warm white
911401694205	BVP283 LED319/WW 270W 220-240V NB	730 warm white
911401694305	BVP283 LED347/CW 270W 220-240V AWBE	757 cool white
911401694405	BVP283 LED347/CW 270W 220-240V NB	757 cool white
911401694505	BVP283 LED347/NW 270W 220-240V AWBE	740 neutral white
911401694605	BVP283 LED347/NW 270W 220-240V NB	740 neutral white
911401694905	BVP283 LED390/CW 305W 220-240V AWBE	757 cool white
911401695005	BVP283 LED390/CW 305W 220-240V NB	757 cool white
911401695105	BVP283 LED390/CW 305W 220-240V SWB	757 cool white
911401695205	BVP283 LED390/NW 305W 220-240V AWBE	740 neutral white
911401695305	BVP283 LED390/NW 305W 220-240V NB	740 neutral white

Order Code	Full Product Name	Light source colour
911401695405	BVP283 LED390/NW 305W 220-240V SWB	740 neutral white
911401695505	BVP283 LED375/WW 320W 220-240V AWB	730 warm white
911401695605	BVP283 LED375/WW 320W 220-240V AWBE	730 warm white
911401695705	BVP283 LED375/WW 320W 220-240V NB	730 warm white
911401695805	BVP283 LED375/WW 320W 220-240V SWB	730 warm white
911401695905	BVP283 LED408/CW 320W 220-240V AWB	757 cool white
911401696005	BVP283 LED408/CW 320W 220-240V AWBE	757 cool white
911401696105	BVP283 LED408/CW 320W 220-240V NB	757 cool white
911401696205	BVP283 LED408/CW 320W 220-240V SWB	757 cool white
911401696305	BVP283 LED408/NW 320W 220-240V AWB	740 neutral white
911401696405	BVP283 LED408/NW 320W 220-240V AWBE	740 neutral white
911401696505	BVP283 LED408/NW 320W 220-240V NB	740 neutral white
911401696605	BVP283 LED408/NW 320W 220-240V SWB	740 neutral white
911401697005	BVP283 LED395/WW 335W 220-240V AWBE	730 warm white
911401697105	BVP283 LED395/WW 335W 220-240V NB	730 warm white
911401697205	BVP283 LED395/WW 335W 220-240V SWB	730 warm white
911401697305	BVP283 LED430/CW 335W 220-240V AWB	757 cool white
911401697405	BVP283 LED430/CW 335W 220-240V AWBE	757 cool white
911401697505	BVP283 LED430/CW 335W 220-240V NB	757 cool white
911401697605	BVP283 LED430/CW 335W 220-240V SWB	757 cool white
911401697705	BVP283 LED430/NW 335W 220-240V AWB	740 neutral white
911401697805	BVP283 LED430/NW 335W 220-240V AWBE	740 neutral white
911401697905	BVP283 LED430/NW 335W 220-240V NB	740 neutral white
911401698005	BVP283 LED430/NW 335W 220-240V SWB	740 neutral white
911401698105	BVP283 LED430/NW 335W AWB P7 GM	740 neutral white

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
911401692505	BVP283 LED262/CW 200W 220-240V AWB	5700 K	26200 lm
911401692605	BVP283 LED262/CW 200W 220-240V AWBE	5700 K	26200 lm
911401692705	BVP283 LED262/CW 200W 220-240V NB	5700 K	26200 lm
911401692805	BVP283 LED262/CW 200W 220-240V SWB	5700 K	26200 lm
911401692905	BVP283 LED262/NW 200W 220-240V AWB	4000 K	26200 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
911401693005	BVP283 LED262/NW 200W 220-240V AWBE	4000 K	26200 lm
911401693105	BVP283 LED262/NW 200W 220-240V NB	4000 K	26200 lm
911401693205	BVP283 LED262/NW 200W 220-240V SWB	4000 K	26200 lm
911401693505	BVP283 LED281/WW 235W 220-240V AWB	3000 K	28100 lm
911401693605	BVP283 LED281/WW 235W 220-240V AWBE	3000 K	28100 lm

Tango G2 LED

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
911401693705	BVP283 LED306/CW 235W 220-240V AWB	5700 K	30600 lm
911401693805	BVP283 LED306/CW 235W 220-240V AWBE	5700 K	30600 lm
911401693905	BVP283 LED306/NW 235W 220-240V AWB	4000 K	30600 lm
911401694005	BVP283 LED306/NW 235W 220-240V AWBE	4000 K	30600 lm
911401694105	BVP283 LED319/WW 270W 220-240V AWBE	3000 K	31900 lm
911401694205	BVP283 LED319/WW 270W 220-240V NB	3000 K	31900 lm
911401694305	BVP283 LED347/CW 270W 220-240V AWBE	5700 K	34700 lm
911401694405	BVP283 LED347/CW 270W 220-240V NB	5700 K	34700 lm
911401694505	BVP283 LED347/NW 270W 220-240V AWBE	4000 K	34700 lm
911401694605	BVP283 LED347/NW 270W 220-240V NB	4000 K	34700 lm
911401694905	BVP283 LED390/CW 305W 220-240V AWBE	5700 K	39000 lm
911401695005	BVP283 LED390/CW 305W 220-240V NB	5700 K	39000 lm
911401695105	BVP283 LED390/CW 305W 220-240V SWB	5700 K	39000 lm
911401695205	BVP283 LED390/NW 305W 220-240V AWBE	4000 K	39000 lm
911401695305	BVP283 LED390/NW 305W 220-240V NB	4000 K	39000 lm
911401695405	BVP283 LED390/NW 305W 220-240V SWB	4000 K	39000 lm
911401695505	BVP283 LED375/WW 320W 220-240V AWB	3000 K	37500 lm
911401695605	BVP283 LED375/WW 320W 220-240V AWBE	3000 K	37500 lm
911401695705	BVP283 LED375/WW 320W 220-240V NB	3000 K	37500 lm
911401695805	BVP283 LED375/WW 320W 220-240V SWB	3000 K	37500 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
911401695905	BVP283 LED408/CW 320W 220-240V AWB	5700 K	40800 lm
911401696005	BVP283 LED408/CW 320W 220-240V AWBE	5700 K	40800 lm
911401696105	BVP283 LED408/CW 320W 220-240V NB	5700 K	40800 lm
911401696205	BVP283 LED408/CW 320W 220-240V SWB	5700 K	40800 lm
911401696305	BVP283 LED408/NW 320W 220-240V AWB	4000 K	40800 lm
911401696405	BVP283 LED408/NW 320W 220-240V AWBE	4000 K	40800 lm
911401696505	BVP283 LED408/NW 320W 220-240V NB	4000 K	40800 lm
911401696605	BVP283 LED408/NW 320W 220-240V SWB	4000 K	40800 lm
911401697005	BVP283 LED395/WW 335W 220-240V AWBE	3000 K	39500 lm
911401697105	BVP283 LED395/WW 335W 220-240V NB	3000 K	39500 lm
911401697205	BVP283 LED395/WW 335W 220-240V SWB	3000 K	39500 lm
911401697305	BVP283 LED430/CW 335W 220-240V AWB	5700 K	43000 lm
911401697405	BVP283 LED430/CW 335W 220-240V AWBE	5700 K	43000 lm
911401697505	BVP283 LED430/CW 335W 220-240V NB	5700 K	43000 lm
911401697605	BVP283 LED430/CW 335W 220-240V SWB	5700 K	43000 lm
911401697705	BVP283 LED430/NW 335W 220-240V AWB	4000 K	43000 lm
911401697805	BVP283 LED430/NW 335W 220-240V AWBE	4000 K	43000 lm
911401697905	BVP283 LED430/NW 335W 220-240V NB	4000 K	43000 lm
911401698005	BVP283 LED430/NW 335W 220-240V SWB	4000 K	43000 lm
911401698105	BVP283 LED430/NW 335W AWB P7 GM	4000 K	43000 lm

Tango G2 LED

