



# Energy-efficient lighting for industrial and commercial applications

## Vandalite Waterproof

Mini Vandalite LED is the perfect all-night luminaire for industrial corridors, security lighting, garages and residential areas. LED-based, it reduces cost with low energy consumption and low maintenance because of LEDs' high reliability and long service life. It can be either ceiling or wall-mounted, and the translucent bowl provides excellent distribution of low-level lighting for the surroundings. Robust with vandal-resistant construction, Mini Vandalite LED is suitable for both outdoor and indoor applications.

### Benefits

- Highly energy-efficient
- Long life, maintenance-free
- Robust design and vandal-proof construction

### Features

- Continuous energy-efficient lighting
- Reliable long-lasting LEDs
- Sturdy, vandal-resistant design and construction

### Application

- Industrial areas
- Residential areas
- Security lighting

Versions



BCW098 LED20



BCW098 LED20

# Vandalite Waterproof

## Application conditions

Ambient temperature range	-20 to +45 °C
Maximum dim level	Not applicable

## Approval and application

Mech. impact protection code	IK10
Ingress protection code	IP65

## Controls and dimming

Dimmable	No
----------	----

## Operating and electrical

Input Voltage	220 to 240 V
---------------	--------------

## General information

CE mark	CE mark
Protection class IEC	Safety class I (I)
Optical cover/lens type	O
Driver included	Yes
ENEC mark	-
Flammability mark	NO
Gear	-
Glow-wire test	650/30
Lamp family code	LED20S
Light source replaceable	No
Number of gear units	1 unit
Optic type	WB
UL mark	-

## Initial performance (IEC compliant)

Initial chromaticity	-
Init. Color Rendering Index	85
Initial LED luminaire efficacy	105 lm/W
Initial luminous flux	2000 lm
Luminous flux tolerance	+/-7.5%
Initial input power	19 W

## Mechanical and housing

Color	Gray
-------	------

## Initial performance (IEC compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature
911401839599	BCW098 LED20/NW PSU L600	4000 K
911401839699	BCW098 LED20/CW PSU L600	6500 K

