



A flexible and affordable retail toolbox

GreenSpace Accent Projector

Thanks to the GreenSpace Accent family, retailers and building operators can now make the switch from CDM to LED and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Projector's regular 3C adaptor and specific lumen packages make retrofit installation quick and easy. For fashion and food retailers, the GreenSpace Accent Projector is available with special light flavours and LED recipes to show the clothes and fresh food produce on offer in the very best light. Check out our Fashion and Food catalogue pages to find out more about CrispWhite, PremiumWhite, Fresh Food Meat and Fresh Food Champagne.

Benefits

- Clean and robust design
- Full retail application coverage
- Lighting flexibility beyond CDM

Features

- Driver integrated in a compact housing
- Philips PerfectAccent light quality
- Light flavours for fashion and LED recipes for food included
- CDM retrofit track-mounted luminaire

Application

- Retail outlets, especially food and fashion shops

Specifications

GreenSpace Accent Projector

Type	ST320T (3C track version)
Light source	Non-replaceable LED module
Power	14.4, 23 and 32.9 W at light colours 830, 840 and 827 for LED17S, LED27S and LED39S
Beam angle	10° (NB), 24° (MB), 36° (WB), 60° (VWB)
Luminous flux	1,700 lm (for light colour 830, PW9) 2,600 lm (light colour 827, PW9 and CRW) 3,600 lm (light colour PW9) 1,750 lm (for light colour CRW, CH) 1,650, 3,700 lm (for light colour 827) 2,700, 3,900 lm (for light colour 830) 1,800, 2,800, 4,000 lm (for light colour 840)
Correlated Colour	2,500 K (for Fresh Food Champagne CH)
Temperature	2,700, 3,000 K (for 830, PremiumWhite PW9, CrispWhite CRW, Fresh Food Meat FMT) 4,000 K
Colour Rendering Index	>80 (for 3,000, 4,000 and 2,700 K, Fresh Food Meat FMT) >90 (for PremiumWhite PW9, CrispWhite CRW, Fresh Food Champagne CH)
Standard deviation colour matching (SDCM)	3 (with a tolerance of +/- 0.005 on colour point measurement)
Lumen maintenance at median useful life*	L80 50,000 h

Control gear failure rate at median useful life	5% 50,000 h
Performance Ambient Temperature Tq	+25 °C
Operating temperature range	10 to +40 °C
Driver	Built-in
Power/Data supply	Not applicable
Mains voltage	220-240 V / 50-60 Hz
Dimming	Not available
Material	Tube: aluminium Bracket: polyamide Optical cover: PMMA
Colour	White (WH, RAL9003), black (BK, RAL 9004), silver (SI, RAL9006)
Connection	3C track adaptor
Installation	On 3-circuit track Through-wiring not applicable
Accessories	Honeycomb (HC), skirt black or white (SK). To be ordered separately or directly with the product.

Versions



GreenSpace Accent Projector
ST320T luminaire



GreenSpace Accent Projector
ST320T luminaire



GreenSpace Accent Projector

Product details



GreenSpace_Accent_Projector-ST320T_BK-DP01.tif



GreenSpace_Accent_Projector-ST320T_BK-DP02.tif



GreenSpace_Accent_Projector-ST320T_BK-DP03.tif



GreenSpace_Accent_Projector-ST320T_BK-DP04.tif



GreenSpace_Accent_Projector-ST320T_BK-DP05.tif



GreenSpace_Accent_Projector-ST320T_BK-DP06.tif

GreenSpace Accent Projector

Application Conditions

Ambient temperature range +10 to +40 °C

Approval and Application

Mech. impact protection code IK02

Ingress protection code IP20

Operating and Electrical

Input Voltage 220-240 V

General Information

Beam angle of light source 120 °

CE mark CE mark

Driver included Yes

ENEC mark ENEC mark

Flammability mark F

Glow-wire test 650/5

Light source replaceable No

Number of gear units 1 unit

Product Family Code ST320T

Initial Performance (IEC Compliant)

Luminous flux tolerance +/-10%

Controls and Dimming

Order Code	Full Product Name	Dimmable
16648900	ST320T LED19S/FMT PSU MB WH	No
16650200	ST320T LED27S/PW930 PSU MB WH	No
16652600	ST320T LED17S/827 PSU MB WH	No
16653300	ST320T LED17S/830 PSU MB WH	No
16654000	ST320T LED17S/840 PSU MB WH	No
16655700	ST320T LED17S/CRW PSU MB WH	No
16656400	ST320T LED17S/PW930 PSU MB WH	No
16658800	ST320T LED27S/827 PSU MB WH	No
16660100	ST320T LED27S/830 PSU MB WH	No
16661800	ST320T LED27S/840 PSU MB WH	No
16662500	ST320T LED27S/840 PSU WB WH	No
16663200	ST320T LED27S/CRW PSU MB WH	No
16666300	ST320T LED20S/PW930 PSU NB WH	No
16668700	ST320T LED39S/827 PSU VWB WH	No
16669400	ST320T LED39S/827 PSU WB WH	No
16670000	ST320T LED39S/830 PSU VWB WH	No
16675500	ST320T LED39S/830 PSU WB WH	No
16676200	ST320T LED39S/840 PSU VWB WH	No
16679300	ST320T LED39S/840 PSU WB WH	No
16682300	ST320T LED39S/PW930 PSU WB WH	No
39939900	ST320T LED17S/CH PSU WB WH	No
40335500	ST320T LED49S/830 PSU MB WH	No
40336200	ST320T LED49S/827 PSD-VLC MB WH	Yes
40337900	ST320T LED49S/827 PSU MB WH	No
16649600	ST320T LED20S/PW930 PSU NB BK	No
16651900	ST320T LED27S/PW930 PSU MB BK	No
16671700	ST320T LED39S/830 PSU VWB BK	No
16673100	ST320T LED39S/830 PSU WB BK	No
16677900	ST320T LED39S/840 PSU WB BK	No
16680900	ST320T LED39S/PW930 PSU WB BK	No
40338600	ST320T LED49S/830 PSD-VLC MB BK	Yes
40339300	ST320T LED49S/840 PSU WB BK	No
16659500	ST320T LED27S/830 PSU MB SI	No
16664900	ST320T LED27S/PW930 PSU MB SI	No
16665600	ST320T LED20S/PW930 PSU NB SI	No
16667000	ST320T LED27S/PW930 PSU WB SI	No
16672400	ST320T LED39S/830 PSU VWB SI	No
16674800	ST320T LED39S/830 PSU WB SI	No
16678600	ST320T LED39S/840 PSU WB SI	No
16681600	ST320T LED39S/PW930 PSU WB SI	No
40340900	ST320T LED49S/840 PSD-VLC WB SI	Yes

General Information (1/2)

Order Code	Full Product Name	Cap-Base	Protection class IEC	Optical cover/ lens type	Lamp family code
16648900	ST320T LED19S/FMT PSU MB WH	-	Safety class II (II)	PM	LED19

Order Code	Full Product Name	Cap-Base	Protection class IEC	Optical cover/ lens type	Lamp family code
16650200	ST320T LED27S/PW930 PSU MB WH	-	Safety class II (II)	PM	LED27

GreenSpace Accent Projector

Order Code	Full Product Name	Cap-Base	Protection class IEC	Optical cover/ lens type	Lamp family code
16652600	ST320T LED17S/827 PSU MB WH	-	-	PM	LED17
16653300	ST320T LED17S/830 PSU MB WH	-	Safety class II (II)	PM	LED17
16654000	ST320T LED17S/840 PSU MB WH	-	Safety class II (II)	PM	LED17
16655700	ST320T LED17S/CRW PSU MB WH	-	Safety class II (II)	PM	LED17
16656400	ST320T LED17S/PW930 PSU MB WH	-	Safety class II (II)	PM	LED17
16658800	ST320T LED27S/827 PSU MB WH	-	Safety class II (II)	PM	LED27
16660100	ST320T LED27S/830 PSU MB WH	-	Safety class II (II)	PM	LED27
16661800	ST320T LED27S/840 PSU MB WH	-	Safety class II (II)	PM	LED27
16662500	ST320T LED27S/840 PSU WB WH	-	Safety class II (II)	PM	LED27
16663200	ST320T LED27S/CRW PSU MB WH	-	Safety class II (II)	PM	LED27
16666300	ST320T LED20S/PW930 PSU NB WH	-	Safety class II (II)	G	LED20
16668700	ST320T LED39S/827 PSU VWB WH	-	Safety class II (II)	PM	LED39
16669400	ST320T LED39S/827 PSU WB WH	-	Safety class II (II)	PM	LED39
16670000	ST320T LED39S/830 PSU VWB WH	-	Safety class II (II)	PM	LED39
16675500	ST320T LED39S/830 PSU WB WH	-	Safety class II (II)	PM	LED39
16676200	ST320T LED39S/840 PSU VWB WH	-	Safety class II (II)	PM	LED39
16679300	ST320T LED39S/840 PSU WB WH	-	Safety class II (II)	PM	LED39
16682300	ST320T LED39S/PW930 PSU WB WH	-	Safety class II (II)	PM	LED39
39939900	ST320T LED17S/CH PSU WB WH	-	Safety class II (II)	PM	LED17
40335500	ST320T LED49S/830 PSU MB WH	-	Safety class II (II)	PM	LED49S

Order Code	Full Product Name	Cap-Base	Protection class IEC	Optical cover/ lens type	Lamp family code
40336200	ST320T LED49S/827 PSD-VLC MB WH	-	Safety class II (II)	PM	LED49S
40337900	ST320T LED49S/827 PSU MB WH	-	Safety class II (II)	PM	LED49S
16649600	ST320T LED20S/PW930 PSU NB BK	-	Safety class II (II)	G	LED20
16651900	ST320T LED27S/PW930 PSU MB BK	-	Safety class II (II)	PM	LED27
16671700	ST320T LED39S/830 PSU VWB BK	-	Safety class II (II)	PM	LED39
16673100	ST320T LED39S/830 PSU WB BK	-	Safety class II (II)	PM	LED39
16677900	ST320T LED39S/840 PSU WB BK	-	Safety class II (II)	PM	LED39
16680900	ST320T LED39S/PW930 PSU WB BK	-	Safety class II (II)	PM	LED39
40338600	ST320T LED49S/830 PSD-VLC MB BK	-	Safety class II (II)	PM	LED49S
40339300	ST320T LED49S/840 PSU WB BK	-	Safety class II (II)	PM	LED49S
16659500	ST320T LED27S/830 PSU MB SI	-	Safety class II (II)	PM	LED27
16664900	ST320T LED27S/PW930 PSU MB SI	-	Safety class II (II)	PM	LED27
16665600	ST320T LED20S/PW930 PSU NB SI	-	Safety class II (II)	G	LED20
16667000	ST320T LED27S/PW930 PSU WB SI	-	Safety class II (II)	PM	LED27
16672400	ST320T LED39S/830 PSU VWB SI	-	Safety class II (II)	PM	LED39
16674800	ST320T LED39S/830 PSU WB SI	-	Safety class II (II)	PM	LED39
16678600	ST320T LED39S/840 PSU WB SI	-	Safety class II (II)	PM	LED39
16681600	ST320T LED39S/PW930 PSU WB SI	-	Safety class II (II)	PM	LED39
40340900	ST320T LED49S/840 PSD-VLC WB SI	-	Safety class II (II)	PM	LED49S

General Information (2/2)

Order Code	Full Product Name	Number of light sources	Optic type	UL mark
16648900	ST320T LED19S/FMT PSU MB WH	1	MB	-
16650200	ST320T LED27S/PW930 PSU MB WH	1	MB	-
16652600	ST320T LED17S/827 PSU MB WH	1	MB	-
16653300	ST320T LED17S/830 PSU MB WH	1	MB	-
16654000	ST320T LED17S/840 PSU MB WH	1	MB	-

Order Code	Full Product Name	Number of light sources	Optic type	UL mark
16655700	ST320T LED17S/CRW PSU MB WH	1	MB	-
16656400	ST320T LED17S/PW930 PSU MB WH	1	MB	-
16658800	ST320T LED27S/827 PSU MB WH	1	MB	-
16660100	ST320T LED27S/830 PSU MB WH	1	MB	-
16661800	ST320T LED27S/840 PSU MB WH	1	MB	-

GreenSpace Accent Projector

Order Code	Full Product Name	Number of light sources	Optic type	UL mark
16662500	ST320T LED27S/840 PSU WB WH	1	WB	-
16663200	ST320T LED27S/CRW PSU MB WH	1	MB	-
16666300	ST320T LED20S/PW930 PSU NB WH	1	NB	-
16668700	ST320T LED39S/827 PSU VWB WH	1	VWB	-
16669400	ST320T LED39S/827 PSU WB WH	1	WB	-
16670000	ST320T LED39S/830 PSU VWB WH	1	VWB	-
16675500	ST320T LED39S/830 PSU WB WH	1	WB	-
16676200	ST320T LED39S/840 PSU VWB WH	1	VWB	-
16679300	ST320T LED39S/840 PSU WB WH	1	WB	-
16682300	ST320T LED39S/PW930 PSU WB WH	1	WB	-
39939900	ST320T LED17S/CH PSU WB WH	-	WB	-
40335500	ST320T LED49S/830 PSU MB WH	-	MB	-
40336200	ST320T LED49S/827 PSD-VLC MB WH	-	MB	-
40337900	ST320T LED49S/827 PSU MB WH	-	MB	-
16649600	ST320T LED20S/PW930 PSU NB BK	1	NB	-

Order Code	Full Product Name	Number of light sources	Optic type	UL mark
16651900	ST320T LED27S/PW930 PSU MB BK	1	MB	-
16671700	ST320T LED39S/830 PSU VWB BK	1	VWB	-
16673100	ST320T LED39S/830 PSU WB BK	1	WB	-
16677900	ST320T LED39S/840 PSU WB BK	1	WB	-
16680900	ST320T LED39S/PW930 PSU WB BK	1	WB	-
40338600	ST320T LED49S/830 PSD-VLC MB BK	-	MB	-
40339300	ST320T LED49S/840 PSU WB BK	-	WB	-
16659500	ST320T LED27S/830 PSU MB SI	1	MB	-
16664900	ST320T LED27S/PW930 PSU MB SI	1	MB	-
16665600	ST320T LED20S/PW930 PSU NB SI	1	NB	-
16667000	ST320T LED27S/PW930 PSU WB SI	1	WB	-
16672400	ST320T LED39S/830 PSU VWB SI	1	VWB	-
16674800	ST320T LED39S/830 PSU WB SI	1	WB	-
16678600	ST320T LED39S/840 PSU WB SI	1	WB	-
16681600	ST320T LED39S/PW930 PSU WB SI	1	WB	-
40340900	ST320T LED49S/840 PSD-VLC WB SI	-	WB	-

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Temperature	Init. Colour Rendering Index	Initial LED luminaire efficacy
16648900	ST320T LED19S/F MT PSU MB WH	(0.40, 0.33)	3000 K	≥85	70.37037037037037 lm/W
16650200	ST320T LED27S/PW930 PSU MB WH	(0.42, 0.39)	3000 K	≥90	105.88235294117646 lm/W
16652600	ST320T LED17S/8 27 PSU MB WH	(0.46, 0.41)	2700 K	≥80	114.58333333333333 lm/W
16653300	ST320T LED17S/8 30 PSU MB WH	(0.43, 0.40)	3000 K	≥80	118.05555555555556 lm/W
16654000	ST320T LED17S/8 40 PSU MB WH	(0.38, 0.38)	4000 K	≥80	125 lm/W
16655700	ST320T LED17S/C RW PSU MB WH	(0.43, 0.40)	3000 K	≥95	66.66666666666667 lm/W
16656400	ST320T LED17S/PW930	(0.42, 0.39)	3000 K	≥90	102.40963855421685 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Temperature	Init. Colour Rendering Index	Initial LED luminaire efficacy
16651900	ST320T LED27S/PW930 PSU MB BK	(0.46, 0.41)	2700 K	≥80	110.63829787234043 lm/W
16658800	ST320T LED27S/8 27 PSU MB WH	(0.43, 0.40)	3000 K	≥80	114.8936170212766 lm/W
16660100	ST320T LED27S/8 30 PSU MB WH	(0.38, 0.38)	4000 K	≥80	119.14893617021276 lm/W
16661800	ST320T LED27S/8 40 PSU MB WH	(0.38, 0.38)	4000 K	≥80	119.14893617021276 lm/W
16662500	ST320T LED27S/8 40 PSU WB WH	(0.43, 0.40)	3000 K	≥95	67.5 lm/W
16663200	ST320T LED27S/C RW PSU MB WH	(0.42, 0.39)	3000 K	≥90	93.02325581395348 lm/W
16666300	ST320T LED20S/PW930 PSU NB WH	(0.42, 0.39)	3000 K	≥90	93.02325581395348 lm/W

GreenSpace Accent Projector

Order Code	Full Product		Init. Corr. Colour Temperature	Init. Colour Rendering		Initial LED luminaire efficacy
	Name	Initial chromaticity		Index	Initial LED luminaire efficacy	
16668700	ST320T LED39S/8 27 PSU VWB WH	(0.46, 0.41) SDCM<3	2700 K	≥80	119.04761904761905 lm/W	
16669400	ST320T LED39S/8 27 PSU WB WH	(0.46, 0.41) SDCM<3	2700 K	≥80	119.04761904761905 lm/W	
16670000	ST320T LED39S/8 30 PSU VWB WH	(0.43, 0.40) SDCM<3	3000 K	≥80	123.80952380952381 lm/W	
16675500	ST320T LED39S/8 30 PSU WB WH	(0.43, 0.40) SDCM<3	3000 K	≥80	123.80952380952381 lm/W	
16676200	ST320T LED39S/8 40 PSU VWB WH	(0.38, 0.38) SDCM<3	4000 K	≥80	120.63492063492063 lm/W	
16679300	ST320T LED39S/8 40 PSU WB WH	(0.38, 0.38) SDCM<3	4000 K	≥80	120.63492063492063 lm/W	
16682300	ST320T LED39S/ PW930 PSU WB WH	(0.42, 0.39) SDCM<3	3000 K	≥90	101.2987012987013 lm/W	
39939900	ST320T LED17S/C H PSU WB WH	(0.46, 0.39) SDCM<3	2700 K	≥90	114.58333333333333 lm/W	
40335500	ST320T LED49S/8 30 PSU MB WH	(0.43, 0.40) SDCM<3	3000 K	≥80	122.5 lm/W	
40336200	ST320T LED49S/8 27 PSD- VLC MB WH	(0.45, 0.41) SDCM<3	2700 K	≥80	118.75 lm/W	
40337900	ST320T LED49S/8 27 PSU MB WH	(0.45, 0.41) SDCM<3	2700 K	≥80	118.75 lm/W	
16649600	ST320T LED20S/ PW930	(0.42, 0.39) SDCM<3	3000 K	≥90	93.02325581395348 lm/W	

Order Code	Full Product		Init. Corr. Colour Temperature	Init. Colour Rendering		Initial LED luminaire efficacy
	Name	Initial chromaticity		Index	Initial LED luminaire efficacy	
	PSU NB BK					
16651900	ST320T LED27S/ PW930 PSU MB BK	(0.42, 0.39) SDCM<3	3000 K	≥90	105.88235294117646 lm/W	
16671700	ST320T LED39S/8 30 PSU VWB BK	(0.43, 0.40) SDCM<3	3000 K	≥80	123.80952380952381 lm/W	
16673100	ST320T LED39S/8 30 PSU WB BK	(0.43, 0.40) SDCM<3	3000 K	≥80	123.80952380952381 lm/W	
16677900	ST320T LED39S/8 40 PSU WB BK	(0.38, 0.38) SDCM<3	4000 K	≥80	120.63492063492063 lm/W	
16680900	ST320T LED39S/ PW930 PSU WB BK	(0.42, 0.39) SDCM<3	3000 K	≥90	101.2987012987013 lm/W	
40338600	ST320T LED49S/8 30 PSD- VLC MB BK	(0.43, 0.40) SDCM<3	3000 K	≥80	122.5 lm/W	
40339300	ST320T LED49S/8 40 PSU WB BK	(0.38, 0.38) SDCM<3	4000 K	≥80	128.75 lm/W	
16659500	ST320T LED27S/8 30 PSU MB SI	(0.43, 0.40) SDCM<3	3000 K	≥80	114.8936170212766 lm/W	
16664900	ST320T LED27S/ PW930 PSU MB SI	(0.42, 0.39) SDCM<3	3000 K	≥90	105.88235294117646 lm/W	
16665600	ST320T LED20S/ PW930 PSU NB SI	(0.42, 0.39) SDCM<3	3000 K	≥90	93.02325581395348 lm/W	
16667000	ST320T LED27S/ PW930	(0.42, 0.39) SDCM<3	3000 K	≥90	105.88235294117646 lm/W	

GreenSpace Accent Projector

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Init. Colour	
				Rendering Index	Initial LED luminaire efficacy
	PSU WB SI				
16672400	ST320T LED39S/8 SDCM<3 30 PSU VWB SI	(0.43, 0.40)	3000 K	≥80	123.80952380952381 lm/W
16674800	ST320T LED39S/8 SDCM<3 30 PSU WB SI	(0.43, 0.40)	3000 K	≥80	123.80952380952381 lm/W
16678600	ST320T LED39S/8 SDCM<3 40 PSU WB SI	(0.38, 0.38)	4000 K	≥80	120.63492063492063 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Init. Colour	
				Rendering Index	Initial LED luminaire efficacy
16681600	ST320T LED39S/ SDCM<3 PW930 PSU WB SI	(0.42, 0.39)	3000 K	≥90	101.2987012987013 lm/W
40340900	ST320T LED49S/8 SDCM<3 40 PSD-VLC WB SI	(0.38, 0.38)	4000 K	≥80	128.75 lm/W

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial luminous flux	Initial input power
16648900	ST320T LED19S/FMT PSU MB WH	1900 lm	27 W
16650200	ST320T LED27S/PW930 PSU MB WH	2700 lm	25.5 W
16652600	ST320T LED17S/827 PSU MB WH	1650 lm	14.4 W
16653300	ST320T LED17S/830 PSU MB WH	1700 lm	14.4 W
16654000	ST320T LED17S/840 PSU MB WH	1800 lm	14.4 W
16655700	ST320T LED17S/CRW PSU MB WH	1700 lm	25.5 W
16656400	ST320T LED17S/PW930 PSU MB WH	1700 lm	16.6 W
16658800	ST320T LED27S/827 PSU MB WH	2600 lm	23.5 W
16660100	ST320T LED27S/830 PSU MB WH	2700 lm	23.5 W
16661800	ST320T LED27S/840 PSU MB WH	2800 lm	23.5 W
16662500	ST320T LED27S/840 PSU WB WH	2800 lm	23.5 W
16663200	ST320T LED27S/CRW PSU MB WH	2700 lm	40 W
16666300	ST320T LED20S/PW930 PSU NB WH	2000 lm	21.5 W
16668700	ST320T LED39S/827 PSU VWB WH	3750 lm	31.5 W
16669400	ST320T LED39S/827 PSU WB WH	3750 lm	31.5 W
16670000	ST320T LED39S/830 PSU VWB WH	3900 lm	31.5 W
16675500	ST320T LED39S/830 PSU WB WH	3900 lm	31.5 W
16676200	ST320T LED39S/840 PSU VWB WH	3800 lm	31.5 W
16679300	ST320T LED39S/840 PSU WB WH	3800 lm	31.5 W
16682300	ST320T LED39S/PW930 PSU WB WH	3900 lm	38.5 W
39939900	ST320T LED17S/CH PSU WB WH	1650 lm	14.4 W
40335500	ST320T LED49S/830 PSU MB WH	4900 lm	40 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
40336200	ST320T LED49S/827 PSD-VLC MB WH	4750 lm	40 W
40337900	ST320T LED49S/827 PSU MB WH	4750 lm	40 W
16649600	ST320T LED20S/PW930 PSU NB BK	2000 lm	21.5 W
16651900	ST320T LED27S/PW930 PSU MB BK	2700 lm	25.5 W
16671700	ST320T LED39S/830 PSU VWB BK	3900 lm	31.5 W
16673100	ST320T LED39S/830 PSU WB BK	3900 lm	31.5 W
16677900	ST320T LED39S/840 PSU WB BK	3800 lm	31.5 W
16680900	ST320T LED39S/PW930 PSU WB BK	3900 lm	38.5 W
40338600	ST320T LED49S/830 PSD-VLC MB BK	4900 lm	40 W
40339300	ST320T LED49S/840 PSU WB BK	5150 lm	40 W
16659500	ST320T LED27S/830 PSU MB SI	2700 lm	23.5 W
16664900	ST320T LED27S/PW930 PSU MB SI	2700 lm	25.5 W
16665600	ST320T LED20S/PW930 PSU NB SI	2000 lm	21.5 W
16667000	ST320T LED27S/PW930 PSU WB SI	2700 lm	25.5 W
16672400	ST320T LED39S/830 PSU VWB SI	3900 lm	31.5 W
16674800	ST320T LED39S/830 PSU WB SI	3900 lm	31.5 W
16678600	ST320T LED39S/840 PSU WB SI	3800 lm	31.5 W
16681600	ST320T LED39S/PW930 PSU WB SI	3900 lm	38.5 W
40340900	ST320T LED49S/840 PSD-VLC WB SI	5150 lm	40 W

Mechanical and Housing

Order Code	Full Product Name	Colour
16648900	ST320T LED19S/FMT PSU MB WH	White
16650200	ST320T LED27S/PW930 PSU MB WH	White

Order Code	Full Product Name	Colour
16652600	ST320T LED17S/827 PSU MB WH	White
16653300	ST320T LED17S/830 PSU MB WH	White

GreenSpace Accent Projector

Order Code	Full Product Name	Colour
16654000	ST320T LED17S/840 PSU MB WH	White
16655700	ST320T LED17S/CRW PSU MB WH	White
16656400	ST320T LED17S/PW930 PSU MB WH	White
16658800	ST320T LED27S/827 PSU MB WH	White
16660100	ST320T LED27S/830 PSU MB WH	White
16661800	ST320T LED27S/840 PSU MB WH	White
16662500	ST320T LED27S/840 PSU WB WH	White
16663200	ST320T LED27S/CRW PSU MB WH	White
16666300	ST320T LED20S/PW930 PSU NB WH	White
16668700	ST320T LED39S/827 PSU VWB WH	White
16669400	ST320T LED39S/827 PSU WB WH	White
16670000	ST320T LED39S/830 PSU VWB WH	White
16675500	ST320T LED39S/830 PSU WB WH	White
16676200	ST320T LED39S/840 PSU VWB WH	White
16679300	ST320T LED39S/840 PSU WB WH	White
16682300	ST320T LED39S/PW930 PSU WB WH	White
39939900	ST320T LED17S/CH PSU WB WH	White
40335500	ST320T LED49S/830 PSU MB WH	White
40336200	ST320T LED49S/827 PSD-VLC MB WH	White

Order Code	Full Product Name	Colour
40337900	ST320T LED49S/827 PSU MB WH	White
16649600	ST320T LED20S/PW930 PSU NB BK	Black
16651900	ST320T LED27S/PW930 PSU MB BK	Black
16671700	ST320T LED39S/830 PSU VWB BK	Black
16673100	ST320T LED39S/830 PSU WB BK	Black
16677900	ST320T LED39S/840 PSU WB BK	Black
16680900	ST320T LED39S/PW930 PSU WB BK	Black
40338600	ST320T LED49S/830 PSD-VLC MB BK	Black
40339300	ST320T LED49S/840 PSU WB BK	Black
16659500	ST320T LED27S/830 PSU MB SI	Silver
16664900	ST320T LED27S/PW930 PSU MB SI	Silver
16665600	ST320T LED20S/PW930 PSU NB SI	Silver
16667000	ST320T LED27S/PW930 PSU WB SI	Silver
16672400	ST320T LED39S/830 PSU VWB SI	Silver
16674800	ST320T LED39S/830 PSU WB SI	Silver
16678600	ST320T LED39S/840 PSU WB SI	Silver
16681600	ST320T LED39S/PW930 PSU WB SI	Silver
40340900	ST320T LED49S/840 PSD-VLC WB SI	Silver

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
16648900	ST320T LED19S/FMT PSU MB WH	-	-
16650200	ST320T LED27S/PW930 PSU MB WH	-	-
16652600	ST320T LED17S/827 PSU MB WH	-	-
16653300	ST320T LED17S/830 PSU MB WH	-	-
16654000	ST320T LED17S/840 PSU MB WH	-	-
16655700	ST320T LED17S/CRW PSU MB WH	-	-
16656400	ST320T LED17S/PW930 PSU MB WH	-	-
16658800	ST320T LED27S/827 PSU MB WH	-	-
16660100	ST320T LED27S/830 PSU MB WH	-	-
16661800	ST320T LED27S/840 PSU MB WH	-	-
16662500	ST320T LED27S/840 PSU WB WH	-	-
16663200	ST320T LED27S/CRW PSU MB WH	-	-
16666300	ST320T LED20S/PW930 PSU NB WH	-	-
16668700	ST320T LED39S/827 PSU VWB WH	-	-
16669400	ST320T LED39S/827 PSU WB WH	-	-
16670000	ST320T LED39S/830 PSU VWB WH	-	-
16675500	ST320T LED39S/830 PSU WB WH	-	-
16676200	ST320T LED39S/840 PSU VWB WH	-	-
16679300	ST320T LED39S/840 PSU WB WH	-	-
16682300	ST320T LED39S/PW930 PSU WB WH	-	-
39939900	ST320T LED17S/CH PSU WB WH	-	-

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
40335500	ST320T LED49S/830 PSU MB WH	50000 h	25000 h
40336200	ST320T LED49S/827 PSD-VLC MB WH	50000 h	25000 h
40337900	ST320T LED49S/827 PSU MB WH	50000 h	25000 h
16649600	ST320T LED20S/PW930 PSU NB BK	-	-
16651900	ST320T LED27S/PW930 PSU MB BK	-	-
16671700	ST320T LED39S/830 PSU VWB BK	-	-
16673100	ST320T LED39S/830 PSU WB BK	-	-
16677900	ST320T LED39S/840 PSU WB BK	-	-
16680900	ST320T LED39S/PW930 PSU WB BK	-	-
40338600	ST320T LED49S/830 PSD-VLC MB BK	50000 h	25000 h
40339300	ST320T LED49S/840 PSU WB BK	50000 h	25000 h
16659500	ST320T LED27S/830 PSU MB SI	-	-
16664900	ST320T LED27S/PW930 PSU MB SI	-	-
16665600	ST320T LED20S/PW930 PSU NB SI	-	-
16667000	ST320T LED27S/PW930 PSU WB SI	-	-
16672400	ST320T LED39S/830 PSU VWB SI	-	-
16674800	ST320T LED39S/830 PSU WB SI	-	-
16678600	ST320T LED39S/840 PSU WB SI	-	-
16681600	ST320T LED39S/PW930 PSU WB SI	-	-
40340900	ST320T LED49S/840 PSD-VLC WB SI	50000 h	25000 h

GreenSpace Accent Projector

