



T12 Linear fluorescent lighting

T12 Standard

Low-pressure mercury discharge lamps with a tubular 37 mm envelope

Benefits

- Provides highly reliable and high-quality lighting solution at low costStandard colours with moderate colour rendering

Features

- Standard colours with moderate colour rendering (Ra 50 - 75)
- Low-pressure mercury discharge lamps with a tubular 37 mm envelope

Application


- Mostly used in applications where continuous light output is required and colour rendering is not an important factor.

Versions



T12 Standard

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F40T12/54-765 1SL/25	40.5 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

