



T12 Linear fluorescent lighting

T12 Standard

Low-pressure mercury discharge lamps with a tubular 37 mm envelope

Benefits

- Provides highly reliable and high-quality lighting solution at low costStandard colors with moderate color rendering

Features

- Standard colors with moderate color rendering (Ra 50 - 75)
- Low-pressure mercury discharge lamps with a tubular 37 mm envelope

Application

- Mostly used in applications where continuous light output is required and color rendering is not an important factor.

Versions




G13, T12

G13, T12

T12 Standard

Dimensional drawing



General Information	
Cap-Base	G13
System Description	Rapid Start (RS)
Light Technical	
Color Code	54-765
Color Designation	Daylight
Correlated Color Temperature (Nom)	6500 K
Color Rendering Index (Nom)	73
Mechanical and Housing	
Bulb Shape	T12

Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
226472	TL-RS 20W/54-765 30PK 30/1	1.7 mg

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
226480	TL-RS 40W/54-765 30PK 30/1	4.4 mg

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
226472	TL-RS 20W/54-765 30PK 30/1	20 W

Order Code	Full Product Name	Power (Rated) (Nom)
226480	TL-RS 40W/54-765 30PK 30/1	40 W

General Information

Order Code	Full Product Name	Life With 3 Hour Per	
		Life 3-Hr Start [Hrs]	Day Use
226472	TL-RS 20W/54-765 30PK 30/1	9000 h	4 a
226480	TL-RS 40W/54-765 30PK 30/1	20000 h	7 a

Light Technical

Order Code	Full Product Name	Design Mean	
		Lumens	Luminous Flux (Nom)
226472	TL-RS 20W/54-765 30PK 30/1	960 lm	1075 lm

Order Code	Full Product Name	Design Mean	
		Lumens	Luminous Flux (Nom)
226480	TL-RS 40W/54-765 30PK 30/1	2250 lm	2600 lm

T12 Standard

