



# LuxSpace recessed – high efficiency, visual comfort and a stylish design

## LuxSpace Mini, recessed

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

### Benefits

- Best-in-class efficacy
- Creates a gentle, natural light, ensuring visual comfort
- Perfect integration with the ceiling thanks to the thin, narrow rim; rimless version ideal for integration into plaster ceilings

# LuxSpace Mini, recessed

## Features

- Choice of four optics: high-gloss, faceted, matt and white
- Heights: deep (up to UGR 19), low (up to UGR 22)
- Rim colors: high-gloss metalized, white (RAL9003), grey, black (RAL9004) as standard (any other RAL color possible upon request)
- Rimless version available
- Light color: 830, 840, 927, 930 and 940 (CRI90 versions upon request)
- Compliant for central emergency lighting with DC (upon request)
- Multiple additional options: PG and PGO (IP54 front face), emergency lighting (single battery 3 hours), through-wiring, Eca and B2ca cable & connector options

## Application

- Offices
- Retail
- Hospitals
- Hotels
- Airports

## Specifications

<b>Type</b>	DN560B (low height recessed version) DN561B (deep recessed version)
<b>Ceiling type</b>	Plaster (board) ceiling
<b>Light source</b>	Non replaceable LED module
<b>Power</b>	8 or 11.2 W (depending on configuration)
<b>Luminous flux</b>	780 to 1200 lm (depending on configuration)
<b>Correlated Color</b>	2700, 3000 or 4000 K
<b>Temperature</b>	
<b>Color Rendering Index</b>	> 80 90 (available in 3000 K)
<b>Lumen maintenance at median useful life*</b>	L90
<b>50000 h</b>	
<b>Control gear failure rate at median useful life</b>	5%
<b>50000 h</b>	
<b>Performance Ambient Temperature Tq</b>	+25 °C
<b>Operating temperature range</b>	+10 to +40 °C
<b>Driver</b>	Separate

<b>Mains voltage</b>	230 or 240 V / 50-60 Hz
<b>Dimming</b>	DALI dimming possible (PSED-E)
<b>Options</b>	Emergency lighting 3 hours (EL3) Protection glass (PG or PGO, IP54 front face) Through-wiring Rimless version for plaster ceiling Suspended glasses: opal (SG-O), frosted circle (SG-FRC) and frosted halo ring (SG-HR-FR) External or plug-in 3-pole Wieland/Adels connector
<b>Material</b>	Housing and rim: aluminum Reflector: plastic, aluminum coated (for high-gloss and faceted optics)
<b>Color</b>	Rim: white (RAL 9010), grey (similar to RAL 9006), black (RAL 9005) or high-gloss metalized
<b>Optic</b>	High-gloss mirror (C) Matt mirror (M) Faceted reflector (F) White reflector (WR)
<b>Connection</b>	Push-in connector or with pull relief
<b>Installation</b>	Fixation by means of spring fasteners
<b>Remarks</b>	External driver included

# LuxSpace Mini, recessed

## Versions




LuxSpace Mini recessed DN560B  
downlight with high-gloss optic



LuxSpace Mini recessed DN560B  
downlight with faceted optic



LuxSpace Mini recessed DN560B  
downlight with matt optic



LuxSpace Mini recessed DN560B  
downlight with white optic



LuxSpace Mini recessed DN561B  
downlight with high-gloss optic



LuxSpace Mini recessed DN561B  
downlight with faceted optic




LuxSpace Mini recessed DN561B  
downlight with white optic

# LuxSpace Mini, recessed

## Product details



LuxSpace Mini recessed DN560B  
downlight with high-gloss optic,  
black version



LuxSpace Mini recessed DN560B  
downlight with high-gloss optic,  
grey version




IPPR1 DN560Bi 0041



IPPR1 DN560Bi 0025

## Accessories



Protection glass

Ordercode 910503706523



Protection glass, opal

Ordercode 910503706524

## LuxSpace Mini, recessed

### Application Conditions

Ambient temperature range	+10 to +25 °C
Suitable for random switching	Yes

### Approval and Application

Mech. impact protection code	IK02
------------------------------	------

### Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

### General Information

Cap-Base	-
CE mark	CE mark
Protection class IEC	Safety class II
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Gear	-
Glow-wire test	Temperature 850 °C, duration 5 s
Light source replaceable	No
Number of gear units	1 unit
UL mark	-

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

### Application Conditions

Order Code	Full Product Name	Maximum dim level
910503586404	DN560B LED12S/830 PSU-E C WH	-
910503586405	DN560B LED12S/840 PSU-E C WH	-
910503586406	DN560B LED12S/830 PSD-VLC-E C WH	1%
910503586407	DN560B LED12S/840 PSD-VLC-E C WH	1%
910503586428	DN560B LED12S/830 PSU-E C PG WH	-
910503586429	DN560B LED12S/830 PSD-VLC-E C PG WH	1%
910503586432	DN560B LED12S/830 PSU-E C WH	-
910503586436	DN560B LED12S/830 PSD-VLC-E C WH	1%
910503706506	DN560B LED8S/830 PSU-E C WH	-
910503706507	DN560B LED8S/840 PSU-E C WH	-
910503706508	DN560B LED8S/830 PSD-VLC-E C WH	1%
910503706509	DN560B LED8S/840 PSD-VLC-E C WH	1%
910503706529	DN560B LED12S/930 PSU-E C WH	-
910503706682	DN560B LED12S/830 PSU-E C ELP3 WH	-
910503586408	DN560B LED12S/830 PSU-E F WH	-
910503586409	DN560B LED12S/840 PSU-E F WH	-
910503586410	DN560B LED12S/830 PSD-VLC-E F WH	1%
910503586411	DN560B LED12S/840 PSD-VLC-E F WH	1%
910503586430	DN560B LED12S/830 PSE-E F PG WH	-
910503586431	DN560B LED12S/830 PSED-VLC-E F PG WH	1%
910503706512	DN560B LED8S/830 PSD-VLC-E F WH	1%
910503706513	DN560B LED8S/840 PSD-VLC-E F WH	1%
910503586412	DN560B LED12S/830 PSU-E M WH	-
910503586414	DN560B LED12S/830 PSU-E WR WH	-
910503586441	DN561B LED12S/830 PSU-E C WH	-
910503586442	DN561B LED12S/840 PSU-E C WH	-
910503586443	DN561B LED12S/830 PSD-VLC-E C WH	1%
910503586444	DN561B LED12S/840 PSD-VLC-E C WH	1%
910503586465	DN561B LED12S/830 PSE-E C PG WH	-
910503586466	DN561B LED12S/830 PSED-VLC-E C PG WH	1%
910503706514	DN561B LED8S/830 PSU-E C WH	-
910503706515	DN561B LED8S/840 PSU-E C WH	-
910503706516	DN561B LED8S/830 PSD-VLC-E C WH	1%
910503706517	DN561B LED8S/840 PSD-VLC-E C WH	1%
910503586445	DN561B LED12S/830 PSE-E F WH	-
910503586446	DN561B LED12S/840 PSU-E F WH	-
910503586447	DN561B LED12S/830 PSED-VLC-E F WH	1%
910503586448	DN561B LED12S/840 PSD-VLC-E F WH	1%
910503586467	DN561B LED12S/830 PSE-E F PG WH	-
910503586468	DN561B LED12S/830 PSED-VLC-E F PG WH	1%
910503706518	DN561B LED8S/830 PSU-E F WH	-
910503586451	DN561B LED12S/830 PSU-E WR WH	-

### Approval and Application

Order Code	Full Product Name	Ingress protection code	Order Code	Full Product Name	Ingress protection code
910503586404	DN560B LED12S/830 PSU-E C WH	IP20	910503586428	DN560B LED12S/830 PSU-E C PG WH	IP20/54
910503586405	DN560B LED12S/840 PSU-E C WH	IP20	910503586429	DN560B LED12S/830 PSD-VLC-E C PG WH	IP20/54
910503586406	DN560B LED12S/830 PSD-VLC-E C WH	IP20	910503586432	DN560B LED12S/830 PSU-E C WH	IP20
910503586407	DN560B LED12S/840 PSD-VLC-E C WH	IP20	910503586436	DN560B LED12S/830 PSD-VLC-E C WH	IP20

## LuxSpace Mini, recessed

Order Code	Full Product Name	Ingress protection code
910503706506	DN560B LED8S/830 PSU-E C WH	IP20
910503706507	DN560B LED8S/840 PSU-E C WH	IP20
910503706508	DN560B LED8S/830 PSD-VLC-E C WH	IP20
910503706509	DN560B LED8S/840 PSD-VLC-E C WH	IP20
910503706529	DN560B LED12S/930 PSU-E C WH	IP20
910503706682	DN560B LED12S/830 PSU-E C ELP3 WH	IP20
910503586408	DN560B LED12S/830 PSU-E F WH	IP20
910503586409	DN560B LED12S/840 PSU-E F WH	IP20
910503586410	DN560B LED12S/830 PSD-VLC-E F WH	IP20
910503586411	DN560B LED12S/840 PSD-VLC-E F WH	IP20
910503586430	DN560B LED12S/830 PSE-E F PG WH	IP20/54
910503586431	DN560B LED12S/830 PSED-VLC-E F PG WH	IP20/54
910503706512	DN560B LED8S/830 PSD-VLC-E F WH	IP20
910503706513	DN560B LED8S/840 PSD-VLC-E F WH	IP20
910503586412	DN560B LED12S/830 PSU-E M WH	IP20
910503586414	DN560B LED12S/830 PSU-E WR WH	IP20
910503586441	DN561B LED12S/830 PSU-E C WH	IP20

Order Code	Full Product Name	Ingress protection code
910503586442	DN561B LED12S/840 PSU-E C WH	IP20
910503586443	DN561B LED12S/830 PSD-VLC-E C WH	IP20
910503586444	DN561B LED12S/840 PSD-VLC-E C WH	IP20
910503586465	DN561B LED12S/830 PSE-E C PG WH	IP20/54
910503586466	DN561B LED12S/830 PSED-VLC-E C PG WH	IP20/54
910503706514	DN561B LED8S/830 PSU-E C WH	IP20
910503706515	DN561B LED8S/840 PSU-E C WH	IP20
910503706516	DN561B LED8S/830 PSD-VLC-E C WH	IP20
910503706517	DN561B LED8S/840 PSD-VLC-E C WH	IP20
910503586445	DN561B LED12S/830 PSE-E F WH	IP20
910503586446	DN561B LED12S/840 PSU-E F WH	IP20
910503586447	DN561B LED12S/830 PSED-VLC-E F WH	IP20
910503586448	DN561B LED12S/840 PSD-VLC-E F WH	IP20
910503586467	DN561B LED12S/830 PSE-E F PG WH	IP20/54
910503586468	DN561B LED12S/830 PSED-VLC-E F PG WH	IP20/54
910503706518	DN561B LED8S/830 PSU-E F WH	IP20
910503586451	DN561B LED12S/830 PSU-E WR WH	IP20

### Controls and Dimming

Order Code	Full Product Name	Dimmable
910503586404	DN560B LED12S/830 PSU-E C WH	No
910503586405	DN560B LED12S/840 PSU-E C WH	No
910503586406	DN560B LED12S/830 PSD-VLC-E C WH	Yes
910503586407	DN560B LED12S/840 PSD-VLC-E C WH	Yes
910503586428	DN560B LED12S/830 PSU-E C PG WH	No
910503586429	DN560B LED12S/830 PSD-VLC-E C PG WH	Yes
910503586432	DN560B LED12S/830 PSU-E C WH	No
910503586436	DN560B LED12S/830 PSD-VLC-E C WH	Yes
910503706506	DN560B LED8S/830 PSU-E C WH	No
910503706507	DN560B LED8S/840 PSU-E C WH	No
910503706508	DN560B LED8S/830 PSD-VLC-E C WH	Yes
910503706509	DN560B LED8S/840 PSD-VLC-E C WH	Yes
910503706529	DN560B LED12S/930 PSU-E C WH	No
910503706682	DN560B LED12S/830 PSU-E C ELP3 WH	No
910503586408	DN560B LED12S/830 PSU-E F WH	No
910503586409	DN560B LED12S/840 PSU-E F WH	No
910503586410	DN560B LED12S/830 PSD-VLC-E F WH	Yes
910503586411	DN560B LED12S/840 PSD-VLC-E F WH	Yes
910503586430	DN560B LED12S/830 PSE-E F PG WH	No
910503586431	DN560B LED12S/830 PSED-VLC-E F PG WH	Yes
910503706512	DN560B LED8S/830 PSD-VLC-E F WH	Yes

Order Code	Full Product Name	Dimmable
910503706513	DN560B LED8S/840 PSD-VLC-E F WH	Yes
910503586412	DN560B LED12S/830 PSU-E M WH	No
910503586414	DN560B LED12S/830 PSU-E WR WH	No
910503586441	DN561B LED12S/830 PSU-E C WH	No
910503586442	DN561B LED12S/840 PSU-E C WH	No
910503586443	DN561B LED12S/830 PSD-VLC-E C WH	Yes
910503586444	DN561B LED12S/840 PSD-VLC-E C WH	Yes
910503586465	DN561B LED12S/830 PSE-E C PG WH	No
910503586466	DN561B LED12S/830 PSED-VLC-E C PG WH	Yes
910503706514	DN561B LED8S/830 PSU-E C WH	No
910503706515	DN561B LED8S/840 PSU-E C WH	No
910503706516	DN561B LED8S/830 PSD-VLC-E C WH	Yes
910503706517	DN561B LED8S/840 PSD-VLC-E C WH	Yes
910503586445	DN561B LED12S/830 PSE-E F WH	No
910503586446	DN561B LED12S/840 PSU-E F WH	No
910503586447	DN561B LED12S/830 PSED-VLC-E F WH	Yes
910503586448	DN561B LED12S/840 PSD-VLC-E F WH	Yes
910503586467	DN561B LED12S/830 PSE-E F PG WH	No
910503586468	DN561B LED12S/830 PSED-VLC-E F PG WH	Yes
910503706518	DN561B LED8S/830 PSU-E F WH	No
910503586451	DN561B LED12S/830 PSU-E WR WH	No

### General Information (1/2)

Order Code	Full Product Name	Optical			
		cover/lens type	Decorative accessories	Emergency lighting	ENEC mark
910503586404	DN560B LED12S/830 PSU-E C WH	-	-	-	ENEC mark

Order Code	Full Product Name	Optical			
		cover/lens type	Decorative accessories	Emergency lighting	ENEC mark
910503586405	DN560B LED12S/840 PSU-E C WH	-	-	-	ENEC mark

## LuxSpace Mini, recessed

Order Code	Full Product Name	Optical			
		cover/lens type	Decorative accessories	Emergency lighting	ENEC mark
910503586406	DN560B LED12S/830 PSD- VLC-E C WH	-	-	-	ENEC mark
910503586407	DN560B LED12S/840 PSD- VLC-E C WH	-	-	-	ENEC mark
910503586428	DN560B LED12S/830 PSU- E C PG WH	Protection glass	-	-	ENEC mark
910503586429	DN560B LED12S/830 PSD- VLC-E C PG WH	Protection glass	-	-	ENEC mark
910503586432	DN560B LED12S/830 PSU- E C WH	-	-	-	ENEC mark
910503586436	DN560B LED12S/830 PSD- VLC-E C WH	-	-	-	ENEC mark
910503706506	DN560B LED8S/830 PSU-E C WH	-	-	-	ENEC mark
910503706507	DN560B LED8S/840 PSU-E C WH	-	-	-	ENEC mark
910503706508	DN560B LED8S/830 PSD- VLC-E C WH	-	-	-	ENEC mark
910503706509	DN560B LED8S/840 PSD- VLC-E C WH	-	-	-	ENEC mark
910503706529	DN560B LED12S/930 PSU- E C WH	-	-	-	ENEC mark
910503706682	DN560B LED12S/830 PSU- E C ELP3 WH	-	-	Emergency lighting 3 hours duration Pro version	-
910503586408	DN560B LED12S/830 PSU- E F WH	-	-	-	ENEC mark
910503586409	DN560B LED12S/840 PSU- E F WH	-	-	-	ENEC mark
910503586410	DN560B LED12S/830 PSD- VLC-E F WH	-	-	-	ENEC mark
910503586411	DN560B LED12S/840 PSD- VLC-E F WH	-	-	-	ENEC mark

Order Code	Full Product Name	Optical			
		cover/lens type	Decorative accessories	Emergency lighting	ENEC mark
910503586430	DN560B LED12S/830 PSE- E F PG WH	Protection glass	-	-	ENEC mark
910503586431	DN560B LED12S/830 PSED-VLC-E F PG WH	Protection glass	-	-	ENEC mark
910503706512	DN560B LED8S/830 PSD- VLC-E F WH	-	-	-	ENEC mark
910503706513	DN560B LED8S/840 PSD- VLC-E F WH	-	-	-	ENEC mark
910503586412	DN560B LED12S/830 PSU- E M WH	-	-	-	ENEC mark
910503586414	DN560B LED12S/830 PSU- E WR WH	-	-	-	ENEC mark
910503586441	DN561B LED12S/830 PSU- E C WH	-	-	-	ENEC mark
910503586442	DN561B LED12S/840 PSU- E C WH	-	-	-	ENEC mark
910503586443	DN561B LED12S/830 PSD- VLC-E C WH	-	-	-	ENEC mark
910503586444	DN561B LED12S/840 PSD- VLC-E C WH	-	-	-	ENEC mark
910503586465	DN561B LED12S/830 PSE- E C PG WH	Protection glass	-	-	ENEC mark
910503586466	DN561B LED12S/830 PSED-VLC-E C PG WH	Protection glass	-	-	ENEC mark
910503706514	DN561B LED8S/830 PSU-E C WH	-	-	-	ENEC mark
910503706515	DN561B LED8S/840 PSU-E C WH	-	-	-	ENEC mark
910503706516	DN561B LED8S/830 PSD- VLC-E C WH	-	-	-	ENEC mark
910503706517	DN561B LED8S/840 PSD- VLC-E C WH	-	-	-	ENEC mark

## LuxSpace Mini, recessed

Order Code	Full Product Name	Optical				ENEC mark
		cover/lens type	Decorative accessories	Emergency lighting		
910503586445	DN561B LED12S/830 PSE- E F WH	-	-	-		ENEC mark
910503586446	DN561B LED12S/840 PSU- E F WH	-	-	-		ENEC mark
910503586447	DN561B LED12S/830 PSED-VLC-E F WH	-	-	-		ENEC mark
910503586448	DN561B LED12S/840 PSD- VLC-E F WH	-	-	-		ENEC mark

Order Code	Full Product Name	Optical				ENEC mark
		cover/lens type	Decorative accessories	Emergency lighting		
910503586467	DN561B LED12S/830 PSE- E F PG WH	Protection glass	-	-		ENEC mark
910503586468	DN561B LED12S/830 PSED-VLC-E F PG WH	Protection glass	-	-		ENEC mark
910503706518	DN561B LED8S/830 PSU-E F WH	-	-	-		ENEC mark
910503586451	DN561B LED12S/830 PSU- E WR WH	-	-	-		ENEC mark

### General Information (2/2)

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product	
					Family Code	Service tag
910503586404	DN560B LED12S/830 PSU-E C WH	LED12S	1 pc	High-gloss mirror	DN560B	Yes
910503586405	DN560B LED12S/840 PSU-E C WH	LED12S	1 pc	High-gloss mirror	DN560B	Yes
910503586406	DN560B LED12S/830 PSD-VLC-E C WH	LED12S	1 pc	High-gloss mirror	DN560B	Yes
910503586407	DN560B LED12S/840 PSD-VLC-E C WH	LED12S	1 pc	High-gloss mirror	DN560B	Yes
910503586428	DN560B LED12S/830 PSU-E C PG WH	LED12S	1 pc	High-gloss mirror	DN560B	Yes
910503586429	DN560B LED12S/830 PSD-VLC-E C PG WH	LED12S	1 pc	High-gloss mirror	DN560B	Yes
910503586432	DN560B LED12S/830 PSU-E C WH	LED12S	1 pc	High-gloss mirror	DN560B	Yes
910503586436	DN560B LED12S/830 PSD-VLC-E C WH	LED12S	1 pc	High-gloss mirror	DN560B	Yes

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product	
					Family Code	Service tag
910503706506	DN560B LED8S/830 PSU-E C WH	LED8S	1 pc	High-gloss mirror	DN560B	Yes
910503706507	DN560B LED8S/840 PSU-E C WH	LED8S	1 pc	High-gloss mirror	DN560B	Yes
910503706508	DN560B LED8S/830 PSD-VLC-E C WH	LED8S	1 pc	High-gloss mirror	DN560B	Yes
910503706509	DN560B LED8S/840 PSD-VLC-E C WH	LED8S	1 pc	High-gloss mirror	DN560B	Yes
910503706529	DN560B LED12S/930 PSU-E C WH	LED12S	1 pc	High-gloss mirror	DN560B	Yes
910503706682	DN560B LED12S/830 PSU-E C ELP3 WH	LED12S	-	High-gloss mirror	DN560B	-
910503586408	DN560B LED12S/830 PSU-E F WH	LED12S	1 pc	Facetted reflector	DN560B	Yes
910503586409	DN560B LED12S/840 PSU-E F WH	LED12S	1 pc	Facetted reflector	DN560B	Yes
910503586410	DN560B LED12S/830 PSD-VLC-E F WH	LED12S	1 pc	Facetted reflector	DN560B	Yes



## LuxSpace Mini, recessed

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product Family Code	Service tag
910503586411	DN560B LED12S/840 PSD-VLC-E F WH	LED12S	1 pc	Facetted reflector	DN560B	Yes
910503586430	DN560B LED12S/830 PSE-E F PG WH	LED12S	1 pc	Facetted reflector	DN560B	Yes
910503586431	DN560B LED12S/830 PSED-VLC-E F PG WH	LED12S	1 pc	Facetted reflector	DN560B	Yes
910503706512	DN560B LED8S/830 PSD-VLC-E F WH	LED8S	1 pc	Facetted reflector	DN560B	Yes
910503706513	DN560B LED8S/840 PSD-VLC-E F WH	LED8S	1 pc	Facetted reflector	DN560B	Yes
910503586412	DN560B LED12S/830 PSU-E M WH	LED12S	1 pc	Matt mirror	DN560B	Yes
910503586414	DN560B LED12S/830 PSU-E WR WH	LED12S	1 pc	White reflector without louver	DN560B	Yes
910503586441	DN561B LED12S/830 PSU-E C WH	LED12S	1 pc	High-gloss mirror	DN561B	-
910503586442	DN561B LED12S/840 PSU-E C WH	LED12S	1 pc	High-gloss mirror	DN561B	-
910503586443	DN561B LED12S/830 PSD-VLC-E C WH	LED12S	1 pc	High-gloss mirror	DN561B	-
910503586444	DN561B LED12S/840 PSD-VLC-E C WH	LED12S	1 pc	High-gloss mirror	DN561B	-
910503586465	DN561B LED12S/830 PSE-E C PG WH	LED12S	1 pc	High-gloss mirror	DN561B	-
910503586466	DN561B LED12S/830 PSED-VLC-E C PG WH	LED12S	1 pc	High-gloss mirror	DN561B	-

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product Family Code	Service tag
910503706514	DN561B LED8S/830 PSU-E C WH	LED8S	1 pc	High-gloss mirror	DN561B	-
910503706515	DN561B LED8S/840 PSU-E C WH	LED8S	1 pc	High-gloss mirror	DN561B	-
910503706516	DN561B LED8S/830 PSD-VLC-E C WH	LED8S	1 pc	High-gloss mirror	DN561B	-
910503706517	DN561B LED8S/840 PSD-VLC-E C WH	LED8S	1 pc	High-gloss mirror	DN561B	-
910503586445	DN561B LED12S/830 PSE-E F WH	LED12S	1 pc	Facetted reflector	DN561B	-
910503586446	DN561B LED12S/840 PSU-E F WH	LED12S	1 pc	Facetted reflector	DN561B	-
910503586447	DN561B LED12S/830 PSED-VLC-E F WH	LED12S	1 pc	Facetted reflector	DN561B	-
910503586448	DN561B LED12S/840 PSD-VLC-E F WH	LED12S	1 pc	Facetted reflector	DN561B	-
910503586467	DN561B LED12S/830 PSE-E F PG WH	LED12S	1 pc	Facetted reflector	DN561B	-
910503586468	DN561B LED12S/830 PSED-VLC-E F PG WH	LED12S	1 pc	Facetted reflector	DN561B	-
910503706518	DN561B LED8S/830 PSU-E F WH	LED8S	1 pc	Facetted reflector	DN561B	-
910503586451	DN561B LED12S/830 PSU-E WR WH	LED12S	1 pc	White reflector without louver	DN561B	-

### Initial Performance (IEC Compliant) (1/2)

## LuxSpace Mini, recessed

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910503586404	DN560B LED12S/830 PSU-E C WH	(0.43, 0.40) SDCM <3	3000 K	>80	103 lm/W
910503586405	DN560B LED12S/840 PSU-E C WH	(0.38, 0.37) SDCM <3	4000 K	>80	103 lm/W
910503586406	DN560B LED12S/830 PSD-VLC-E C WH	(0.43, 0.40) SDCM <3	3000 K	>80	103 lm/W
910503586407	DN560B LED12S/840 PSD-VLC-E C WH	(0.38, 0.37) SDCM <3	4000 K	>80	103 lm/W
910503586428	DN560B LED12S/830 PSU-E C PG WH	(0.43, 0.40) SDCM <3	3000 K	>80	99 lm/W
910503586429	DN560B LED12S/830 PSD-VLC-E C PG WH	(0.43, 0.40) SDCM <3	3000 K	>80	99 lm/W
910503586432	DN560B LED12S/830 PSU-E C WH	(0.43, 0.40) SDCM <3	3000 K	>80	103 lm/W
910503586436	DN560B LED12S/830 PSD-VLC-E C WH	(0.43, 0.40) SDCM <3	3000 K	>80	103 lm/W
910503706506	DN560B LED8S/830 PSU-E C WH	(0.43, 0.40) SDCM <3	3000 K	>80	103 lm/W
910503706507	DN560B LED8S/840 PSU-E C WH	(0.38, 0.37) SDCM <3	4000 K	>80	103 lm/W
910503706508	DN560B LED8S/830 PSD-VLC-E C WH	(0.43, 0.40) SDCM <3	3000 K	>80	103 lm/W
910503706509	DN560B LED8S/840 PSD-VLC-E C WH	(0.38, 0.37) SDCM <3	4000 K	>80	103 lm/W
910503706529	DN560B LED12S/930 PSU-E C WH	(0.43, 0.40) SDCM <3	3000 K	>90	77 lm/W
910503706682	DN560B LED12S/830 PSU-E C ELP3 WH	(0.43, 0.40) SDCM <3	3000 K	>80	83 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910503586408	DN560B LED12S/830 PSU-E F WH	(0.43, 0.40) SDCM <3	3000 K	>80	103 lm/W
910503586409	DN560B LED12S/840 PSU-E F WH	(0.38, 0.37) SDCM <3	4000 K	>80	103 lm/W
910503586410	DN560B LED12S/830 PSD-VLC-E F WH	(0.43, 0.40) SDCM <3	3000 K	>80	103 lm/W
910503586411	DN560B LED12S/840 PSD-VLC-E F WH	(0.38, 0.37) SDCM <3	4000 K	>80	103 lm/W
910503586430	DN560B LED12S/830 PSE-E F PG WH	(0.43, 0.40) SDCM <3	3000 K	>80	99 lm/W
910503586431	DN560B LED12S/830 PSED-VLC-E F PG WH	(0.43, 0.40) SDCM <3	3000 K	>80	99 lm/W
910503706512	DN560B LED8S/830 PSD-VLC-E F WH	(0.43, 0.40) SDCM <3	3000 K	>80	103 lm/W
910503706513	DN560B LED8S/840 PSD-VLC-E F WH	(0.38, 0.37) SDCM <3	4000 K	>80	103 lm/W
910503586412	DN560B LED12S/830 PSU-E M WH	(0.43, 0.40) SDCM <3	3000 K	>80	91 lm/W
910503586414	DN560B LED12S/830 PSU-E WR WH	(0.43, 0.40) SDCM <3	3000 K	>80	99 lm/W
910503586441	DN561B LED12S/830 PSU-E C WH	(0.43, 0.40) SDCM <3	3000 K	>80	99 lm/W
910503586442	DN561B LED12S/840 PSU-E C WH	(0.38, 0.37) SDCM <3	4000 K	>80	99 lm/W
910503586443	DN561B LED12S/830 PSD-VLC-E C WH	(0.43, 0.40) SDCM <3	3000 K	>80	99 lm/W
910503586444	DN561B LED12S/840 SDCM <3	(0.38, 0.37) SDCM <3	4000 K	>80	99 lm/W

## LuxSpace Mini, recessed

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
	PSD-VLC-E C WH				
910503586465	DN561B LED12S/830 PSE-E C PG WH	(0.43, 0.40)	3000 K	>80	95 lm/W
910503586466	DN561B LED12S/830 PSED-VLC-E C PG WH	(0.43, 0.40)	3000 K	>80	95 lm/W
910503706514	DN561B LED8S/830 PSU-E C WH	(0.43, 0.40)	3000 K	>80	98 lm/W
910503706515	DN561B LED8S/840 PSU-E C WH	(0.38, 0.37)	4000 K	>80	98 lm/W
910503706516	DN561B LED8S/830 PSD-VLC-E C WH	(0.43, 0.40)	3000 K	>80	98 lm/W
910503706517	DN561B LED8S/840 PSD-VLC-E C WH	(0.38, 0.37)	4000 K	>80	98 lm/W
910503586445	DN561B LED12S/830 PSE-E F WH	(0.43, 0.40)	3000 K	>80	99 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910503586446	DN561B LED12S/840 PSU-E F WH	(0.38, 0.37)	4000 K	>80	99 lm/W
910503586447	DN561B LED12S/830 PSED-VLC-E F WH	(0.43, 0.40)	3000 K	>80	99 lm/W
910503586448	DN561B LED12S/840 PSD-VLC-E F WH	(0.38, 0.37)	4000 K	>80	99 lm/W
910503586467	DN561B LED12S/830 PSE-E F PG WH	(0.43, 0.40)	3000 K	>80	95 lm/W
910503586468	DN561B LED12S/830 PSED-VLC-E F PG WH	(0.43, 0.40)	3000 K	>80	95 lm/W
910503706518	DN561B LED8S/830 PSU-E F WH	(0.43, 0.40)	3000 K	>80	98 lm/W
910503586451	DN561B LED12S/830 PSU-E WR WH	(0.43, 0.40)	3000 K	>80	95 lm/W

### Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial luminous flux	Initial input power
910503586404	DN560B LED12S/830 PSU-E C WH	1200 lm	11.6 W
910503586405	DN560B LED12S/840 PSU-E C WH	1200 lm	11.6 W
910503586406	DN560B LED12S/830 PSD-VLC-E C WH	1200 lm	11.6 W
910503586407	DN560B LED12S/840 PSD-VLC-E C WH	1200 lm	11.6 W
910503586428	DN560B LED12S/830 PSU-E C PG WH	1150 lm	11.6 W
910503586429	DN560B LED12S/830 PSD-VLC-E C PG WH	1150 lm	11.6 W
910503586432	DN560B LED12S/830 PSU-E C WH	1200 lm	11.6 W
910503586436	DN560B LED12S/830 PSD-VLC-E C WH	1200 lm	11.6 W
910503706506	DN560B LED8S/830 PSU-E C WH	820 lm	8 W
910503706507	DN560B LED8S/840 PSU-E C WH	820 lm	8 W
910503706508	DN560B LED8S/830 PSD-VLC-E C WH	820 lm	8 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
910503706509	DN560B LED8S/840 PSD-VLC-E C WH	820 lm	8 W
910503706529	DN560B LED12S/930 PSU-E C WH	980 lm	12.8 W
910503706682	DN560B LED12S/830 PSU-E C ELP3 WH	1200 lm	14.4 W
910503586408	DN560B LED12S/830 PSU-E F WH	1200 lm	11.6 W
910503586409	DN560B LED12S/840 PSU-E F WH	1200 lm	11.6 W
910503586410	DN560B LED12S/830 PSD-VLC-E F WH	1200 lm	11.6 W
910503586411	DN560B LED12S/840 PSD-VLC-E F WH	1200 lm	11.6 W
910503586430	DN560B LED12S/830 PSE-E F PG WH	1150 lm	11.6 W
910503586431	DN560B LED12S/830 PSED-VLC-E F PG WH	1150 lm	11.6 W
910503706512	DN560B LED8S/830 PSD-VLC-E F WH	820 lm	8 W

## LuxSpace Mini, recessed

Order Code	Full Product Name	Initial luminous flux	Initial input power
910503706513	DN560B LED8S/840 PSD-VLC-E F WH	820 lm	8 W
910503586412	DN560B LED12S/830 PSU-E M WH	1050 lm	11.6 W
910503586414	DN560B LED12S/830 PSU-E WR WH	1150 lm	11.6 W
910503586441	DN561B LED12S/830 PSU-E C WH	1150 lm	11.6 W
910503586442	DN561B LED12S/840 PSU-E C WH	1150 lm	11.6 W
910503586443	DN561B LED12S/830 PSD-VLC-E C WH	1150 lm	11.6 W
910503586444	DN561B LED12S/840 PSD-VLC-E C WH	1150 lm	11.6 W
910503586465	DN561B LED12S/830 PSE-E C PG WH	1100 lm	11.6 W
910503586466	DN561B LED12S/830 PSED-VLC-E C PG WH	1100 lm	11.6 W
910503706514	DN561B LED8S/830 PSU-E C WH	780 lm	8 W
910503706515	DN561B LED8S/840 PSU-E C WH	780 lm	8 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
910503706516	DN561B LED8S/830 PSD-VLC-E C WH	780 lm	8 W
910503706517	DN561B LED8S/840 PSD-VLC-E C WH	780 lm	8 W
910503586445	DN561B LED12S/830 PSE-E F WH	1150 lm	11.6 W
910503586446	DN561B LED12S/840 PSU-E F WH	1150 lm	11.6 W
910503586447	DN561B LED12S/830 PSED-VLC-E F WH	1150 lm	11.6 W
910503586448	DN561B LED12S/840 PSD-VLC-E F WH	1150 lm	11.6 W
910503586467	DN561B LED12S/830 PSE-E F PG WH	1100 lm	11.6 W
910503586468	DN561B LED12S/830 PSED-VLC-E F PG WH	1100 lm	11.6 W
910503706518	DN561B LED8S/830 PSU-E F WH	780 lm	8 W
910503586451	DN561B LED12S/830 PSU-E WR WH	1100 lm	11.6 W

### Light Technical

Order Code	Full Product Name	Optical cover/lens acc. type
910503586404	DN560B LED12S/830 PSU-E C WH	-
910503586405	DN560B LED12S/840 PSU-E C WH	-
910503586406	DN560B LED12S/830 PSD-VLC-E C WH	-
910503586407	DN560B LED12S/840 PSD-VLC-E C WH	-
910503586428	DN560B LED12S/830 PSU-E C PG WH	Protection glass
910503586429	DN560B LED12S/830 PSD-VLC-E C PG WH	Protection glass
910503586432	DN560B LED12S/830 PSU-E C WH	-
910503586436	DN560B LED12S/830 PSD-VLC-E C WH	-
910503706506	DN560B LED8S/830 PSU-E C WH	-
910503706507	DN560B LED8S/840 PSU-E C WH	-
910503706508	DN560B LED8S/830 PSD-VLC-E C WH	-
910503706509	DN560B LED8S/840 PSD-VLC-E C WH	-
910503706529	DN560B LED12S/930 PSU-E C WH	-
910503706682	DN560B LED12S/830 PSU-E C ELP3 WH	-
910503586408	DN560B LED12S/830 PSU-E F WH	-
910503586409	DN560B LED12S/840 PSU-E F WH	-
910503586410	DN560B LED12S/830 PSD-VLC-E F WH	-
910503586411	DN560B LED12S/840 PSD-VLC-E F WH	-
910503586430	DN560B LED12S/830 PSE-E F PG WH	Protection glass
910503586431	DN560B LED12S/830 PSED-VLC-E F PG WH	Protection glass
910503706512	DN560B LED8S/830 PSD-VLC-E F WH	-

Order Code	Full Product Name	Optical cover/lens acc. type
910503706513	DN560B LED8S/840 PSD-VLC-E F WH	-
910503586412	DN560B LED12S/830 PSU-E M WH	-
910503586414	DN560B LED12S/830 PSU-E WR WH	-
910503586441	DN561B LED12S/830 PSU-E C WH	-
910503586442	DN561B LED12S/840 PSU-E C WH	-
910503586443	DN561B LED12S/830 PSD-VLC-E C WH	-
910503586444	DN561B LED12S/840 PSD-VLC-E C WH	-
910503586465	DN561B LED12S/830 PSE-E C PG WH	Protection glass
910503586466	DN561B LED12S/830 PSED-VLC-E C PG WH	Protection glass
910503706514	DN561B LED8S/830 PSU-E C WH	-
910503706515	DN561B LED8S/840 PSU-E C WH	-
910503706516	DN561B LED8S/830 PSD-VLC-E C WH	-
910503706517	DN561B LED8S/840 PSD-VLC-E C WH	-
910503586445	DN561B LED12S/830 PSE-E F WH	-
910503586446	DN561B LED12S/840 PSU-E F WH	-
910503586447	DN561B LED12S/830 PSED-VLC-E F WH	-
910503586448	DN561B LED12S/840 PSD-VLC-E F WH	-
910503586467	DN561B LED12S/830 PSE-E F PG WH	Protection glass
910503586468	DN561B LED12S/830 PSED-VLC-E F PG WH	Protection glass
910503706518	DN561B LED8S/830 PSU-E F WH	-
910503586451	DN561B LED12S/830 PSU-E WR WH	-

### Mechanical and Housing

Order Code	Full Product Name	Color
910503586404	DN560B LED12S/830 PSU-E C WH	White RAL 9003
910503586405	DN560B LED12S/840 PSU-E C WH	White RAL 9003
910503586406	DN560B LED12S/830 PSD-VLC-E C WH	White RAL 9003
910503586407	DN560B LED12S/840 PSD-VLC-E C WH	White RAL 9003

Order Code	Full Product Name	Color
910503586428	DN560B LED12S/830 PSU-E C PG WH	White RAL 9003
910503586429	DN560B LED12S/830 PSD-VLC-E C PG WH	White RAL 9003
910503586432	DN560B LED12S/830 PSU-E C WH	White RAL 9003
910503586436	DN560B LED12S/830 PSD-VLC-E C WH	White RAL 9003

## LuxSpace Mini, recessed

Order Code	Full Product Name	Color
910503706506	DN560B LED8S/830 PSU-E C WH	White RAL 9003
910503706507	DN560B LED8S/840 PSU-E C WH	White RAL 9003
910503706508	DN560B LED8S/830 PSD-VLC-E C WH	White RAL 9003
910503706509	DN560B LED8S/840 PSD-VLC-E C WH	White RAL 9003
910503706529	DN560B LED12S/930 PSU-E C WH	White RAL 9003
910503706682	DN560B LED12S/830 PSU-E C ELP3 WH	White RAL 9003
910503586408	DN560B LED12S/830 PSU-E F WH	White RAL 9003
910503586409	DN560B LED12S/840 PSU-E F WH	White RAL 9003
910503586410	DN560B LED12S/830 PSD-VLC-E F WH	White RAL 9003
910503586411	DN560B LED12S/840 PSD-VLC-E F WH	White RAL 9003
910503586430	DN560B LED12S/830 PSE-E F PG WH	White RAL 9003
910503586431	DN560B LED12S/830 PSED-VLC-E F PG WH	White RAL 9003
910503706512	DN560B LED8S/830 PSD-VLC-E F WH	White RAL 9003
910503706513	DN560B LED8S/840 PSD-VLC-E F WH	White RAL 9003
910503586412	DN560B LED12S/830 PSU-E M WH	White RAL 9003
910503586414	DN560B LED12S/830 PSU-E WR WH	White RAL 9003
910503586441	DN561B LED12S/830 PSU-E C WH	White

Order Code	Full Product Name	Color
910503586442	DN561B LED12S/840 PSU-E C WH	White
910503586443	DN561B LED12S/830 PSD-VLC-E C WH	White
910503586444	DN561B LED12S/840 PSD-VLC-E C WH	White
910503586465	DN561B LED12S/830 PSE-E C PG WH	White RAL 9003
910503586466	DN561B LED12S/830 PSED-VLC-E C PG WH	White RAL 9003
910503706514	DN561B LED8S/830 PSU-E C WH	White
910503706515	DN561B LED8S/840 PSU-E C WH	White
910503706516	DN561B LED8S/830 PSD-VLC-E C WH	White
910503706517	DN561B LED8S/840 PSD-VLC-E C WH	White
910503586445	DN561B LED12S/830 PSE-E F WH	White RAL 9003
910503586446	DN561B LED12S/840 PSU-E F WH	White
910503586447	DN561B LED12S/830 PSED-VLC-E F WH	White RAL 9003
910503586448	DN561B LED12S/840 PSD-VLC-E F WH	White
910503586467	DN561B LED12S/830 PSE-E F PG WH	White RAL 9003
910503586468	DN561B LED12S/830 PSED-VLC-E F PG WH	White RAL 9003
910503706518	DN561B LED8S/830 PSU-E F WH	White
910503586451	DN561B LED12S/830 PSU-E WR WH	White

