



Reliable Compact Fluorescent lamp non- integrated

PL-L Essential.

Energy-saving compact fluorescent non-integrated lamp

Benefits

- Good color rendering (CRI >80)
- Long life and sustainable light output

Features

- 4-pin base without starter and capacitor
- Fluorescent tri-phosphor technology

Application

- Designed for use in general lighting in shops and residential areas

PL-L Essential.

Versions




LPPR PLL4PAPR 0002



LPPR PLL4PAPR 0003

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-L Essential 36W/865/4P 1CT/50	37.5 mm	16.9 mm	382.2 mm	408 mm	415.0 mm
PL-L Essential 55W/865/4P 1CT/50	37.5 mm	16.9 mm	507.2 mm	532 mm	539.0 mm

General Information	
Cap-Base	2G11
Light Technical	
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	80
Luminous Efficacy (rated) (Nom)	69 lm/W
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg

Light Technical

Order Code	Full Product Name	Luminous Flux
927933686503	PL-L Essential 36W/865/4P 1CT/50	2,550 lm

Order Code	Full Product Name	Luminous Flux
927933786503	PL-L Essential 55W/865/4P 1CT/50	3,900 lm

Operating and Electrical

PL-L Essential.

Order Code	Full Product Name	Lamp	Voltage (Nom)	Power Consumption
		Current (Nom)		
927933686503	PL-L Essential 36W/ 865/4P 1CT/50	0.435 A	106 V	36 W

Order Code	Full Product Name	Lamp	Voltage (Nom)	Power Consumption
		Current (Nom)		
927933786503	PL-L Essential 55W/ 865/4P 1CT/50	0.550 A	101 V	55 W

