



SmartBalance, wall-mounted – Stylish and comfortable

SmartBalance Wall-mounted

Striking the right balance between the different lighting needs in a patient room is a challenge for many hospitals. That's why our bed-head luminaires offer some of the key functionalities required by both patients and staff. The SmartBalance, wall-mounted luminaire combines high-quality lighting performance with a stylish, timeless design. General ambience light is provided indirectly via the upper part of the luminaire. The lower part delivers direct, diffuse light, allowing patients to read and clinical staff to carry out examinations at the bed.

Benefits

- Elegant, slim design
- Delivers patient-room illumination levels
- Energy savings and long lifetime

Features

- Slim design: lower in height than competitor models
- Compliant with lighting norms for patient rooms and corridors
- Appealing, timeless design
- Flexible mounting, both electrical and mechanical
- State-of-the-art LED technology
- Configurator approach to meet a range of hospital requirements

Application

- Patient rooms
- Corridors

Specifications

SmartBalance Wall-mounted

Type	WL484W
Light source	Philips Fortimo LED Line 1R
Power	32.7 to 45 W (depending on type)
Beam angle	Asymmetrical beam
Luminous flux	4,000 or 5,200 lm (downlight versions) 4,400 or 4,600 lm (uplight versions)
Correlated Colour	3,000 or 4,000 K
Temperature	
Colour Rendering Index	>80
Lumen maintenance at median useful life* 50,000 h	L80
Control gear failure rate at median useful life 50,000 h	5%

Performance Ambient Temperature Tq	+25 °C
Operating temperature range	-20 to +30 °C
Driver	Built-in
Mains voltage	230 or 240 V/50-60 Hz
Dimming	DALI dimmable
Options	EFE relay, nightlight
Material	Housing: aluminium Optic: PMMA
Colour	Silver grey (comparable to RAL 9006) White (RAL 9003)
Installation	Screw mounting, directly onto surface Through-wiring not possible

Versions



SmartBalance Wall-mounted
WL484W luminaire with direct/indirect
light distribution

Product details



SmartBalance Wall-mounted

Application Conditions

Ambient temperature range	0 to +35 °C
Maximum dim level	1%
Suitable for random switching	No

Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP40

Controls and Dimming

Dimmable	Yes
----------	-----

Operating and Electrical

Input Voltage	220-240 V
---------------	-----------

General Information

Beam angle of light source	- °
Cap-Base	-
CE mark	CE mark
Protection class IEC	Safety class I (I)
Optical cover/lens type	PC
Driver included	Yes
ENEC mark	ENEC plus mark
Flammability mark	F
Gear	-
Glow-wire test	650/5
Embedded control	No
Light source replaceable	No
Light regulation	-
Number of gear units	2 units
Number of light sources	1
Optic type	No
Product Family Code	WL484W
UL mark	No

Initial Performance (IEC Compliant)

Init. Colour Rendering Index	≥80
Luminous flux tolerance	+/-10%

Mechanical and Housing

Colour	White
--------	-------

General Information

Order Code	Full Product Name	Lamp family code
910504094103	WL484W LED52S/830 PSD D/I SW WH	LED52S
910504096303	WL484W LED40S/840 PSD D/I SW WH	LED40S

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
910504094103	WL484W LED52S/830 PSD D/I SW WH	(0.43, 0.40) SDCM <3	3000 K	116 lm/W	5200 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
910504096303	WL484W LED40S/840 PSD D/I SW WH	(0.38, 0.38) SDCM <3	4000 K	122 lm/W	4000 lm

Initial Performance (IEC Compliant) (2/2)

SmartBalance Wall-mounted

Order Code	Full Product Name	Initial input power	Order Code	Full Product Name	Initial input power
910504094103	WL484W LED52S/830 PSD D/I SW WH	45 W	910504096303	WL484W LED40S/840 PSD D/I SW WH	32.7 W

