



Product Description

Softone ESaver Candle

Standard energy-saving lamps in the shape of an incandescent candle lamp

Benefits

- Light quality and distribution similar to the opalised incandescent lamps
- Gives a soft, diffuse light with a high comfort level

Features

- Long average lifetime compared to a standard incandescent lamp
- Almost instant, flicker-free start (<1 s)
- Light output after 1 minute 95%
- Recommended ambient temperature range to ensure almost constant light output (>90%): between +10°C and +45°C
- Flawless ignition at -20°C and up.

Application

- Designed for replacement of incandescent candle lamps in consumer applications
- Especially for applications where lamps is visible
- Enclosed fixtures are required for outdoor applications
- Not suitable for dimming and electronic devices


Softone ESaver Candle

Versions



12 W E14 B45

Dimensional drawing



Product	D (max)	C (max)	F (max)
Softone Candle 12W WW E14 220-240V 1PF/6	46.5 mm	126.0 mm	43 mm

