



The affordable LEDspot solution

CorePro LEDspot MV

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E27 base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimise maintenance cost.

Benefits

- Warm white light
- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs

Features

- Easy retrofit
- Lifetime of 15,000 hours
- Compatible with an extensive range of dimmers
- UV- and IR-free light
- Free of mercury and hazardous materials – RoHS Compliant

Application


- Hotels, restaurants, bars, cafés, museums, shops
- Lobbies, corridors, stairwells, washrooms, reception areas, exhibitions, display cabinets

CorePro LEDspot MV


Versions




Dimensional drawing



Product	D	C
CorePro LEDspot 5-50W GU10 827 36D DIM	50 mm	54 mm




Accent Diagrams



CorePro LEDspotMV 50W GU10 830 36D CLA

CorePro LEDspot MV

Beam Diagrams



CorePro LEDspotMV 50W GU10 830 36D CLA

