



# Simple, robust magnetic ballast

## HID-Basic ballasts for HPL and HPI(PLUS) lamps

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.

### Benefits

- Limited volume of ballast coil; also lightweight
- Simple installation and cabling

### Features

- Orthocyclic winding process
- Ballasts equipped with screw terminal blocks as standard
- Earthing-while-mounting facility (HID Standard ballasts)
- Low wattage losses

### Application

- For built-in applications for road and public lighting with HPL, HPI and HPI (Plus) lamps
- HID-Basic ballasts should be restricted to built-in situations where relative humidity is limited.


# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## Versions




GPPR BCHPL1 0001

## Dimensional drawing



Product	D1	C1	A1	A2	B1
BHLA 125L 200	6.3 mm	64.5 mm	120.0 mm	100.0 mm	75.0 mm



Product	D1	C1	A1	A2	B1
BHL 250L 202	6.3 mm	64.5 mm	125.0 mm	104.0 mm	72.5 mm
BHL 400L 202	6.3 mm	64.5 mm	150.0 mm	134.0 mm	75.5 mm
BHLE 400L 202	6.2 mm	64.5 mm	165.0 mm	144.0 mm	75.5 mm



## HID-Basic ballasts for HPL and HPI(PLUS) lamps

### Operating and Electrical

Input Frequency	50 Hz
Line Frequency	50 Hz

### Operating and Electrical

Order Code	Full Product Name	Input Voltage	Order Code	Full Product Name	Input Voltage
913710102550	BHL 250L 202	230 V	913713017650	BHLE 400L 202	230 V
913710102650	BHL 400L 202	230 V	913713018659	BHLA 125L 200	220 V

